



□□□□□

Eaton 192324

Eaton Moeller series Molded case circuit breaker, PXR25, Electronic, NZMN3, 450 A, Three-pole, 690 V, Screw connection

□□□□

PRODUCT NAME	Eaton Moeller series NZM molded case circuit breaker electronic
CATALOG NUMBER	192324
PRODUCT LENGTH/DEPTH	275 mm
PRODUCT HEIGHT	120.5 mm
PRODUCT WIDTH	140 mm
PRODUCT WEIGHT	6.65 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 60947 IEC

AMPERAGE RATING	450 A
VOLTAGE RATING	690 V - 690 V
CIRCUIT BREAKER FRAME TYPE	NZM3
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

	eaton-circuit-breaker-nzm-mccb-characteristic-curve-015.eps
CHARACTERISTIC CURVE	eaton-circuit-breaker-nzm-mccb-characteristic-curve-011.eps eaton-circuit-breaker-nzm-mccb-characteristic-curve-029.eps
MCAD MODEL	eaton-molded-case-switches-mcad-3d-models-nzm3-3p.stp eaton-molded-case-switches-mcad-drawings-nzm3-3p.dwg
PEP ECO-PASSPORT	eaton-molded-case-switches-pep-eato-00251-v0101-en.pdf
□□□□□	eaton-circuit-breaker-basic-unit-bg3-il012100zu.pdf
	eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps
□□	eaton-circuit-breaker-nzm-mccb-dimensions-020.eps eaton-general-ie-ready-dilm-contactor-standards.eps

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Thermal protection
POLLUTION DEGREE	3
LIFESPAN, MECHANICAL	15000 operations
UTILIZATION CATEGORY	A (IEC/EN 60947-2)
MOUNTING METHOD	Built-in device fixed built-in technique Fixed
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	60.75 W
ISOLATION	500 V AC (between auxiliary contacts and main contacts) 300 V AC (between the auxiliary contacts)
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
PROTECTION AGAINST DIRECT CONTACT	Finger and back-of-hand proof to VDE 0106 part

	100
RATED INSULATION VOLTAGE (UI)	690 V
RATED OPERATING POWER AT AC-3, 230 V	132 kW
RATED OPERATING POWER AT AC-3, 400 V	250 kW
SWITCH OFF TECHNIQUE	Electronic
DEGREE OF PROTECTION	IP20 IP20 (basic degree of protection, in the operating controls area)
DIRECTION OF INCOMING SUPPLY	As required
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION (IP), FRONT SIDE	IP66 (with door coupling rotary handle) IP40 (with insulating surround)
DEGREE OF PROTECTION (TERMINATIONS)	IP10 (tunnel terminal) IP00 (terminations, phase isolator and strip terminal)
NUMBER OF POLES	Three-pole
TERMINAL CAPACITY (COPPER STRIP)	Min. 6 segments of 16 mm x 0.8 mm at box terminal Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched) 10 segments of 50 mm x 1 mm (2x) at rear-side width extension Max. 10 segments of 24 mm x 1 mm + 5 segments of 24 mm x 1 mm at box terminal Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1 mm at rear-side connection (punched) Max. 8 segments of 24 mm x 1 mm (2x) at box terminal
LIFESPAN, ELECTRICAL	5000 operations at 400 V AC-1 2000 operations at 690 V AC-3 3000 operations at 690 V AC-1 2000 operations at 400 V

	AC-3 2000 operations at 415 V AC-3 5000 operations at 415 V AC-1
FUNCTIONS	Motor protection with class 1 energy metering Phase failure sensitive
TYPE	Circuit breaker

SPECIAL FEATURES

- IEC/EN 60947-2
with characteristic
conforming to
IEC/EN 60947-4-1
with phase failure
sensitivity
- The circuit-breaker
fulfills all
requirements for
AC-3 switching
category.
- R.m.s. value
measurement and
"thermal memory"
- Adjustable time
delay setting to
overcome current
peaks I_r at $6 \times I_r$
also infinity
(without overload
releases)
- All AC-3 rating data
applies to direct
switching by the
circuit-breaker
under normal
operating
conditions. If, for
example, a
contactor takes
over AC-3 switching
under normal
operating
conditions, the full
rated
uninterrupted
current applies to
the circuit-breaker,
 $I_n = I_u$.
- Maximum back-up
fuse, if the
expected short-
circuit currents at
the installation
location exceed the
switching capacity
of the circuit
breaker (Rated

- short-circuit
breaking capacity
I_{cn})
- Rated current =
rated
uninterrupted
current: 450 A
 - Terminal capacity
hint: Up to 240
mm² can be
connected
depending on the
cable
manufacturer.

APPLICATION	Use in unearthed supply systems at 690 V
SHOCK RESISTANCE	20 g (half-sinusoidal shock 20 ms)
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (I_N)	450 A
RATED SHORT-TIME WITHSTAND CURRENT (I_t = 0.3 S)	3.3 kA
RATED SHORT-TIME WITHSTAND CURRENT (I_t = 1 S)	3.3 kA
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX	5400 A
SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN	900 A
HANDLE TYPE	Rocker lever
INSTANTANEOUS CURRENT SETTING (I_{II}) - MAX	12 A
INSTANTANEOUS CURRENT SETTING (I_{II}) - MIN	2 A
NUMBER OF OPERATIONS PER HOUR - MAX	60
OVERLOAD CURRENT SETTING (I_R) - MAX	450 A
OVERLOAD CURRENT SETTING (I_R) - MIN	180 A
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 230 V, 50/60 HZ	85 kA
RATED SHORT-CIRCUIT	35 kA

BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ	
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 440 V, 50/60 HZ	35 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 525 V, 50/60 HZ	13 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 690 V, 50/60 HZ	5 kA
STANDARD TERMINALS	Screw terminal
OPTIONAL TERMINALS	Box terminal. Connection on rear. Tunnel terminal
RELEASE SYSTEM	Electronic release
SHORT-CIRCUIT TOTAL BREAKTIME	< 10 ms
TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)	16 mm ² (1x) at tunnel terminal
TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)	25 mm ² - 185 mm ² (1x) at tunnel terminal 50 mm ² - 240 mm ² (2x) at 2-hole tunnel terminal 50 mm ² - 240 mm ² (1x) at 2-hole tunnel terminal
TERMINAL CAPACITY (CONTROL CABLE)	0.75 mm ² - 1.5 mm ² (2x) 0.75 mm ² - 2.5 mm ² (1x)
TERMINAL CAPACITY (COPPER BUSBAR)	Max. 10 mm x 50 mm (2x) at rear-side width extension Min. 20 mm x 5 mm direct at switch rear-side connection M10 at rear-side screw connection Max. 30 mm x 10 mm + 30 mm x 5 mm direct at switch rear-side connection
TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)	300 mm ² (2x) at rear-side width extension 16 mm ² (1x) at tunnel terminal 16 mm ² (2x) at box terminal 16 mm ² (1x) direct at switch rear-side connection 16 mm ² (2x) direct at switch rear-side

	connection
TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)	25 mm ² - 120 mm ² (2x) at box terminal
	25 mm ² - 240 mm ² (2x) direct at switch rear-side connection
	35 mm ² - 240 mm ² (1x) at box terminal
	16 mm ² - 185 mm ² (1x) at 1-hole tunnel terminal
	25 mm ² - 240 mm ² (1x) direct at switch rear-side connection
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 400/415 V, 50/60 HZ	35 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ	105 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ	74 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ	53 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ	40 kA
RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ	187 kA
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS	6000 V
RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS	8000 V

□□□□:
□□□□:
□□□:
□□: