



□□□□□

## Eaton 192364

Eaton Moeller series NZM - Molded Case Circuit Breaker. NZM3 PXR25 circuit breaker - integrated energy measurement class 1, 400A, 3p, box terminal, N, 3

□□□□

|                             |                                                                 |
|-----------------------------|-----------------------------------------------------------------|
| <b>PRODUCT NAME</b>         | Eaton Moeller series NZM molded case circuit breaker electronic |
| <b>CATALOG NUMBER</b>       | 192364                                                          |
| <b>PRODUCT LENGTH/DEPTH</b> | 275 mm                                                          |
| <b>PRODUCT HEIGHT</b>       | 120.5 mm                                                        |
| <b>PRODUCT WIDTH</b>        | 140 mm                                                          |
| <b>PRODUCT WEIGHT</b>       | 6.65 kg                                                         |
| <b>COMPLIANCES</b>          | RoHS conform                                                    |
| <b>CERTIFICATIONS</b>       | IEC/EN 60947<br>IEC                                             |



Powering Business Worldwide

## □□□□

**AMPERAGE RATING** 400 A

**VOLTAGE RATING** 690 V - 690 V

**CIRCUIT BREAKER FRAME TYPE** NZM3

**FEATURES** Protection unit  
Motor drive optional

**10.10 TEMPERATURE RISE** The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

**10.11 SHORT-CIRCUIT RATING** Is the panel builder's responsibility. The specifications for the switchgear must be observed.

**10.12 ELECTROMAGNETIC COMPATIBILITY** Is the panel builder's responsibility. The specifications for the switchgear must be observed.

**10.13 MECHANICAL FUNCTION** The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

**10.2.2 CORROSION RESISTANCE** Meets the product standard's requirements.

**10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES** Meets the product standard's requirements.

**10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT** Meets the product standard's requirements.

**10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS** Meets the product standard's requirements.

**10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION** Meets the product standard's requirements.

**10.2.5 LIFTING** Does not apply, since the entire switchgear needs to be evaluated.

**10.2.6 MECHANICAL IMPACT** Does not apply, since the entire switchgear needs to be evaluated.

**10.2.7 INSCRIPTIONS** Meets the product standard's requirements.

## □□

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-029.eps](#)

CHARACTERISTIC CURVE

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-015.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-011.eps](#)

□□□□□

[eaton-circuit-breaker-basic-unit-bg3-il012100zu.pdf](#)

□□

[eaton-circuit-breaker-nzm-mccb-dimensions-020.eps](#)

[eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps](#)

|                                                                 |                                                                                                      |
|-----------------------------------------------------------------|------------------------------------------------------------------------------------------------------|
| <b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>                  | Does not apply, since the entire switchgear needs to be evaluated.                                   |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.                                                           |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated.                                   |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated.                                   |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.                                                               |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.                                                               |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.                                                               |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.                                                               |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.                                                               |
| <b>POLLUTION DEGREE</b>                                         | 3                                                                                                    |
| <b>LIFESPAN, MECHANICAL</b>                                     | 15000 operations                                                                                     |
| <b>UTILIZATION CATEGORY</b>                                     | A (IEC/EN 60947-2)                                                                                   |
| <b>MOUNTING METHOD</b>                                          | Built-in device fixed built-in technique<br>Fixed                                                    |
| <b>CLIMATIC PROOFING</b>                                        | Damp heat, constant, to IEC 60068-2-78<br>Damp heat, cyclic, to IEC 60068-2-30                       |
| <b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>            | 48 W                                                                                                 |
| <b>ISOLATION</b>                                                | 500 V AC (between auxiliary contacts and main contacts)<br>300 V AC (between the auxiliary contacts) |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                      | 70 °C                                                                                                |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                      | -25 °C                                                                                               |
| <b>AMBIENT STORAGE TEMPERATURE - MAX</b>                        | 70 °C                                                                                                |
| <b>AMBIENT STORAGE TEMPERATURE - MIN</b>                        | 40 °C                                                                                                |
| <b>NUMBER OF AUXILIARY</b>                                      | 0                                                                                                    |

|                                                                |                                                                                                                                                                                                                                                                                                                                                                                                                       |
|----------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>CONTACTS (CHANGE-OVER CONTACTS)</b>                         |                                                                                                                                                                                                                                                                                                                                                                                                                       |
| <b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b> | 0                                                                                                                                                                                                                                                                                                                                                                                                                     |
| <b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>   | 0                                                                                                                                                                                                                                                                                                                                                                                                                     |
| <b>PROTECTION AGAINST DIRECT CONTACT</b>                       | Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110                                                                                                                                                                                                                                                                                                                                                       |
| <b>DEGREE OF PROTECTION</b>                                    | IP20 (basic degree of protection, in the operating controls area)<br>IP20                                                                                                                                                                                                                                                                                                                                             |
| <b>DIRECTION OF INCOMING SUPPLY</b>                            | As required                                                                                                                                                                                                                                                                                                                                                                                                           |
| <b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>              | Frame clamp                                                                                                                                                                                                                                                                                                                                                                                                           |
| <b>OVERVOLTAGE CATEGORY</b>                                    | III                                                                                                                                                                                                                                                                                                                                                                                                                   |
| <b>DEGREE OF PROTECTION (IP), FRONT SIDE</b>                   | IP40 (with insulating surround)<br>IP66 (with door coupling rotary handle)                                                                                                                                                                                                                                                                                                                                            |
| <b>DEGREE OF PROTECTION (TERMINATIONS)</b>                     | IP10 (tunnel terminal)<br>IP00 (terminations, phase isolator and strip terminal)                                                                                                                                                                                                                                                                                                                                      |
| <b>NUMBER OF POLES</b>                                         | Three-pole                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>TERMINAL CAPACITY (COPPER STRIP)</b>                        | Max. 10 segments of 24 mm x 1 mm + 5 segments of 24 mm x 1 mm<br>Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched)<br>10 segments of 50 mm x 1 mm (2x) at rear-side width extension<br>Max. 8 segments of 24 mm x 1 mm (2x) at box terminal<br>Min. 6 segments of 16 mm x 0.8 mm at box terminal<br>Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1 mm at rear-side connection (punched) |
| <b>LIFESPAN, ELECTRICAL</b>                                    | 5000 operations at 415 V AC-1<br>3000 operations at 690 V AC-1<br>5000 operations at 400 V AC-1                                                                                                                                                                                                                                                                                                                       |

|                         |                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
|-------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>FUNCTIONS</b>        | Systems, cable, selectivity and generator protection                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                |
| <b>TYPE</b>             | Circuit breaker                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                     |
| <b>SPECIAL FEATURES</b> | <ul style="list-style-type: none"> <li>• LSI overload protection and delayed and non-delayed short-circuit protective device</li> <li>• Class 1 energy measurement, r.m.s. value measurement, and "thermal memory"</li> <li>• USB interface for configuration and test function with Power Xpert Protection Manager software</li> <li>• Interface module in equipment supplied.</li> <li>• Optionally communication-capable with internal Modbus RTU module or CAM</li> <li>• Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity <math>I_{cn}</math>)</li> <li>• Rated current = rated uninterrupted current: 400 A</li> <li>• Terminal capacity hint: Up to 240 mm<sup>2</sup> can be connected depending on the cable manufacturer.</li> </ul> |
| <b>APPLICATION</b>      | Use in unearthed supply systems at 690 V                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                            |
| <b>SHOCK RESISTANCE</b> | 20 g (half-sinusoidal shock 20 ms)                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                                  |

|                                                                      |                                                                                                                                                                                                                                                                                  |
|----------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT</b>               | Front side                                                                                                                                                                                                                                                                       |
| <b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b> | 400 A                                                                                                                                                                                                                                                                            |
| <b>RELEASE SYSTEM</b>                                                | Electronic release                                                                                                                                                                                                                                                               |
| <b>SHORT-CIRCUIT TOTAL BREAKTIME</b>                                 | < 10 ms                                                                                                                                                                                                                                                                          |
| <b>RATED SHORT-TIME WITHSTAND CURRENT (T = 0.3 S)</b>                | 3.3 kA                                                                                                                                                                                                                                                                           |
| <b>RATED SHORT-TIME WITHSTAND CURRENT (T = 1 S)</b>                  | 3.3 kA                                                                                                                                                                                                                                                                           |
| <b>SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX</b>                   | 4000 A                                                                                                                                                                                                                                                                           |
| <b>SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN</b>                   | 320 A                                                                                                                                                                                                                                                                            |
| <b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX</b>               | 4800 A                                                                                                                                                                                                                                                                           |
| <b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN</b>               | 800 A                                                                                                                                                                                                                                                                            |
| <b>TERMINAL CAPACITY (CONTROL CABLE)</b>                             | 0.75 mm <sup>2</sup> - 2.5 mm <sup>2</sup> (1x)<br>0.75 mm <sup>2</sup> - 1.5 mm <sup>2</sup> (2x)                                                                                                                                                                               |
| <b>TERMINAL CAPACITY (COPPER BUSBAR)</b>                             | M10 at rear-side screw connection<br>Min. 20 mm x 5 mm direct at switch rear-side connection<br>Max. 10 mm x 50 mm (2x) at rear-side width extension<br>Max. 30 mm x 10 mm + 30 mm x 5 mm direct at switch rear-side connection                                                  |
| <b>TERMINAL CAPACITY (COPPER SOLID CONDUCTOR/CABLE)</b>              | 16 mm <sup>2</sup> (1x) at tunnel terminal<br>16 mm <sup>2</sup> (1x) direct at switch rear-side connection<br>300 mm <sup>2</sup> (2x) at rear-side width extension<br>16 mm <sup>2</sup> (2x) at box terminal<br>16 mm <sup>2</sup> (2x) direct at switch rear-side connection |
| <b>TERMINAL CAPACITY (ALUMINUM SOLID CONDUCTOR/CABLE)</b>            | 16 mm <sup>2</sup> (1x) at tunnel terminal                                                                                                                                                                                                                                       |

|                                                                                                    |                                                                                                                                                                                                                                                                                                                                                                                                              |
|----------------------------------------------------------------------------------------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>TERMINAL CAPACITY<br/>(COPPER STRANDED<br/>CONDUCTOR/CABLE)</b>                                 | 25 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x)<br>direct at switch rear-side<br>connection<br>16 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at<br>1-hole tunnel terminal<br>35 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) at<br>box terminal<br>25 mm <sup>2</sup> - 120 mm <sup>2</sup> (2x) at<br>box terminal<br>25 mm <sup>2</sup> - 240 mm <sup>2</sup> (2x)<br>direct at switch rear-side<br>connection |
| <b>TERMINAL CAPACITY<br/>(ALUMINUM STRANDED<br/>CONDUCTOR/CABLE)</b>                               | 50 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) at<br>2-hole tunnel terminal<br>25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at<br>tunnel terminal<br>50 mm <sup>2</sup> - 240 mm <sup>2</sup> (2x) at<br>2-hole tunnel terminal                                                                                                                                                                              |
| <b>HANDLE TYPE</b>                                                                                 | Rocker lever                                                                                                                                                                                                                                                                                                                                                                                                 |
| <b>SHORT DELAY CURRENT<br/>SETTING (ISD) - MAX</b>                                                 | 10 A                                                                                                                                                                                                                                                                                                                                                                                                         |
| <b>SHORT DELAY CURRENT<br/>SETTING (ISD) - MIN</b>                                                 | 2 A                                                                                                                                                                                                                                                                                                                                                                                                          |
| <b>INSTANTANEOUS<br/>CURRENT SETTING (II) -<br/>MAX</b>                                            | 12 A                                                                                                                                                                                                                                                                                                                                                                                                         |
| <b>INSTANTANEOUS<br/>CURRENT SETTING (II) -<br/>MIN</b>                                            | 2 A                                                                                                                                                                                                                                                                                                                                                                                                          |
| <b>NUMBER OF<br/>OPERATIONS PER HOUR -<br/>MAX</b>                                                 | 60                                                                                                                                                                                                                                                                                                                                                                                                           |
| <b>OVERLOAD CURRENT<br/>SETTING (IR) - MAX</b>                                                     | 400 A                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>OVERLOAD CURRENT<br/>SETTING (IR) - MIN</b>                                                     | 160 A                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>RATED SHORT-CIRCUIT<br/>BREAKING CAPACITY ICS<br/>(IEC/EN 60947) AT 230 V,<br/>50/60 HZ</b>     | 85 kA                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>RATED SHORT-CIRCUIT<br/>BREAKING CAPACITY ICS<br/>(IEC/EN 60947) AT<br/>400/415 V, 50/60 HZ</b> | 50 kA                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>RATED SHORT-CIRCUIT<br/>BREAKING CAPACITY ICS<br/>(IEC/EN 60947) AT 440 V,<br/>50/60 HZ</b>     | 35 kA                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>RATED SHORT-CIRCUIT<br/>BREAKING CAPACITY ICS<br/>(IEC/EN 60947) AT 525 V,<br/>50/60 HZ</b>     | 13 kA                                                                                                                                                                                                                                                                                                                                                                                                        |
| <b>RATED SHORT-CIRCUIT<br/>BREAKING CAPACITY ICS</b>                                               | 5 kA                                                                                                                                                                                                                                                                                                                                                                                                         |

|                                                                |                                                     |
|----------------------------------------------------------------|-----------------------------------------------------|
| (IEC/EN 60947) AT 690 V, 50/60 HZ                              |                                                     |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 400/415 V, 50/60 HZ | 105 kA                                              |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 440 V, 50/60 HZ     | 74 kA                                               |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 525 V, 50/60 HZ     | 53 kA                                               |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 690 V, 50/60 HZ     | 40 kA                                               |
| STANDARD TERMINALS                                             | Box terminal                                        |
| OPTIONAL TERMINALS                                             | Connection on rear. Screw terminal. Tunnel terminal |
| RATED SHORT-CIRCUIT MAKING CAPACITY ICM AT 240 V, 50/60 HZ     | 187 kA                                              |
| RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT AUXILIARY CONTACTS   | 6000 V                                              |
| RATED IMPULSE WITHSTAND VOLTAGE (UIMP) AT MAIN CONTACTS        | 8000 V                                              |
| RATED INSULATION VOLTAGE (UI)                                  | 690 V AC                                            |

|       |
|-------|
| □□□□: |
| □□□□: |
| □□□:  |
| □□:   |