

## Eaton 192552

Eaton Moeller series NZMN4 PXR20 circuit breaker, 1000 A, 3-pole, Screw terminal, UL/CSA

<b>PRODUCT NAME</b>	Eaton Moeller series NZM molded case circuit breaker electronic
<b>CATALOG NUMBER</b>	192552
<b>PRODUCT LENGTH/DEPTH</b>	401 mm
<b>PRODUCT HEIGHT</b>	207 mm
<b>PRODUCT WIDTH</b>	210 mm
<b>PRODUCT WEIGHT</b>	21 kg
<b>COMPLIANCES</b>	RoHS conform
<b>CERTIFICATIONS</b>	CSA-C22.2 No. 5-09 UL/CSA IEC 60947-2 UL listed UL (File No. E31593) CE marking UL 489 Specially designed for North America CSA (File No. 22086) CSA (Class No. 1432-01) UL (Category Control Number DIVQ) IEC CSA certified

<b>AMPERAGE RATING</b>	1000 A
<b>VOLTAGE RATING</b>	690 V - 690 V
<b>CIRCUIT BREAKER FRAME TYPE</b>	NZM4
<b>FEATURES</b>	Protection unit Motor drive optional
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">DA-DC-03 N4</a>
	<a href="#">eaton-circuit-breaker-basic-unit-bg4-il012101zu.pdf</a>

	be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>MOUNTING METHOD</b>	Fixed Built-in device fixed built-in technique
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>	165 W
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	40 °C
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY</b>	0

<b>CONTACTS (NORMALLY OPEN CONTACTS)</b>	
<b>PROTECTION AGAINST DIRECT CONTACT</b>	Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110
<b>DEGREE OF PROTECTION</b>	IP20
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>NUMBER OF POLES</b>	Three-pole
<b>TERMINAL CAPACITY (COPPER STRIP)</b>	<p>Min. 6 segments of 16 mm x 0.8 mm at flat conductor terminal</p> <p>Max. 10 segments of 32 mm x 1 mm (2x) at flat conductor terminal</p> <p>10 segments of 50 mm x 1 mm (2x) at 1-hole module plate</p> <p>Min. 10 segments of 50 mm x 1 mm (2x) at rear-side connection (punched)</p> <p>Max. 10 segments of 50 mm x 1 mm (2x) at rear-side connection (punched)</p> <p>10 segments of 80 mm x 1 mm (2x) at rear-side width extension</p> <p>NA: same as for IEC</p>
<b>FUNCTIONS</b>	Systems, cable, selectivity and generator protection
<b>TYPE</b>	<ul style="list-style-type: none"> <li>Rated current = rated uninterrupted current: 1000 A</li> <li>Switches conform to UL/CSA as well as the IEC regulations. IEC switching performance values are contained on the rating plate.</li> </ul>
<b>SPECIAL FEATURES</b>	Circuit breaker
<b>APPLICATION</b>	Branch circuits, feeder circuits
<b>POSITION OF CONNECTION FOR MAIN CURRENT CIRCUIT</b>	Front side
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	1000 A

<b>RELEASE SYSTEM</b>	Electronic release
<b>SHORT-CIRCUIT RELEASE DELAYED SETTING - MAX</b>	10000 A
<b>SHORT-CIRCUIT RELEASE DELAYED SETTING - MIN</b>	800 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MAX</b>	18000 A
<b>SHORT-CIRCUIT RELEASE NON-DELAYED SETTING - MIN</b>	2000 A
<b>TERMINAL CAPACITY (COPPER BUSBAR)</b>	M10 at rear-side screw connection Min. 25 mm x 5 mm direct at switch rear-side connection Max. 50 mm x 10 mm (2x) direct at switch rear-side connection Min. 25 mm x 5 mm at rear-side 1-hole module plate Max. 50 mm x 10 mm (2x) at rear-side 1-hole module plate 50 mm x 10 mm (2x) at rear-side 2-hole module plate Min. 60 mm x 10 mm at rear-side width extension Max. 80 mm x 10 mm (2x) at rear-side width extension NA: same as for IEC
<b>TERMINAL CAPACITY (COPPER STRANDED CONDUCTOR/CABLE)</b>	50 mm <sup>2</sup> - 240 mm <sup>2</sup> (4x) at 4- hole tunnel terminal 120 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) direct at switch rear-side connection 50 mm <sup>2</sup> - 185 mm <sup>2</sup> (4x) direct at switch rear-side connection Min. 120 mm <sup>2</sup> - 300 mm <sup>2</sup> (1x) at rear-side 1-hole module plate Max. 95 mm <sup>2</sup> - 300 mm <sup>2</sup> (2x) at rear-side 1-hole module plate Min. 95 mm <sup>2</sup> - 185 mm <sup>2</sup> (2x) at rear-side 2-hole module plate Max. 35 mm <sup>2</sup> - 185 mm <sup>2</sup> (4x) at rear-side 2-hole module plate

	<p>300 mm<sup>2</sup> (4x) at rear-side width extension</p> <p>95 mm<sup>2</sup> - 240 mm<sup>2</sup> (6x) at rear-side width extension</p> <p>NA: AWG 0- kcmil 500 (4x) at 4-hole tunnel terminal</p> <p>NA: kcmil 250 - kcmil 350 (1x) direct at switch rear-side connection</p> <p>NA: AWG 0 - kcmil 350 (4x) direct at switch rear-side connection</p> <p>NA: min. kcmil 250 - kcmil 600 (1x) at rear-side 1-hole module plate</p> <p>NA: max. AWG 3/0 - kcmil 600 (2x) at rear-side 1-hole module plate</p> <p>NA: min. AWG 3/0 - kcmil 350 (2x) at rear-side 2-hole module plate</p> <p>NA: max. AWG 2 - kcmil 350 (4x) at rear-side 2-hole module plate</p> <p>NA: kcmil 600 (4x) at rear-side width extension</p> <p>NA: AWG 3/0 - kcmil 500 (6x) at rear-side width extension</p>
<b>TERMINAL CAPACITY (ALUMINUM STRANDED CONDUCTOR/CABLE)</b>	<p>Min. 185 mm<sup>2</sup> - 240 mm<sup>2</sup> (1x) at rear-side 1-hole module plate</p> <p>Max. 70 mm<sup>2</sup> - 185 mm<sup>2</sup> (2x) at rear-side 1-hole module plate</p> <p>50 mm<sup>2</sup> (4x) at rear-side 2-hole module plate</p> <p>240 mm<sup>2</sup> (2x) at rear-side width extension</p> <p>70 mm<sup>2</sup> - 240 mm<sup>2</sup> (6x) at rear-side width extension</p> <p>NA: aluminum conductor not applicable</p>
<b>HANDLE TYPE</b>	Rocker lever
<b>SHORT DELAY CURRENT SETTING (ISD) - MAX</b>	10000 A
<b>SHORT DELAY CURRENT SETTING (ISD) - MIN</b>	2000 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MAX</b>	18 A
<b>INSTANTANEOUS CURRENT SETTING (II) - MIN</b>	2 A

<b>OVERLOAD CURRENT SETTING (IR) - MAX</b>	1000 A
<b>OVERLOAD CURRENT SETTING (IR) - MIN</b>	400 A
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICS (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b>	50 kA
<b>STANDARD TERMINALS</b>	Screw connection,Optional:Tunnel terminal,Rear-side connection,Strip connection
<b>RATED OPERATING VOLTAGE UE (UL) - MAX</b>	600 V
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 525 V, 50/60 HZ</b>	25 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 400/415 V, 50/60 HZ</b>	50 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 230 V, 50/60 HZ</b>	50 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 690 V, 50/60 HZ</b>	20 kA
<b>RATED SHORT-CIRCUIT BREAKING CAPACITY ICU (IEC/EN 60947) AT 440 V, 50/60 HZ</b>	35 kA
<b>RATED INSULATION VOLTAGE (UI)</b>	690 V AC

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House  
30 Pembroke Road  
Dublin 4,  
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

