



## Eaton 192769

Eaton Moeller® series MSC-DMEA DOL starter, 380 V 400 V 415 V: 11 kW, Ir: 8 - 32 A, Connection to SmartWire-DT: yes, 24 V DC, DC

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series MSC-DMEA DOL starter
<b>CATALOG NUMBER</b>	192769
<b>PRODUCT LENGTH/DEPTH</b>	149.5 mm
<b>PRODUCT HEIGHT</b>	206 mm
<b>PRODUCT WIDTH</b>	45 mm
<b>PRODUCT WEIGHT</b>	0.998 kg
<b>CERTIFICATIONS</b>	VDE 0660 IEC/EN 60947-4-1



Powering Business Worldwide

<b>TYPE</b>	Starter with electronic trip unit
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND</b>	Meets the product

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">eaton-dol-starter-declaration-of-conformity-uk251163en.pdf</a>
<b>MCAD MODEL</b>	<a href="#">msc_dme_bg2.stp</a> <a href="#">eaton-motor-starter-mcad-drawings-msc-dme-bg2.dwg</a>
□□□□	<a href="#">IL034054ZU</a>
□□□	<a href="#">eaton-manual-motor-starters-msc-d-dol-starter-wiring-diagram.eps</a>
□□□□	<a href="#">eaton-msfs-motor-starter-feeder-system-brochure-br034005en-en-us.pdf</a>
□□	<a href="#">eaton-manual-motor-starters-msc-d-dol-starter-dimensions-004.eps</a> <a href="#">eaton-manual-motor-starters-msc-d-dol-starter-3d-drawing-005.eps</a>

<b>CREEPAGE DISTANCES</b>	standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Short-circuit release
<b>POLLUTION DEGREE</b>	3
<b>CLASS</b>	Adjustable
<b>CONNECTION TO SMARTWIRE-DT</b>	Yes In conjunction with PKE-SWD-32 SmartWire DT PKE module
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	6000 V AC
<b>MODEL</b>	IEC starter
<b>ALTITUDE</b>	Max. 2000 m
<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>VOLTAGE TYPE</b>	DC
<b>MOUNTING METHOD</b>	DIN rail
<b>CURRENT FLOW TIMES - MIN</b>	1000 (Class 20) AC-4 cycle operation, Main conducting paths Note: Going below the minimum current flow time can cause overheating of the load (motor). 700 (Class 10) AC-4 cycle operation, Main conducting paths 500 (Class 5) AC-4 cycle operation, Main conducting paths 900 (Class 15) AC-4 cycle

	operation, Main conducting paths For all combinations with an SWD activation, you need not adhere to the minimum current flow times and minimum cut-out periods.
<b>OVERVOLTAGE CATEGORY</b>	III
<b>CONNECTION</b>	Screw terminals
<b>CUT-OUT PERIODS - MIN</b>	≤ 500 ms, main conducting paths, AC-4 cycle operation
<b>FUNCTIONS</b>	Temperature compensated overload protection
<b>OVERLOAD RELEASE CURRENT SETTING - MIN</b>	8 A
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ), TYPE 2, 230 V</b>	100000 A
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ), TYPE 2, 380 V, 400 V, 415 V</b>	100000 A
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX</b>	24 V
<b>RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN</b>	24 V
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V</b>	25 A
<b>PROTOCOL</b>	Other bus systems
<b>RATED OPERATIONAL CURRENT (IE)</b>	21.7 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V</b>	23.4 A
<b>RATED OPERATIONAL VOLTAGE</b>	230 - 690 V AC
<b>SUITABLE FOR</b>	Also motors with efficiency class IE3
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	55 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>COORDINATION TYPE</b>	2
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY</b>	1

<b>CLOSED CONTACTS)</b>	
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>NUMBER OF COMMAND POSITIONS</b>	0
<b>NUMBER OF PILOT LIGHTS</b>	0
<b>OVERLOAD RELEASE CURRENT SETTING - MAX</b>	32 A
<b>RATED OPERATIONAL POWER AT AC-3, 220/230 V, 50 HZ</b>	5.5 kW
<b>RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ</b>	12.5 kW
<b>RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ</b>	15 kW
<b>SHORT-CIRCUIT RELEASE (IRM) - MAX</b>	496 A
<b>COORDINATION CLASS (IEC 60947-4-3)</b>	Class 2
<b>DEGREE OF PROTECTION</b>	IP20 NEMA Other
<b>ELECTRICAL CONNECTION TYPE FOR AUXILIARY- AND CONTROL-CURRENT CIRCUIT</b>	Screw connection
<b>ACTUATING VOLTAGE</b>	24 V DC
<b>POWER CONSUMPTION</b>	0.9 W
<b>RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ</b>	11 kW
<b>RATED OPERATIONAL CURRENT (IE) AT AC-3, 690 V</b>	12.6 A

