



□□□□

Eaton 193059

Eaton xEnergy Light LV systems LV switchgear. Base frame for WxD= 300 x 300mm, grey

□□□□

PRODUCT NAME	Eaton xEnergy Light LV systems LV switchgear
CATALOG NUMBER	193059
PRODUCT LENGTH/DEPTH	276 mm
PRODUCT HEIGHT	240 mm
PRODUCT WIDTH	301 mm
PRODUCT WEIGHT	6.9 kg
COMPLIANCES	RoHS conform



Powering Business Worldwide

FEATURES	Connectable EMC-version Mounting plate depth- adjustable
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility.
10.13 MECHANICAL FUNCTION	Meets the product standard's requirements.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Not applicable.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Not applicable.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Not relevant to indoor installations.
10.2.5 LIFTING	Met; assembled and secured as per the latest applicable instruction leaflet.
10.2.6 MECHANICAL IMPACT	IK10
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Is the panel builder's responsibility.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	< 0.1 Ω; meets the product standard's requirements.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Is the panel builder's responsibility.
10.7 INTERNAL ELECTRICAL CIRCUITS	Is the panel builder's responsibility.

□□□□	eaton-xenergy-light-add-on-distribution-board-product-catalog-2017-en-us.pdf
	eaton-pdd-xenergy-light-catalog-ca014022en-en-us.pdf

AND CONNECTIONS	
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Ui = 690 V AC
10.9.3 IMPULSE WITHSTAND VOLTAGE	6 kV
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Does not apply to metal enclosures.
POLLUTION DEGREE	3
SURFACE FINISHING	Powder coating
DEGREE OF PROTECTION	IK10 Other
MATERIAL QUALITY	Other
COLOR	Gray
PERMISSIBLE LOAD OF THE MOUNTING PLATE ACCORDING TO IEC 62208 - MAX	4000 N
NUMBER OF LOCKS	0
RAL-NUMBER	7035
MATERIAL	Steel
MOUNTING METHOD	Wall fastening
OVERVOLTAGE CATEGORY	IV
INSTALLATION TYPE	Floor standing wall model
PROTECTION CLASS	I
NUMBER OF COVERS/DOORS	0
SUITABLE FOR	Metrical mounting
PERMISSIBLE LOAD OF THE ENCLOSURE ACCORDING TO IEC 62208 - MAX	5000 N
PERMISSIBLE LOAD OF THE DOOR(S) ACCORDING TO IEC 62208 - MAX	1000 N
NUMBER OF CONNECTOR HOLES	0

