



□□□□□

## Eaton 192345

Eaton Moeller series NZM - Molded Case Circuit Breaker. NZM3 PXR25 circuit breaker - integrated energy measurement class 1, 250A, 3p, plug-in technology, H, 3

□□□□

|                             |   |
|-----------------------------|---|
| <b>PRODUCT NAME</b>         | Eaton Moeller series NZM molded case circuit breaker electronic |
| <b>CATALOG NUMBER</b>       | 192345  |
| <b>PRODUCT LENGTH/DEPTH</b> | 335 mm  |
| <b>PRODUCT HEIGHT</b>       | 215.2 mm  |
| <b>PRODUCT WIDTH</b>        | 140 mm  |
| <b>PRODUCT WEIGHT</b>       | 6.85 kg   |
| <b>COMPLIANCES</b>          | RoHS conform  |
| <b>CERTIFICATIONS</b>       | IEC<br>IEC/EN 60947   |

## □□□□

**AMPERAGE RATING** 250 A

**VOLTAGE RATING** 690 V - 690 V

**CIRCUIT BREAKER FRAME TYPE** NZM3

**FEATURES** Protection unit  
Motor drive optional

**ACCESSORIES REQUIRED** NZM3-XSVS

**10.10 TEMPERATURE RISE** The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

**10.11 SHORT-CIRCUIT RATING** Is the panel builder's responsibility. The specifications for the switchgear must be observed.

**10.12 ELECTROMAGNETIC COMPATIBILITY** Is the panel builder's responsibility. The specifications for the switchgear must be observed.

**10.13 MECHANICAL FUNCTION** The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

**10.2.2 CORROSION RESISTANCE** Meets the product standard's requirements.

**10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES** Meets the product standard's requirements.

**10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT** Meets the product standard's requirements.

**10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS** Meets the product standard's requirements.

**10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION** Meets the product standard's requirements.

**10.2.5 LIFTING** Does not apply, since the entire switchgear needs to be evaluated.

**10.2.6 MECHANICAL IMPACT** Does not apply, since the entire switchgear needs to be evaluated.

## □□

**CHARACTERISTIC CURVE** [eaton-circuit-breaker-nzm-mccb-characteristic-curve-012.eps](#)

[eaton-circuit-breaker-nzm-mccb-characteristic-curve-016.eps](#)

**□□□□□** [eaton-circuit-breaker-basic-unit-bg3-il012100zu.pdf](#)

[eaton-circuit-breaker-plugin-adaptor-nzm2-il01219023z.pdf](#)

[eaton-circuit-breaker-nzm-mccb-dimensions-016.eps](#)

**□□** [eaton-circuit-breaker-switch-nzm-mccb-dimensions-016.eps](#)

[eaton-circuit-breaker-nzm-mccb-dimensions-020.eps](#)

|   |  |
|---|--|
| <b>10.2.7 INSCRIPTIONS</b>                                      | Meets the product standard's requirements.   |
| <b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>                  | Does not apply, since the entire switchgear needs to be evaluated.                                   |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.   |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated.                                   |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated.                                   |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.   |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.   |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.   |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.   |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.   |
| <b>POLLUTION DEGREE</b>   | 3  |
| <b>LIFESPAN, MECHANICAL</b>                                     | 15000 operations   |
| <b>UTILIZATION CATEGORY</b>                                     | A (IEC/EN 60947-2)   |
| <b>MOUNTING METHOD</b>  | Built-in device plug-in technique<br>Plug-in unit  |
| <b>CLIMATIC PROOFING</b>  | Damp heat, constant, to IEC 60068-2-78<br>Damp heat, cyclic, to IEC 60068-2-30                       |
| <b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>            | 18.75 W  |
| <b>ISOLATION</b>  | 300 V AC (between the auxiliary contacts)<br>500 V AC (between auxiliary contacts and main contacts) |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                      | 70 °C  |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                      | -25 °C   |
| <b>AMBIENT STORAGE TEMPERATURE - MAX</b>                        | 70 °C  |
| <b>AMBIENT STORAGE</b>  | 40 °C  |

|  |   |
|--|---|
| <b>TEMPERATURE - MIN</b>                                       |   |
| <b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>     | 0   |
| <b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b> | 0   |
| <b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>   | 0   |
| <b>PROTECTION AGAINST DIRECT CONTACT</b>                       | Finger and back-of-hand proof to DIN EN 50274/VDE 0106 part 110   |
| <b>DEGREE OF PROTECTION</b>                                    | IP20<br>IP20 (basic degree of protection, in the operating controls area)   |
| <b>DIRECTION OF INCOMING SUPPLY</b>                            | As required   |
| <b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>              | Other   |
| <b>OVERVOLTAGE CATEGORY</b>                                    | III   |
| <b>DEGREE OF PROTECTION (IP), FRONT SIDE</b>                   | IP40 (with insulating surround)<br>IP66 (with door coupling rotary handle)  |
| <b>DEGREE OF PROTECTION (TERMINATIONS)</b>                     | IP00 (terminations, phase isolator and strip terminal)<br>IP10 (tunnel terminal)  |
| <b>NUMBER OF POLES</b>   | Three-pole  |
| <b>TERMINAL CAPACITY (COPPER STRIP)</b>                        | 10 segments of 50 mm x 1 mm (2x) at rear-side width extension<br>Min. 6 segments of 16 mm x 0.8 mm at rear-side connection (punched)<br>Max. 10 segments of 32 mm x 1 mm + 5 segments of 32 mm x 1 mm at rear-side connection (punched)<br><br>Min. 6 segments of 16 mm x 0.8 mm at box terminal<br>Max. 8 segments of 24 mm x 1 mm (2x) at box terminal<br>Max. 10 segments of 24 mm x 1 mm + 5 segments of 24 mm x 1 mm |
| <b>LIFESPAN, ELECTRICAL</b>                                    | 5000 operations at 415 V AC-1   |

|                  |  |
|------------------|--|
|                  | 3000 operations at 690 V AC-1<br>5000 operations at 400 V AC-1 |
| <b>FUNCTIONS</b> | Systems, cable, selectivity and generator protection           |
| <b>TYPE</b>      | Circuit breaker  |

#### **SPECIAL FEATURES**

- LSI overload protection and delayed and non-delayed short-circuit protective device
- Class 1 energy measurement, r.m.s. value measurement, and "thermal memory"
- USB interface for configuration and test function with Power Xpert Protection Manager software
- Interface module in equipment supplied.
- Optionally communication-capable with internal Modbus RTU module or CAM
- Maximum back-up fuse, if the expected short-circuit currents at the installation location exceed the switching capacity of the circuit breaker (Rated short-circuit breaking capacity  $I_{cn}$ )
- Rated current = rated uninterrupted current: 250 A
- Terminal capacity hint: Up to 240 mm<sup>2</sup> can be connected depending on the cable manufacturer.

|                    |                         |
|--------------------|-------------------------|
| <b>APPLICATION</b> | Use in unearthed supply |
|--------------------|-------------------------|

|  |   |
|--|---|
|  | systems at 690 V  |
| <b>SHOCK RESISTANCE</b>  | 20 g (half-sinusoidal shock<br>20 ms)   |
| <b>POSITION OF<br/>CONNECTION FOR MAIN<br/>CURRENT CIRCUIT</b>               | Connection at separate<br>chassis part  |
| <b>RATED OPERATIONAL<br/>CURRENT FOR SPECIFIED<br/>HEAT DISSIPATION (IN)</b> | 250 A   |
| <b>RELEASE SYSTEM</b>  | Electronic release  |
| <b>SHORT-CIRCUIT TOTAL<br/>BREAKTIME</b>                                     | < 10 ms   |
| <b>RATED SHORT-TIME<br/>WITHSTAND CURRENT (T<br/>= 0.3 S)</b>                | 3.3 kA  |
| <b>RATED SHORT-TIME<br/>WITHSTAND CURRENT (T<br/>= 1 S)</b>                  | 3.3 kA  |
| <b>SHORT-CIRCUIT RELEASE<br/>DELAYED SETTING - MAX</b>                       | 2500 A  |
| <b>SHORT-CIRCUIT RELEASE<br/>DELAYED SETTING - MIN</b>                       | 200 A   |
| <b>SHORT-CIRCUIT RELEASE<br/>NON-DELAYED SETTING -<br/>MAX</b>               | 4500 A  |
| <b>SHORT-CIRCUIT RELEASE<br/>NON-DELAYED SETTING -<br/>MIN</b>               | 500 A   |
| <b>TERMINAL CAPACITY<br/>(CONTROL CABLE)</b>                                 | 0.75 mm <sup>2</sup> - 2.5 mm <sup>2</sup> (1x)<br>0.75 mm <sup>2</sup> - 1.5 mm <sup>2</sup> (2x)  |
| <b>TERMINAL CAPACITY<br/>(COPPER BUSBAR)</b>                                 | Max. 30 mm x 10 mm + 30<br>mm x 5 mm direct at<br>switch rear-side<br>connection<br>M10 at rear-side screw<br>connection<br>Min. 20 mm x 5 mm direct<br>at switch rear-side<br>connection<br>Max. 10 mm x 50 mm (2x)<br>at rear-side width<br>extension   |
| <b>TERMINAL CAPACITY<br/>(COPPER SOLID<br/>CONDUCTOR/CABLE)</b>              | 300 mm <sup>2</sup> (2x) at rear-side<br>width extension<br>16 mm <sup>2</sup> (1x) at tunnel<br>terminal<br>16 mm <sup>2</sup> (2x) at box<br>terminal<br>16 mm <sup>2</sup> (2x) direct at<br>switch rear-side<br>connection<br>16 mm <sup>2</sup> (1x) direct at<br>switch rear-side<br>connection |

|  |  |
|--|--|
| <b>TERMINAL CAPACITY<br/>(ALUMINUM SOLID<br/>CONDUCTOR/CABLE)</b>                                  | 16 mm <sup>2</sup> (1x) at tunnel<br>terminal  |
| <b>TERMINAL CAPACITY<br/>(COPPER STRANDED<br/>CONDUCTOR/CABLE)</b>                                 | 25 mm <sup>2</sup> - 120 mm <sup>2</sup> (2x) at<br>box terminal<br>25 mm <sup>2</sup> - 240 mm <sup>2</sup> (2x)<br>direct at switch rear-side<br>connection<br>35 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) at<br>box terminal<br>16 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at<br>1-hole tunnel terminal<br>25 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x)<br>direct at switch rear-side<br>connection |
| <b>TERMINAL CAPACITY<br/>(ALUMINUM STRANDED<br/>CONDUCTOR/CABLE)</b>                               | 25 mm <sup>2</sup> - 185 mm <sup>2</sup> (1x) at<br>tunnel terminal<br>50 mm <sup>2</sup> - 240 mm <sup>2</sup> (1x) at<br>2-hole tunnel terminal<br>50 mm <sup>2</sup> - 240 mm <sup>2</sup> (2x) at<br>2-hole tunnel terminal  |
| <b>HANDLE TYPE</b>   | Rocker lever   |
| <b>SHORT DELAY CURRENT<br/>SETTING (ISD) - MAX</b>   | 10 A   |
| <b>SHORT DELAY CURRENT<br/>SETTING (ISD) - MIN</b>   | 2 A  |
| <b>INSTANTANEOUS<br/>CURRENT SETTING (II) -<br/>MAX</b>  | 18 A   |
| <b>INSTANTANEOUS<br/>CURRENT SETTING (II) -<br/>MIN</b>  | 2 A  |
| <b>NUMBER OF<br/>OPERATIONS PER HOUR -<br/>MAX</b>   | 60   |
| <b>OVERLOAD CURRENT<br/>SETTING (IR) - MAX</b>   | 250 A  |
| <b>OVERLOAD CURRENT<br/>SETTING (IR) - MIN</b>   | 100 A  |
| <b>RATED SHORT-CIRCUIT<br/>BREAKING CAPACITY ICS<br/>(IEC/EN 60947) AT 230 V,<br/>50/60 HZ</b>     | 150 kA   |
| <b>RATED SHORT-CIRCUIT<br/>BREAKING CAPACITY ICS<br/>(IEC/EN 60947) AT<br/>400/415 V, 50/60 HZ</b> | 150 kA   |
| <b>RATED SHORT-CIRCUIT<br/>BREAKING CAPACITY ICS<br/>(IEC/EN 60947) AT 440 V,<br/>50/60 HZ</b>     | 130 kA   |
| <b>RATED SHORT-CIRCUIT<br/>BREAKING CAPACITY ICS<br/>(IEC/EN 60947) AT 525 V,</b>                  | 33 kA  |

|  |  |
|--|--|
| 50/60 HZ   |  |
| RATED SHORT-CIRCUIT<br>BREAKING CAPACITY ICS<br>(IEC/EN 60947) AT 690 V,<br>50/60 HZ | 9 kA   |
| RATED SHORT-CIRCUIT<br>MAKING CAPACITY ICM<br>AT 400/415 V, 50/60 HZ                 | 330 kA   |
| RATED SHORT-CIRCUIT<br>MAKING CAPACITY ICM<br>AT 440 V, 50/60 HZ                     | 286 kA   |
| RATED SHORT-CIRCUIT<br>MAKING CAPACITY ICM<br>AT 525 V, 50/60 HZ                     | 143 kA   |
| RATED SHORT-CIRCUIT<br>MAKING CAPACITY ICM<br>AT 690 V, 50/60 HZ                     | 74 kA  |
| STANDARD TERMINALS   | Screw terminal                                       |
| OPTIONAL TERMINALS   | Box terminal. Connection<br>on rear. Tunnel terminal |
| RATED SHORT-CIRCUIT<br>MAKING CAPACITY ICM<br>AT 240 V, 50/60 HZ                     | 330 kA   |
| RATED IMPULSE<br>WITHSTAND VOLTAGE<br>(UIMP) AT AUXILIARY<br>CONTACTS                | 6000 V   |
| RATED IMPULSE<br>WITHSTAND VOLTAGE<br>(UIMP) AT MAIN<br>CONTACTS                     | 8000 V   |
| RATED INSULATION<br>VOLTAGE (UI)   | 690 V AC   |

|       |
|-------|
| □□□□: |
| □□□□: |
| □□□:  |
| □□:   |