



□□□□□

Eaton 193230

Eaton xEnergy Basic LV systems Low voltage switchgear. Surface-mounted distribution board without door, IP55, HxWxD=1260x1000x270mm

□□□□

PRODUCT NAME	Eaton xEnergy Basic empty enclosure
CATALOG NUMBER	193230
PRODUCT LENGTH/DEPTH	270 mm
PRODUCT HEIGHT	1260 mm
PRODUCT WIDTH	1000 mm
PRODUCT WEIGHT	28.5 kg
COMPLIANCES	RoHS conform

SPECIAL FEATURES	Without door
TYPE	Basic device
FEATURES	Mounting plate depth-adjustable EMC-version
SURFACE FINISHING	Powder coating
DEGREE OF PROTECTION	IP55 IK10 Other
GRADE MATERIAL	Sheet steel
MATERIAL QUALITY	Other
COLOR	Gray
PERMISSIBLE LOAD OF THE MOUNTING PLATE ACCORDING TO IEC 62208 - MAX	0 N
NUMBER OF LOCKS	0
RAL-NUMBER	7035
MATERIAL	Steel Sheet steel
MOUNTING METHOD	Surface mounting Wall fastening
FUNCTIONS	Basic device
INSTALLATION TYPE	Floor standing wall model
NUMBER OF COVERS/DOORS	0
SUITABLE FOR	Metrical mounting
PERMISSIBLE LOAD OF THE ENCLOSURE ACCORDING TO IEC 62208 - MAX	0 N
PERMISSIBLE LOAD OF THE DOOR(S) ACCORDING TO IEC 62208 - MAX	0 N
THERMAL DISSIPATION (DELTA T = 20 K) ACCORDING TO IEC/TR 60890	0 W
NUMBER OF CONNECTOR HOLES	0

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

