



## Eaton 195051

Eaton Moeller series xPole Home - HN/HN-HX MCB. Miniature circuit breaker (MCB), 16 A, 1p+N, characteristic: C, HX

□□□□

|                             |  |
|-----------------------------|--|
| <b>PRODUCT NAME</b>         | Eaton Moeller series xPole Home - HN/HN-HX MCB |
| <b>CATALOG NUMBER</b>       | 195051   |
| <b>PRODUCT LENGTH/DEPTH</b> | 85 mm  |
| <b>PRODUCT HEIGHT</b>       | 73 mm  |
| <b>PRODUCT WIDTH</b>        | 35.4 mm  |
| <b>PRODUCT WEIGHT</b>       | 0.22 kg  |
| <b>COMPLIANCES</b>          | RoHS conform                                   |



Powering Business Worldwide

|   |   |
|---|---|
| <b>USED WITH</b>  | Miniature circuit breaker<br>HN-HX  |
| <b>AMPERAGE RATING</b>  | 16 A  |
| <b>FEATURES</b>   | Additional equipment<br>possible  |
| <b>10.10 TEMPERATURE RISE</b>   | The panel builder is<br>responsible for the<br>temperature rise<br>calculation. Eaton will<br>provide heat dissipation<br>data for the devices. |
| <b>10.11 SHORT-CIRCUIT<br/>RATING</b>   | Is the panel builder's<br>responsibility. The<br>specifications for the<br>switchgear must be<br>observed.                                      |
| <b>10.12 ELECTROMAGNETIC<br/>COMPATIBILITY</b>  | Is the panel builder's<br>responsibility. The<br>specifications for the<br>switchgear must be<br>observed.                                      |
| <b>10.13 MECHANICAL<br/>FUNCTION</b>  | The device meets the<br>requirements, provided<br>the information in the<br>instruction leaflet (IL) is<br>observed.                            |
| <b>10.2.2 CORROSION<br/>RESISTANCE</b>  | Meets the product<br>standard's requirements.   |
| <b>10.2.3.1 VERIFICATION OF<br/>THERMAL STABILITY OF<br/>ENCLOSURES</b>                                 | Meets the product<br>standard's requirements.   |
| <b>10.2.3.2 VERIFICATION OF<br/>RESISTANCE OF<br/>INSULATING MATERIALS<br/>TO NORMAL HEAT</b>           | Meets the product<br>standard's requirements.   |
| <b>10.2.3.3 RESIST. OF<br/>INSUL. MAT. TO<br/>ABNORMAL HEAT/FIRE<br/>BY INTERNAL ELECT.<br/>EFFECTS</b> | Meets the product<br>standard's requirements.   |
| <b>10.2.4 RESISTANCE TO<br/>ULTRA-VIOLET (UV)<br/>RADIATION</b>   | Meets the product<br>standard's requirements.   |
| <b>10.2.5 LIFTING</b>   | Does not apply, since the<br>entire switchgear needs to<br>be evaluated.  |
| <b>10.2.6 MECHANICAL<br/>IMPACT</b>   | Does not apply, since the<br>entire switchgear needs to<br>be evaluated.  |
| <b>10.2.7 INSCRIPTIONS</b>  | Meets the product<br>standard's requirements.   |
| <b>10.3 DEGREE OF</b>   | Does not apply, since the   |

|                             |  |
|-----------------------------|--|
| <b>CHARACTERISTIC CURVE</b> | <a href="#">eaton-xpole-mmc4-6-m-<br/>mcb-characteristic-curve-<br/>004.jpg</a><br><br><a href="#">eaton-xpole-mmc4-6-m-<br/>mcb-characteristic-curve-<br/>002.jpg</a> |
| <b>PEP ECO-PASSPORT</b>     | <a href="#">eaton-non-selective-<br/>universal-mcb-pep-eato-<br/>00046-v0102-en.pdf</a>  |
| □□□□□                       | <a href="#">eaton-rccb-rcbo-g9-<br/>il019140zu.pdf</a>   |
| □□□                         | <a href="#">eaton-xpole-mmc4-6-m-<br/>mcb-wiring-diagram.jpg</a>   |
| □□□□                        | <a href="#">eaton-xPole-home-leaflet-<br/>br003019en-en-gb.pdf</a>   |
| □□□□                        | <a href="#">eaton-xpole%20home-hn-<br/>mcb-catalog-ca019020en-<br/>en-us.pdf</a>   |
| □□                          | <a href="#">eaton-xpole-hnhn-hx-mcb-<br/>3d-drawing-002.jpg</a><br><br><a href="#">eaton-xpole-pl6-mcb-<br/>dimensions.jpg</a>   |

|   |  |
|---|--|
| <b>PROTECTION OF ASSEMBLIES</b>                                 | entire switchgear needs to be evaluated.                           |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.                         |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.                             |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.                             |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.                             |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.                             |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.                             |
| <b>POLLUTION DEGREE</b>   | 3  |
| <b>DEGREE OF PROTECTION</b>                                     | IP20   |
| <b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>            | 2.6 W  |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>                   | 4 kV   |
| <b>TRIPPING CHARACTERISTIC</b>                                  | C  |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                      | 75 °C  |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                      | -25 °C   |
| <b>BUILT-IN DEPTH</b>   | 44 mm  |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX</b>  | 25 mm <sup>2</sup>   |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b>  | 1 mm <sup>2</sup>  |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX</b>   | 25 mm <sup>2</sup>   |
| <b>CONNECTABLE</b>  | 1 mm <sup>2</sup>  |

|  |  |
|--|--|
| <b>CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>                    |  |
| <b>CURRENT LIMITING CLASS</b>  | 3  |
| <b>FREQUENCY RATING - MAX</b>  | 60 Hz  |
| <b>FREQUENCY RATING - MIN</b>  | 50 Hz  |
| <b>HEAT DISSIPATION CAPACITY</b>                                     | 0 W  |
| <b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT</b>                  | 0 W  |
| <b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>                           | 2  |
| <b>VOLTAGE TYPE</b>  | AC   |
| <b>OVERVOLTAGE CATEGORY</b>  | III  |
| <b>NUMBER OF POLES</b>   | Single-pole + N  |
| <b>RELEASE CHARACTERISTIC</b>  | C  |
| <b>TYPE</b>  | <ul style="list-style-type: none"> <li>• HN-HX</li> <li>• Miniature circuit breaker</li> </ul>   |
| <b>SPECIAL FEATURES</b>  | Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity  |
| <b>APPLICATION</b>   | <ul style="list-style-type: none"> <li>• Switchgear for residential and commercial applications</li> <li>• xPole Home - Switchgear for residential applications</li> </ul> |
| <b>NUMBER OF POLES (PROTECTED)</b>                                   | 1  |
| <b>NUMBER OF POLES (TOTAL)</b>                                       | 2  |
| <b>RATED INSULATION VOLTAGE (UI)</b>                                 | 440 V  |
| <b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b> | 16 A   |
| <b>RATED OPERATIONAL VOLTAGE (UE) - MAX</b>                          | 230 V  |
| <b>RATED SHORT-CIRCUIT</b>   | 6 kA   |

