



Eaton 194584

Eaton xEnergy Safety Ci LV systems LV switchgear. NH panel enclosure 1x XNH00, MB 400A 3p, CI43

□□□□

PRODUCT NAME	Eaton xEnergy Safety Ci fuse enclosure XNH
CATALOG NUMBER	194584
PRODUCT LENGTH/DEPTH	225 mm
PRODUCT HEIGHT	375 mm
PRODUCT WIDTH	250 mm
PRODUCT WEIGHT	5.48 kg
COMPLIANCES	RoHS conform

USED WITH

Enclosures with devices fitted
Busbar housing, system 60 mm, with fuse switch disconnecter XNH
xEnergy Safety Ci

SPECIAL FEATURES

NH single housing with transparent cover 1x NH00 switchgear on busbar system 400 A
Touch protection cover included 3-pole Carrier included for N+PE for retrofitting with copper rails L1/L2/L3: 20 × 10 mm
N: without PE: without without terminals Copper rail connection optional with BBT-S60-20x10-CI
Backup device without fuses

TYPE

Busbar housing, system 60 mm, with fuse switch disconnecter XNH
Enclosures with devices fitted xEnergy Safety Ci

DEGREE OF PROTECTION

IP65
Other

CONSTRUCTION SIZE (FUSE INSERTS)

NH00

UNIT TYPE

Complete housing

HOUSING DEPTH

225 mm

HOUSING HEIGHT

375 mm

HOUSING WIDTH

250 mm

RATED INSULATION VOLTAGE (UI)

800 V

RATED OPERATING VOLTAGE (UE) AT AC - MAX

690 V

COLOR

Light gray (RAL 7035, base)
Transparent, smoky gray (cover)

CONDUCTOR TYPE

L1, L2, L3, (PE, N)

DISTANCE BETWEEN BUSBAR CENTERS

60 mm

FUNCTIONS

Enclosures with devices fitted

RATED OPERATION CURRENT (IE)

400 A

HOUSING OF

With safety switch

□□□□

[eaton-xenergy-safety-ci-subway-line-success-story-en-us.pdf](#)

□□□□

[eaton-xenergy-safety-ci-enclosure-brochure-br014001en-en-us.pdf](#)

□□

[eaton-xenergy-ci-safety-catalog-ca015006en-en-us.pdf](#)

[eaton-enclosures-xenergy-safety-ci-lv-systems-dimensions-004.eps](#)

EQUIPMENT FUSE SWITCH DISCONNECTOR	disconnecter
RATED OPERATIONAL CURRENT	130 A
NUMBER OF POLES	Three-pole

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY: