



## Eaton 194815

Eaton Moeller series xPole - HL/HL-HX MCB.  
HL, xPole Home, 3-pole+N, tripping  
characteristic: C, rated current In: 40 A, rated  
switching capacity IEC/EN 60898-1: 4,5 kA

□□□□

|                                 |                                              |
|---------------------------------|----------------------------------------------|
| <b>PRODUCT NAME</b>             | Eaton Moeller series xPole<br>- HL/HL-HX MCB |
| <b>CATALOG NUMBER</b>           | 194815                                       |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 85 mm                                        |
| <b>PRODUCT HEIGHT</b>           | 73 mm                                        |
| <b>PRODUCT WIDTH</b>            | 70 mm                                        |
| <b>PRODUCT WEIGHT</b>           | 0.456 kg                                     |
| <b>COMPLIANCES</b>              | RoHS conform                                 |



*Powering Business Worldwide*

|                                                                                         |                                                                                                                                  |
|-----------------------------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------|
| <b>USED WITH</b>                                                                        | HL<br>Miniature circuit breaker                                                                                                  |
| <b>AMPERAGE RATING</b>                                                                  | 40 A                                                                                                                             |
| <b>FEATURES</b>                                                                         | Concurrently switching N-neutral<br>Additional equipment possible                                                                |
| <b>10.10 TEMPERATURE RISE</b>                                                           | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| <b>10.11 SHORT-CIRCUIT RATING</b>                                                       | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>                                              | Is the panel builder's responsibility. The specifications for the switchgear must be observed.                                   |
| <b>10.13 MECHANICAL FUNCTION</b>                                                        | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.                         |
| <b>10.2.2 CORROSION RESISTANCE</b>                                                      | Meets the product standard's requirements.                                                                                       |
| <b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>                         | Meets the product standard's requirements.                                                                                       |
| <b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>       | Meets the product standard's requirements.                                                                                       |
| <b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b> | Meets the product standard's requirements.                                                                                       |
| <b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>                                 | Meets the product standard's requirements.                                                                                       |
| <b>10.2.5 LIFTING</b>                                                                   | Does not apply, since the entire switchgear needs to be evaluated.                                                               |
| <b>10.2.6 MECHANICAL IMPACT</b>                                                         | Does not apply, since the entire switchgear needs to be evaluated.                                                               |
| <b>10.2.7 INSCRIPTIONS</b>                                                              | Meets the product                                                                                                                |

|                             |                                                                                                                                                |
|-----------------------------|------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>CHARACTERISTIC CURVE</b> | <a href="#">eaton-xpole-mmc4-6-m-mcb-characteristic-curve-004.jpg</a><br><a href="#">eaton-xpole-mmc4-6-m-mcb-characteristic-curve-002.jpg</a> |
| <b>000</b>                  | <a href="#">eaton-xpole-mmc4-6-m-mcb-wiring-diagram-004.jpg</a>                                                                                |
| <b>0000</b>                 | <a href="#">eaton-xPole-home-leaflet-br003019en-en-gb.pdf</a>                                                                                  |
| <b>0000</b>                 | <a href="#">eaton-xpole%20home-hl-hx-mcb-catalog-ca019019en-en-us.pdf</a>                                                                      |
| <b>00</b>                   | <a href="#">eaton-xpole-pl6-mcb-dimensions.jpg</a><br><a href="#">eaton-xpole-hlhl-hx-mcb-3d-drawing-002.jpg</a>                               |

|                                                                 |                                                                    |
|-----------------------------------------------------------------|--------------------------------------------------------------------|
|                                                                 | standard's requirements.                                           |
| <b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>                  | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.                         |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.                             |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.                             |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.                             |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.                             |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.                             |
| <b>POLLUTION DEGREE</b>                                         | 3                                                                  |
| <b>DEGREE OF PROTECTION</b>                                     | IP20                                                               |
| <b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT</b>            | 11.5 W                                                             |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>                   | 4 kV                                                               |
| <b>TRIPPING CHARACTERISTIC</b>                                  | C                                                                  |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                      | 75 °C                                                              |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                      | -25 °C                                                             |
| <b>BUILT-IN DEPTH</b>                                           | 44 mm                                                              |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX</b>  | 25 mm <sup>2</sup>                                                 |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN</b>  | 1 mm <sup>2</sup>                                                  |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) -</b>       | 25 mm <sup>2</sup>                                                 |

|                                                                      |                                                                                                                                                                            |
|----------------------------------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>MAX</b>                                                           |                                                                                                                                                                            |
| <b>CONNECTABLE CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN</b>        | 1 mm <sup>2</sup>                                                                                                                                                          |
| <b>CURRENT LIMITING CLASS</b>                                        | 3                                                                                                                                                                          |
| <b>FREQUENCY RATING - MAX</b>                                        | 60 Hz                                                                                                                                                                      |
| <b>FREQUENCY RATING - MIN</b>                                        | 50 Hz                                                                                                                                                                      |
| <b>HEAT DISSIPATION CAPACITY</b>                                     | 0 W                                                                                                                                                                        |
| <b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT</b>                  | 0 W                                                                                                                                                                        |
| <b>WIDTH IN NUMBER OF MODULAR SPACINGS</b>                           | 4                                                                                                                                                                          |
| <b>VOLTAGE TYPE</b>                                                  | AC                                                                                                                                                                         |
| <b>OVERVOLTAGE CATEGORY</b>                                          | III                                                                                                                                                                        |
| <b>NUMBER OF POLES</b>                                               | Three-pole + N                                                                                                                                                             |
| <b>RELEASE CHARACTERISTIC</b>                                        | C                                                                                                                                                                          |
| <b>TYPE</b>                                                          | <ul style="list-style-type: none"> <li>• HL</li> <li>• Miniature circuit breaker</li> </ul>                                                                                |
| <b>SPECIAL FEATURES</b>                                              | Ambient temperature hint: a 1 °C increase results in a 0.5% linear reduction of current carrying capacity                                                                  |
| <b>APPLICATION</b>                                                   | <ul style="list-style-type: none"> <li>• Switchgear for residential and commercial applications</li> <li>• xPole Home - Switchgear for residential applications</li> </ul> |
| <b>NUMBER OF POLES (PROTECTED)</b>                                   | 3                                                                                                                                                                          |
| <b>NUMBER OF POLES (TOTAL)</b>                                       | 4                                                                                                                                                                          |
| <b>RATED INSULATION VOLTAGE (UI)</b>                                 | 440 V                                                                                                                                                                      |
| <b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b> | 40 A                                                                                                                                                                       |
| <b>RATED OPERATIONAL</b>                                             | 230 V                                                                                                                                                                      |

|                                                                                |                            |
|--------------------------------------------------------------------------------|----------------------------|
| VOLTAGE (UE) - MAX                                                             |                            |
| RATED SHORT-CIRCUIT<br>BREAKING CAPACITY<br>(IEC/EN 60898-1) - ICN AT<br>230 V | 4.5 kA                     |
| RATED SHORT-CIRCUIT<br>BREAKING CAPACITY<br>(IEC/EN 60898-1)- ICN AT<br>400 V  | 4.5 kA                     |
| RATED SHORT-CIRCUIT<br>BREAKING CAPACITY (IEC<br>60947-2)- ICU AT 230 V        | 0 kA                       |
| RATED SHORT-CIRCUIT<br>BREAKING CAPACITY (IEC<br>60947-2)- ICU AT 400 V        | 0 kA                       |
| RATED SWITCHING<br>CAPACITY (IEC/EN 60898-<br>1)                               | 4.5 kA                     |
| STATIC HEAT<br>DISSIPATION, NON-<br>CURRENT-DEPENDENT                          | 0 W                        |
| SUITABLE FOR                                                                   | Flush-mounted installation |
| POWER LOSS                                                                     | 11.5 W                     |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
|                 |