

Eaton 197496

Eaton DA1 Frequency inverter, 400 V AC, 3-phase, 61 A, 30 kW, IP20/NEMA 0, Radio interference suppression filter, Additional PCB protection, DC link choke, FS5

PRODUCT NAME	Eaton DA1 Variable frequency drive
CATALOG NUMBER	197496
PRODUCT LENGTH/DEPTH	261 mm
PRODUCT HEIGHT	485 mm
PRODUCT WIDTH	234 mm
PRODUCT WEIGHT	18.2 kg
CERTIFICATIONS	CE RoHS, ISO 9001 UL UL 508C UL File No.: E172143 UL report applies to both US and Canada IEC/EN61800-3 RCM Safety: EN 61800-5-1: 2003
	UkrSEPRO IEC/EN 61800-3 IEC/EN 61800-2 UL Category Control No.: NMMS, NMMS7 Certified by UL for use in Canada CUL EAC IEC/EN61800-5
CATALOG NOTES	The brake resistors are assigned based on the maximum rated power of the variable frequency drive. Additional brake resistors and designs (e.g. different duty cycles) are available upon request.

PRODUCT CATEGORY	Variable frequency drives
FEATURES	Parameterization: Fieldbus
	Parameterization: Keypad
	Parameterization: drivesConnect
	Parameterization: drivesConnect mobile (App)
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.

INSTALLATION VIDEOS	Video PowerXL DA1
	eaton-da1-variable-frequency-drive-il040049zu.pdf
	eaton-powerxl-variable-frequency-drives-dc1-da1-brochure-br040001en-en-us.pdf
	eaton-powerxl-da1-application-manual-mn04020006z-en-us.pdf
	eaton-powerxl-da1-installation-manual-mn04020005z-en-us.pdf
	eaton-frequency-inverter-dimensions-013.eps

10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	DC link choke Additional PCB protection Radio interference suppression filter Internal DC link PC connection Control unit Brake chopper Breaking resistance IGBT inverter OLED display
CLIMATIC PROOFING	< 95 average relative humidity (RH), no condensation, no corrosion
CONNECTION TO SMARTWIRE-DT	In conjunction with DX-NET-SWD1 SmartWire DT module Yes
OPERATING MODE	U/f control Speed control with slip compensation

	Optional: Vector control with feedback (CLV) Sensorless vector control (SLV)
FRAME SIZE	FS5
ALTITUDE	Max. 4000 m Max. 1000 m Above 1000 m with 1 % derating per 100 m
ENVIRONMENTAL CLASS	3C2, 3S2 (Air quality)
APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED	Yes
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 30 seconds
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MAX	50 °C
AMBIENT OPERATING TEMPERATURE AT 150% OVERLOAD - MIN	-10 °C
AMBIENT STORAGE TEMPERATURE - MAX	60 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
APPARENT POWER AT 400 V	42.26 kVA
APPARENT POWER AT 480 V	50.71 kVA
ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 150% OVERLOAD	61 A
MOUNTING POSITION	Vertical
RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
PROTECTION	Finger and back-of-hand proof, Protection against

	direct contact (BGV A3, VBG4)
RESOLUTION	0.1 Hz (Frequency resolution, setpoint value)
SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR	780 VDC
VOLTAGE RATING - MAX	480 VAC
COMMUNICATION INTERFACE	CANopen® Ethernet IP, optional DeviceNet, optional PROFINET, optional Modbus RTU EtherCAT, optional PROFIBUS, optional SmartWire-DT, optional OP-Bus (RS485) Modbus-TCP, optional
CONVERTER TYPE	U converter
DEGREE OF PROTECTION	IP20 NEMA Other
PROTOCOL	PROFIBUS DeviceNet CAN TCP/IP MODBUS Other bus systems PROFINET IO EtherNet/IP
ASSIGNED MOTOR CURRENT IM AT 440 - 480 V, 60 HZ, 150% OVERLOAD	52 A
SYSTEM CONFIGURATION TYPE	AC supply systems with earthed center point
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	40 HP
BRAKING RESISTANCE	12 Ω
INPUT CURRENT ILN AT 150% OVERLOAD	63.8 A
BRAKING TORQUE	Max. 30 % MN, Standard - Main circuit Adjustable to 100 % (DC) Max. 100 % of rated operational current Ie with external braking resistor - Main circuit

CABLE LENGTH	<p>C3 ≤ 25 m, maximum motor cable length 200 m, screened, with motor choke, maximum permissible cable length 150 m, unscreened, maximum permissible cable length</p> <p>C2 ≤ 5 m, maximum motor cable length 100 m, screened, maximum permissible cable length 200 m, unscreened, with motor choke, maximum permissible cable length</p>
FUNCTIONS	4-quadrant operation possible
OUTPUT VOLTAGE (U2)	400 V AC, 3-phase 480 V AC, 3-phase
NUMBER OF INPUTS (ANALOG)	2
NUMBER OF INPUTS (DIGITAL)	5
RADIO INTERFERENCE CLASS	<p>Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments</p> <p>C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary.</p>
NUMBER OF OUTPUTS (DIGITAL)	2
STARTING CURRENT - MAX	200 %, IH, max. starting current (High Overload), for 4 seconds every 40 seconds, Power section
NUMBER OF PHASES (INPUT)	3
NUMBER OF RELAY OUTPUTS	2 (parameterizable, 1 N/O and 1 changeover contact, 6 A (250 V, AC-1) / 5 A (30 V, DC-1))
NUMBER OF PHASES (OUTPUT)	3

POWER CONSUMPTION	840 W
RATED CONTROL SUPPLY VOLTAGE	10 V DC (Us, max. 10 mA)
EFFICIENCY	97.4 % (η)
RATED CONTROL VOLTAGE (UC)	24 V DC (external, max. 100 mA)
SUPPLY FREQUENCY	50/60 Hz
LEAKAGE CURRENT AT GROUND IPE - MAX	0.49 mA
MAINS VOLTAGE - MAX	480 V
MAINS VOLTAGE - MIN	380 V
NOMINAL OUTPUT CURRENT I2N	61 A
NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)	0
NUMBER OF HW-INTERFACES (OTHER)	0
NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF OUTPUTS (ANALOG)	2
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	30 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	30 kW
OUTPUT FREQUENCY - MAX	500 Hz
OUTPUT FREQUENCY - MIN	0 Hz
OUTPUT VOLTAGE - MAX	500 V
OVERLOAD CURRENT IL AT 150% OVERLOAD	91.5 A

SUITABLE FOR	Branch circuits, (UL/CSA)
SWITCHING FREQUENCY	8 kHz, 4 - 24 kHz adjustable (audible), fPWM, Power section, Main circuit
RATED OPERATIONAL VOLTAGE	480 V AC, 3-phase 400 V AC, 3-phase
SHORT-CIRCUIT PROTECTION RATING	80 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
RATED FREQUENCY - MAX	62 Hz
RATED FREQUENCY - MIN	48 Hz
RATED OPERATIONAL CURRENT (IE) AT 150% OVERLOAD	61 A
RATED OPERATIONAL POWER AT 380/400 V, 50 HZ, 3-PHASE	30 kW
SAFETY FUNCTION/LEVEL	STO (Safe Torque Off, SIL2, PLc Cat 2)
HEAT DISSIPATION AT CURRENT/SPEED	330 W at 25% current and 0% speed 330 W at 25% current and 50% speed 330 W at 50% current and 0% speed 360 W at 50% current and 50% speed 390 W at 50% current and 90% speed 550 W at 100% current and 0% speed 670 W at 100% current and 50% speed 790 W at 100% current and 90% speed

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

