

Eaton 197666

Eaton XV-363 Single touch display, 12-inch display, 24 VDC, IR, 800 x 600 pixels, 2x Ethernet, 1x RS232, 1x RS485, 1x CAN, PLC function can be fitted by user

PRODUCT NAME	Eaton XV-363 Touch panel
CATALOG NUMBER	197666
PRODUCT LENGTH/DEPTH	361 mm
PRODUCT HEIGHT	100 mm
PRODUCT WIDTH	279 mm
PRODUCT WEIGHT	2.2 kg
CERTIFICATIONS	EAC EN 50178 IEC/EN 61131-2
CATALOG NOTES	Current consumption at 24 V DC

TYPE	HMI (SPS function, retrofittable)
FEATURES	Portrait format RS232 CAN RS485 Ethernet interface PLC function can be fitted by user USB Host Fanless CPU and system cooling, natural convection-based passive cooling USB device Slot for SD card
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to

MCAD MODEL	xv_363_12_c00_a00_1b.stp xv_363_12_c00_a00_1b.dwg eaton-electronics-dimensions-xv-touch-panel-dimensions.eps eaton-operator-panels-dimensions-xv-touch-panel-dimensions-006.eps eaton-electronics-dimensions-xv-touch-panel-dimensions-002.eps eaton-operator-panels-xv-touch-panel-dimensions-005.eps eaton-operator-panels-xv-touch-panel-3d-drawing-003.eps

	be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Meets the product standard's requirements.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	<p>Message system (incl. buffer and confirmation)</p> <p>Recipes</p> <p>1 x USB device (built-in interface)</p> <p>2 x Ethernet 10/100 Mbps (built-in interface)</p> <p>Alpha numeric keyboard</p> <p>1 x USB host 2.0 (built-in interface)</p> <p>1 x RS232 (built-in interface)</p> <p>Message indication</p> <p>1 x RS485 (built-in interface)</p> <p>Color display</p> <p>1 x CAN (built-in interfaces)</p> <p>Numeric keyboard</p>
FUSE TYPE	Built-in fuse (not accessible)

CLIMATIC PROOFING	Cold to EN 60068-2-1 Dry heat to IEC 60068-2-2 Damp heat, constant, to IEC 60068-2-3
SUPPLY VOLTAGE AT AC, 50 HZ - MAX	0 VAC
SUPPLY VOLTAGE AT AC, 50 HZ - MIN	0 VAC
SUPPLY VOLTAGE AT AC, 60 HZ - MAX	0 VAC
SUPPLY VOLTAGE AT AC, 60 HZ - MIN	0 VAC
SUPPLY VOLTAGE AT DC - MAX	30 VDC
SUPPLY VOLTAGE AT DC - MIN	19.2 VDC
WIDTH OF THE FRONT	361.2 mm
PRODUCT CATEGORY	XV-300
RESOLUTION	800 x 600 px
AIR PRESSURE	795 - 1080 hPa (operation)
DISPLAY SIZE	246 x 185 mm 4:3
ENVIRONMENTAL CONDITIONS	Condensation: Non-condensing
BACKUP TIME	10 years, typ. (time at zero voltage)
MEMORY CAPACITY	512,000 kByte
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	0 °C
AMBIENT STORAGE TEMPERATURE - MAX	60 °C
AMBIENT STORAGE TEMPERATURE - MIN	-20 °C
BUILT-IN DEPTH	63 mm
FRONT HEIGHT	279.2 mm
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
NUMBER OF BUTTONS (PROGRAMMABLE FUNCTION)	0
NUMBER OF BUTTONS WITH LED	0

NUMBER OF GREY- SCALES/BLUE-SCALES OF DISPLAY	0
NUMBER OF HW- INTERFACES (INDUSTRIAL ETHERNET)	2
NUMBER OF HW- INTERFACES (OTHER)	2
BATTERY RUNTIME	Back-up of real-time clock: BR 2330, non-replaceable (soldered)
VOLTAGE TYPE	DC
OPERATING SYSTEM	Windows Embedded Compact 7 Pro
SOFTWARE	XSOFT-CODESYS, Visualization software, Engineering GALILEO, Visualization software, Engineering XSOFT-CODESYS-2, PLC- Programming software, Engineering XSOFT-CODESYS-3, PLC- Programming software, Engineering
MOUNTING METHOD	Flush mounting - Clearance: Width x Height x Depth ≥ 30 mm (1.18") Flush mounting
DISPLAY CONTRAST RATIO	500:1
NUMBER OF SLOTS	1 (for SD-Card)
INTERFERENCE IMMUNITY	According to EN 61000-6-2
DISPLAY TYPE	Laminated safety glass, anti-glare in aluminum frame TFT Color display, TFT
RADIO INTERFERENCE CLASS	Class A (EN 55011)
RELATIVE HUMIDITY	10 - 95 % (non- condensing)
DEGREE OF PROTECTION	IP20, rear (according to EN 60529-1)
DEGREE OF PROTECTION (FRONT SIDE)	IP65 NEMA 12
NUMBER OF COLORS OF THE DISPLAY	65536
PROCESSOR	ARM Cortex-A9 800 MHz

ROHS CONFORMITY	Yes
MEMORY	NVRAM: 128kByte Retain Flash: 1 GByte SLC DRAM: 512 MByte RAM SD card, Type: SDSC, SDHC (external memory)
FUNCTIONS	Process value representation (output) possible Additional software components, loadable Process default value (input) possible
TOUCH TECHNOLOGY	Infrared touch Single-touch display Laminated safety glass, non-reflective, Infrared touch protective screen
MODEL	Metal enclosure and glass front in aluminum frame
INTERFACES	USB 2.0 device (not galvanically isolated) 10/100 Mbps Ethernet connection USB 2.0 host (not galvanically isolated) CAN (not galvanically isolated, 9-pin SUB-D plug, UNC) RS232 (not galvanically isolated, 9-pin SUB-D plug, UNC) RS485 (not galvanically isolated, 9-pin SUB-D plug, UNC)
VOLTAGE DIPS	≤ 10 ms from rated voltage (24 V DC) 5 ms from undervoltage (19.2 V DC)
NUMBER OF HW- INTERFACES (PARALLEL)	0
NUMBER OF HW- INTERFACES (RS-232)	1
NUMBER OF HW- INTERFACES (RS-422)	0
NUMBER OF HW- INTERFACES (RS-485)	1
NUMBER OF HW- INTERFACES (SERIAL TTY)	0
NUMBER OF HW- INTERFACES (USB)	2

NUMBER OF HW-INTERFACES (WIRELESS)	0
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF ONLINE/RUNTIME LANGUAGES	100
NUMBER OF PASSWORD LEVELS	200
NUMBER OF PIXELS (HORIZONTAL)	800
NUMBER OF PIXELS (VERTICAL)	600
NUMBER OF SYSTEM BUTTONS	1
OPERATING TEMPERATURE - MAX	50 °C
OPERATING TEMPERATURE - MIN	0 °C
SCREEN SIZE (DIAGONAL)	12.1 in
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	20.5 W
PERMISSIBLE VOLTAGE	<p>19.2 - 30 V DC, effective (rated operating voltage - 20 %/+25 %)</p> <p>18 - 31.2 V DC, battery powered (rated operating voltage -25 %/+30 %)</p> <p>35 V DC (for a duration of < 100 ms)</p> <p>19.2 - 30 V DC, absolute with ripple</p>
POWER CONSUMPTION	<p>Max 20.5 W</p> <p>18 W</p>
PROTOCOL	<p>Other bus systems</p> <p>MODBUS</p> <p>PROFIBUS</p> <p>TCP/IP</p> <p>EtherNet/IP</p> <p>CAN</p> <p>EtherCAT</p>
RATED OPERATIONAL VOLTAGE	24 V DC (power-supply - safety extra low voltage)
SHOCK RESISTANCE	15 g, 11 ms, Mechanical

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

