



□□□□

Eaton 197767

Eaton Moeller series E57G General purpose series, Proximity switch, 10 - 30 V DC, d=30 mm, 1 N/O, 3-wire, 2 m connection cable, Sn= 15 mm, Non-flush mounting, PNP, Stainless steel

□□□□

| | |
|-----------------------------|--|
| PRODUCT NAME | Eaton Moeller® series E57G Proximity switch |
| CATALOG NUMBER | 197767 |
| PRODUCT LENGTH/DEPTH | 67.7 mm |
| PRODUCT HEIGHT | 30 mm |
| PRODUCT WIDTH | 30 mm |
| PRODUCT WEIGHT | 0.177 kg |
| CERTIFICATIONS | CSA-C22.2 No. 14 UL 508 UL Listed UL File No.: E166051 IEC/EN 60947-5-2 Certified by UL for use in Canada UL Category Control No.: NRKH, NRKH7 |



Powering Business Worldwide



| | |
|---|--------------------------------|
| TYPE | Inductive sensor |
| ELECTRIC CONNECTION TYPE | Cable |
| ENCLOSURE MATERIAL FINISHING | Other |
| ACTUATION TYPE | Metallic Target |
| ENCLOSURE MATERIAL | Metal |
| ENCLOSURE TYPE | Cylinder, screw-thread |
| CATEGORY (EN 954-1) | B |
| EXPLOSION SAFETY CATEGORY FOR DUST | None |
| EXPLOSION SAFETY CATEGORY FOR GAS | None |
| SAFETY PERFORMANCE LEVEL (EN ISO 13849-1) | None |
| SIL (IEC 61508) | None |
| AMBIENT OPERATING TEMPERATURE - MAX | 70 °C |
| AMBIENT OPERATING TEMPERATURE - MIN | -25 °C |
| DIAMETER SENSOR | 30 mm |
| NUMBER OF CONTACT ENERGIZED OUTPUTS WITH SIGNALLING FUNCTION | 0 |
| NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS) | 1 |
| NUMBER OF OUTPUTS (PROTECTED CONTACT ENERGIZED) | 0 |
| NUMBER OF OUTPUTS (PROTECTED SEMICONDUCTOR) | 0 |
| NUMBER OF OUTPUTS (SEMICONDUCTOR WITH SIGNALING FUNCTION) | 1 |
| OPERATIONAL CURRENT (IB) IN THE SWITCHED STATE AT 24 V DC | 10 A |
| FUNCTIONS | Short-circuit protection |
| VOLTAGE TYPE | DC |
| MOUNTING METHOD | Non-flush mounting |
| MATERIAL | Stainless steel |
| CONNECTION TYPE | 3-wire 2 m connection cable |
| INSTALLATION TYPE | Not flat |



