



□□□□□

Eaton 195316

Eaton xEnergy Basic LV systems Low voltage switchgear. IP55 Surface-mounted installation distributor, EP, WxHxD=350x860x270mm, gray, rotary lever

□□□□

PRODUCT NAME	Eaton xEnergy Basic empty enclosure
CATALOG NUMBER	195316
PRODUCT LENGTH/DEPTH	270 mm
PRODUCT HEIGHT	860 mm
PRODUCT WIDTH	350 mm
PRODUCT WEIGHT	21.5 kg
COMPLIANCES	RoHS conform

TYPE	Basic device
FEATURES	EMC-version Connectable Mounting plate depth-adjustable
FITTED WITH:	Door
SURFACE FINISHING	Powder coating
DEGREE OF PROTECTION	IP55 IK10 Other
MATERIAL QUALITY	Other
COLOR	Gray
PERMISSIBLE LOAD OF THE MOUNTING PLATE ACCORDING TO IEC 62208 - MAX	0 N
NUMBER OF LOCKS	0
RAL-NUMBER	7035
MATERIAL	Steel
MOUNTING METHOD	Wall fastening
FUNCTIONS	Basic device
INSTALLATION TYPE	Floor standing wall model
NUMBER OF COVERS/DOORS	1
SUITABLE FOR	Metrical mounting
PERMISSIBLE LOAD OF THE ENCLOSURE ACCORDING TO IEC 62208 - MAX	0 N
PERMISSIBLE LOAD OF THE DOOR(S) ACCORDING TO IEC 62208 - MAX	0 N
THERMAL DISSIPATION (DELTA T = 20 K) ACCORDING TO IEC/TR 60890	0 W
NUMBER OF CONNECTOR HOLES	0

