

Eaton 197219

Eaton Moeller® series EASY I/O expansion,
For use with easyE4, 24 V DC, Inputs
expansion (number) digital: 4, screw
terminal

PRODUCT NAME	Eaton Moeller® series EASY I/O expansion
CATALOG NUMBER	197219
PRODUCT LENGTH/DEPTH	58 mm
PRODUCT HEIGHT	90 mm
PRODUCT WIDTH	36 mm
PRODUCT WEIGHT	0.1 kg
CERTIFICATIONS	CSA-C22.2 No. 61010 IEC/EN 61000-6-3 IEC 60068-2-27 IEC 60068-2-30 IEC 60068-2-6 EN 50178 IEC/EN 61000-4-2 IEC/EN 61000-6-2 IEC/EN 61131-2 CULus per UL 61010 EN 61010 UL Listed UL Category Control No.: NRAQ, NRAQ7 UL File No.: E205091 DNV GL CE UL hazardous location class I UL hazardous location division 2 UL hazardous location group A (acetylene) UL hazardous location group B (hydrogen) UL hazardous location group C (ethylene) UL hazardous location group D (propane) UL hazardous location

class I
UL hazardous location
division 2
UL hazardous location
group A (acetylene)
UL hazardous location
group B (hydrogen)
UL hazardous location
group C (ethylene)
UL hazardous location
group D (propane)

TYPE	easyE4 extension
FEATURES	Expandable Expansion device Parallel connection of transistor outputs with resistive load, inductive load with external suppressor circuit, combination within a group - Group 1: Q1 to Q4
AIR DISCHARGE	8 kV
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.

DECLARATIONS OF CONFORMITY	eaton-i-o-expansion-declaration-of-conformity-uk251130en.pdf
INSTALLATION VIDEOS	Video easy E4 control relay
	eaton-modular-plc-easy-i-o-expansion-dimensions.eps
	eaton-modular-plc-easy-i-o-expansion-3d-drawing-002.eps
	eaton-general-easy-control-relays-symbol-002.tif

10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Meets the product standard's requirements.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FREQUENCY RATING	6.5 Hz
OPERATING FREQUENCY	Dependent on the cycle- and transmission-time of the expansion devices Depending on the suppressor circuit (Inductive load to EN 60947-5-1, With external suppressor circuit, Max. switching frequency, max. duty factor) Dependent on the cycle time of the basic device
POLLUTION DEGREE	2
BURST IMPULSE	2 kV, Signal cable 2 kV, Supply cable According to IEC/EN 61000-4-4
AIR PRESSURE	795 - 1080 hPa (operation)
CATEGORY (EN 954-1)	None
EXPLOSION SAFETY CATEGORY FOR DUST	None
ENVIRONMENTAL CONDITIONS	Clearance in air and creepage distances

	<p>according to EN 50178, EN 61010-2-201, UL61010-2-201, CSA-C22.2 NO. 61010-2-201</p> <p>Condensation: prevent with appropriate measures</p>
INDICATION	<p>LCD-display base unit used as Output status indication of Transistor outputs</p> <p>LCD-display base unit used as status indication of Digital inputs 24 V DC</p>
OUTPUT VOLTAGE	<p>$U = U_e - 1 \text{ V}$ (signal 1 at $I_e = 0.5 \text{ A}$, transistor outputs)</p> <p>Max. 2.5 V (at status 0 per channel, transistor outputs)</p>
EXPLOSION SAFETY CATEGORY FOR GAS	None
MOUNTING METHOD	<p>Rail mounting possible</p> <p>Top-hat rail fixing (according to IEC/EN 60715, 35 mm)</p> <p>Wall mounting/direct mounting</p> <p>Screw fixing using fixing brackets ZB4-101-GF1 (accessories)</p> <p>Front build in possible</p>
SCREWDRIVER SIZE	3.5 x 0.8 mm, Terminal screw
VOLTAGE TYPE	DC
MOUNTING POSITION	<p>Horizontal</p> <p>Vertical</p>
OUTPUT	<p>2 A, Max. total current, Outputs</p> <p>4 Transistor Outputs</p> <p>Parallel connection of max. 4 Transistor outputs</p> <p>Voltage</p> <p>Current</p>
CONTACT DISCHARGE	6 kV
BASE TYPE	No
SAFETY PERFORMANCE LEVEL (EN ISO 13849-1)	None
SIL (IEC 61508)	None
AMBIENT OPERATING TEMPERATURE - MAX	55 °C
AMBIENT OPERATING	-25 °C

TEMPERATURE - MIN	
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
CONVENTIONAL THERMAL CURRENT ITH OF AUXILIARY CONTACTS (1-POLE, OPEN)	0.5 A
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
HEIGHT OF FALL (IEC/EN 60068-2-32) - MAX	0.3 m
NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)	0
NUMBER OF HW-INTERFACES (OTHER)	0
NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	0
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF HW-INTERFACES (WIRELESS)	0
OVERVOLTAGE CATEGORY	III
DUTY FACTOR	100 % (Inductive load to EN 60947-5-1, Without external suppressor circuit, DC-13, T0.95 = 72 ms, R = 48 Ω, L = 1.15 H) 100 % (Inductive load to EN 60947-5-1, With external suppressor circuit)

	100 % (Inductive load to EN 60947-5-1, Without external suppressor circuit, T0.95 = 15 ms, R = 48 Ω , L = 0.24 H)
SOFTWARE	EASYSOFT-SWLIC/easySoft
SURGE RATING	1 kV, Supply cables, asymmetrical, power pulses (Surge), EMC 0.5 kV, Supply cables, symmetrical, power pulses (Surge), EMC According to IEC/EN 61000-4-5, power pulses (Surge), EMC
CABLE LENGTH	100 m, unscreened, Digital inputs 24 V DC
ELECTROMAGNETIC FIELDS	10 V/m at 0.8 - 1.0 GHz (according to IEC EN 61000-4-3) 3 V/m at 1.4 - 2 GHz (according to IEC EN 61000-4-3) 1 V/m at 2.0 - 2.7 GHz (according to IEC EN 61000-4-3)
PROTECTION AGAINST POLARITY REVERSAL	Yes, for supply voltage (Siemens MPI optional) For transistor outputs (Caution: A short circuit will result if 0 V/earth is applied to the outputs in the event that the supply voltage is connected to the wrong poles)
NUMBER OF INPUTS (ANALOG)	0
CONNECTION TYPE	Screw terminal
DROP AND TOPPLE	50 mm Drop height, Drop to IEC/EN 60068-2-31
IMMUNITY TO LINE-CONDUCTED INTERFERENCE	10 V (according to IEC/EN 61000-4-6)
RADIO INTERFERENCE CLASS	Class B (EN 61000-6-3)
NUMBER OF OUTPUTS (DIGITAL)	4
RELATIVE HUMIDITY	5 - 95 % (IEC 60068-2-30, IEC 60068-2-78)
DEGREE OF PROTECTION	IP20
DELAY TIME	0.2 ms typ., Digital inputs

	<p>24 V DC (I1 - I4), Delay time from 1 to 0, Debounce OFF</p> <p>0.015 ms typ., Digital inputs 12 V DC (I1 - I8), Delay time from 1 to 0, Debounce OFF</p> <p>0.015 ms typ., Digital inputs 12 V DC (I1 - I8), Delay time from 0 to 1, Debounce OFF</p> <p>20 ms, Digital Inputs 12 V DC, Delay time from 0 to 1, Debounce ON</p> <p>20 ms, Digital Inputs 12 V DC, Delay time from 1 to 0, Debounce ON</p> <p>0.1 ms typ., Digital inputs 24 V DC (I1 - I4), Delay time from 0 to 1, Debounce OFF</p>
RESIDUAL CURRENT	0.1 mA (on signal "1" per channel)
PROTOCOL	MODBUS TCP/IP
RESIDUAL RIPPLE	<p>≤ 5 %</p> <p>5 % (transistor outputs)</p>
RATED OPERATIONAL CURRENT (IE)	Max. 0.5 A at signal „1“ DC per channel
INRUSH CURRENT	12.5 A (for 6 ms)
INSULATION RESISTANCE	According to EN 50178, EN 61010-2-201, UL61010-2-201, CSA-C22.2 NO. 61010-2-201
HEAT DISSIPATION	3.4 W (at 24 V DC)
FUNCTIONS	Thermal cutout
SHORT-CIRCUIT CURRENT	6.8 A, Transistor outputs
VIBRATION RESISTANCE	<p>57 - 150 Hz, 2 g constant acceleration</p> <p>According to IEC/EN 60068-2-6</p> <p>10 - 57 Hz, 0.15 mm constant amplitude</p>
INPUT CURRENT	40 mA
SHOCK RESISTANCE	15 g, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 11 ms, 18 Impacts
INPUT VOLTAGE	<p>Signal 0: ≤ 5 V DC (I1 - I4, Digital inputs, 24 V DC)</p> <p>Signal 1: ≥ 15 V DC (I1 - I4,</p>

	Digital inputs, 24 V DC)
SHORT-CIRCUIT TRIPPING CURRENT	$0.7 \leq I_e \leq 1.7$ per output, For $R_a \leq 10 \text{ m}\Omega$, Depending on number of active channels and their load, Transistor outputs
LAMP LOAD	Max. 3 W (without R_v per channel)
SUPPLY CURRENT	18/32 mA, Normally/max., On 0 signal, Transistor outputs 24/44 mA, Normally/max., On 1 signal, Transistor outputs
UTILIZATION FACTOR	0.25 (Inductive load to EN 60947-5-1, Without external suppressor circuit, $T_{0.95} = 15 \text{ ms}$, $R = 48 \text{ }\Omega$, $L = 0.24 \text{ H}$) 1 (Inductive load to EN 60947-5-1, With external suppressor circuit) 0.25 (Inductive load to EN 60947-5-1, Without external suppressor circuit, DC-13, $T_{0.95} = 72 \text{ ms}$, $R = 48 \text{ }\Omega$, $L = 1.15 \text{ H}$)
POTENTIAL ISOLATION	Between Digital inputs 24 V DC and expansion devices: yes Between Transistor outputs: no Between Digital inputs 24 V DC: no Between Digital inputs 24 V DC and Power supply: no Between Digital inputs 24 V DC and Outputs: no Between Transistor outputs and expansion devices: yes Between Transistor outputs and Power supply: no
NUMBER OF INPUTS (DIGITAL)	4
VOLTAGE DIPS	20 ms $\leq 10 \text{ ms}$, Bridging voltage dips
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF OUTPUTS	0

(ANALOG)	
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	1 W
SUPPLY VOLTAGE AT AC, 50 HZ - MAX	0 VAC
SUPPLY VOLTAGE AT AC, 50 HZ - MIN	0 VAC
SUPPLY VOLTAGE AT AC, 60 HZ - MAX	0 VAC
SUPPLY VOLTAGE AT AC, 60 HZ - MIN	0 VAC
SUPPLY VOLTAGE AT DC - MAX	28.8 VDC
SUPPLY VOLTAGE AT DC - MIN	20.4 VDC
SWITCHING CURRENT	0.5 A
PRODUCT CATEGORY	Control relays easyE4
POWER CONSUMPTION	1 W
RATED OPERATIONAL VOLTAGE	20.4 - 28.8 V DC 20.4 - 28.8 V DC (Transistor outputs) 24 V DC (-15 %/+ 20 % - power supply) 24 V DC (transistor outputs) 24 V DC (digital inputs)
SHORT-CIRCUIT PROTECTION	Yes, electronic (Q1 - Q4), Transistor outputs ≥ 1A (T), Fuse, Power supply
TERMINAL CAPACITY	0.2 - 4 mm ² (AWG 22 - 12), solid 0.2 - 2.5 mm ² (22 - 12 AWG), flexible with ferrule
TIGHTENING TORQUE	0.6 Nm, Screw terminals

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

