



□□□□

Eaton 198885

Eaton Moeller® series Rapid Link - Speed controllers, 4.3 A, 1.5 kW, Sensor input 4, Actuator output 2, 180/207 V DC, Ethernet IP, HAN Q4/2, with manual override switch

□□□□

| | |
|-----------------------------|-----------------------------------|
| PRODUCT NAME | Eaton Rapid Link Speed controller |
| CATALOG NUMBER | 198885 |
| PRODUCT LENGTH/DEPTH | 157 mm |
| PRODUCT HEIGHT | 270 mm |
| PRODUCT WIDTH | 220 mm |
| PRODUCT WEIGHT | 3.59 kg |

| | |
|-----------------------|---|
| CERTIFICATIONS | RoHS IEC/EN 61800-5-1 UL approval CE UL 61800-5-1 |
|-----------------------|---|

CATALOG NOTES

- 3 fixed speeds and 1 potentiometer speed
- can be switched over from U/f to (vector) speed control
- Connection of supply voltage via adapter cable on round or flexible busbar junction
- Diagnostics and reset on the device and via Ethernet IP
- integrated PTC thermistor monitoring and Thermoclick with safe isolation
- optional: 4 sensor inputs with M12-Y adapter for switchover to creep speed
- optional: Faster



Powering Business Worldwide

stop if external 24
V fails

- Two sensor inputs through M12 sockets (max. 150 mA) for quick stop and interlocked manual operation
- with AUTO - OFF/RESET - HAND key switches
- with selector switch REV - OFF - FWD

| | |
|---|--|
| FEATURES | Parameterization: drivesConnect Parameterization: drivesConnect mobile (App) Parameterization: Fieldbus Parameterization: Keypad |
| 10.10 TEMPERATURE RISE | The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 SHORT-CIRCUIT RATING | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.12 ELECTROMAGNETIC COMPATIBILITY | Is the panel builder's responsibility. The specifications for the switchgear must be observed. |
| 10.13 MECHANICAL FUNCTION | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed. |
| 10.2.2 CORROSION RESISTANCE | Meets the product standard's requirements. |
| 10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES | Meets the product standard's requirements. |
| 10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT | Meets the product standard's requirements. |
| 10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS | Meets the product standard's requirements. |
| 10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION | Meets the product standard's requirements. |
| 10.2.5 LIFTING | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.6 MECHANICAL IMPACT | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.2.7 INSCRIPTIONS | Meets the product |

| | |
|----------------------------|---|
| DECLARATIONS OF CONFORMITY | eaton-speed-controller-declaration-of-conformity-uk251321en.pdf |
| ECAD MODEL | ETN.RASP5-4421EIP-412R000S1.edz |
| MCAD MODEL | ramo5_v31.dwg rasp5_v31.stp |
| □□□□□ | eaton-powerxl-speed-control-unit-ethernet-profinet-rasp5-il034093zu.pdf |
| □□□□ | eaton-rapid-link-5-brochure-br040014en-en-us.pdf |
| □□□□ | eaton-rapid-link-5-mn034004en-us.pdf |
| | eaton-bus-adapter-rapidlink-speed-controller-dimensions-005.eps |
| | eaton-bus-adapter-rapidlink-speed-controller-dimensions-002.eps |
| □□ | eaton-bus-adapter-rapidlink-speed-controller-dimensions-003.eps |
| | eaton-bus-adapter-rapidlink-speed-controller-dimensions-004.eps |

| | |
|---|--|
| | standard's requirements. |
| 10.3 DEGREE OF PROTECTION OF ASSEMBLIES | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 CLEARANCES AND CREEPAGE DISTANCES | Meets the product standard's requirements. |
| 10.5 PROTECTION AGAINST ELECTRIC SHOCK | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS | Is the panel builder's responsibility. |
| 10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS | Is the panel builder's responsibility. |
| 10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH | Is the panel builder's responsibility. |
| 10.9.3 IMPULSE WITHSTAND VOLTAGE | Is the panel builder's responsibility. |
| 10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL | Is the panel builder's responsibility. |
| FITTED WITH: | <p>Two sensor inputs through M12 sockets (max. 150 mA) for quick stop and interlocked manual operation</p> <p>Selector switch (Positions: REV - OFF - FWD)</p> <p>Thermo-click with safe isolation</p> <p>Key switch position AUTO</p> <p>Key switch position OFF/RESET</p> <p>Key switch position HAND</p> <p>IGBT inverter</p> <p>PTC thermistor monitoring</p> <p>Control unit</p> <p>Internal DC link</p> <p>PC connection</p> <p>Manual override switch</p> <p>2 Actuator outputs</p> |
| CLIMATIC PROOFING | <p>< 95 %, no condensation</p> <p>In accordance with IEC/EN 50178</p> |
| OPERATING MODE | <p>PM and LSPM motors</p> <p>U/f control</p> <p>BLDC motors</p> <p>Synchronous reluctance motors</p> <p>Sensorless vector control</p> |

| | |
|--|---|
| | (SLV) |
| RATED IMPULSE WITHSTAND VOLTAGE (UIMP) | 2000 V |
| ALTITUDE | Max. 2000 m Above 1000 m with 1 % performance reduction per 100 m |
| APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED | Yes |
| MAINS SWITCH-ON FREQUENCY | Maximum of one time every 60 seconds |
| AMBIENT OPERATING TEMPERATURE - MAX | 40 °C |
| AMBIENT OPERATING TEMPERATURE - MIN | -10 °C |
| MAINS VOLTAGE - MAX | 480 V |
| OUTPUT VOLTAGE - MAX | 500 V |
| RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE | 10 % |
| RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE | 10 % |
| AMBIENT STORAGE TEMPERATURE - MAX | 70 °C |
| AMBIENT STORAGE TEMPERATURE - MIN | -40 °C |
| APPLICATION IN INDUSTRIAL AREA PERMITTED | Yes |
| MAINS VOLTAGE TOLERANCE | 380 - 480 V (-10 %/+10 %, at 50/60 Hz) |
| PRODUCT CATEGORY | Speed controller |
| PROTECTION | Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4) |
| RESOLUTION | 0.1 Hz (Frequency resolution, setpoint value) |
| MOUNTING POSITION | Vertical |
| RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ) | 10 kA |
| OVERVOLTAGE CATEGORY | III |
| COMMUNICATION INTERFACE | Ethernet IP, built in |
| CONNECTION | Plug type: HAN Q4/2 |

| | |
|---|--|
| CONVERTER TYPE | U converter |
| DEGREE OF PROTECTION | NEMA 12 IP65 |
| ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE | 2 HP |
| HEAT DISSIPATION CAPACITY PDISS | 0 W |
| HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID | 0 W |
| INPUT CURRENT ILN AT 150% OVERLOAD | 4.1 A |
| MAINS CURRENT DISTORTION | 120 % |
| PROTOCOL | EtherNet/IP |
| OVERLOAD CURRENT | For 60 s every 600 s At 40 °C |
| OVERLOAD CURRENT IL AT 150% OVERLOAD | 6.5 A |
| RATED FREQUENCY - MAX | 66 Hz |
| RATED FREQUENCY - MIN | 45 Hz |
| RATED OPERATIONAL POWER AT 380/400 V, 50 HZ, 3-PHASE | 0.75 kW |
| ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 150% OVERLOAD | 4.3 A |
| ASSIGNED MOTOR CURRENT IM AT 440 - 480 V, 60 HZ, 150% OVERLOAD | 4.3 A |
| SYSTEM CONFIGURATION TYPE | AC voltage Center-point earthed star network (TN-S network) Phase-earthed AC supply systems are not permitted. |
| BRAKING CURRENT | ≤ 0.6 A (max. 6 A for 120 ms), Actuator for external motor brake |
| ELECTROMAGNETIC COMPATIBILITY | 1st and 2nd environments (according to EN 61800-3) |
| CURRENT LIMITATION | 0.4 - 4.3 A, motor, main circuit Adjustable, motor, main circuit |
| BRAKING TORQUE | ≤ 30 % (I/Ie) Adjustable to 100 % (I/Ie), DC - Main circuit |

| | |
|------------------------------------|--|
| BRAKING VOLTAGE | 280/207 V DC -15 % / +10 % Actuator for external motor brake |
| CABLE LENGTH | C1 ≤ 1 m, maximum motor cable length C2 ≤ 5 m, maximum motor cable length C3 ≤ 25 m, maximum motor cable length |
| FUNCTIONS | 1 potentiometer speed For actuation of motors with mechanical brake 3 fixed speeds |
| DELAY TIME | < 10 ms, On-delay < 10 ms, Off-delay |
| NUMBER OF INPUTS (ANALOG) | 0 |
| NUMBER OF INPUTS (DIGITAL) | 4 |
| RADIO INTERFERENCE CLASS | C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. C1: for conducted emissions only |
| NUMBER OF OUTPUTS (DIGITAL) | 2 |
| STARTING CURRENT - MAX | 200 % I _H , max. starting current (High Overload), For 2 seconds every 20 seconds, Power section |
| NUMBER OF PHASES (INPUT) | 3 |
| NUMBER OF PHASES (OUTPUT) | 3 |
| POWER CONSUMPTION | 46 W |
| INTERFACES | Number of slave addresses: 31 (AS-Interface®) Max. total power consumption from AS-Interface® power supply unit (30 V): 250 mA Specification: S-7.4 (AS-Interface®) |
| EFFICIENCY | 98 % (η) |
| RATED CONTROL VOLTAGE (UC) | 24 V DC (-15 %/+20 %, external via AS-Interface® plug) 180/207 V DC (external) |

| | |
|---|---|
| | brake 50/60 Hz) |
| SUPPLY FREQUENCY | 50/60 Hz |
| LEAKAGE CURRENT AT GROUND IPE - MAX | 3.5 mA |
| MAINS VOLTAGE - MIN | 380 V |
| NOMINAL OUTPUT CURRENT I2N | 4.3 A |
| NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET) | 2 |
| NUMBER OF HW-INTERFACES (OTHER) | 0 |
| NUMBER OF HW-INTERFACES (PARALLEL) | 0 |
| NUMBER OF HW-INTERFACES (RS-232) | 0 |
| NUMBER OF HW-INTERFACES (RS-422) | 0 |
| NUMBER OF HW-INTERFACES (RS-485) | 1 |
| NUMBER OF HW-INTERFACES (SERIAL TTY) | 0 |
| NUMBER OF HW-INTERFACES (USB) | 0 |
| NUMBER OF INTERFACES (PROFINET) | 0 |
| NUMBER OF OUTPUTS (ANALOG) | 0 |
| OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX | 1.5 kW |
| OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX | 1.5 kW |
| OUTPUT FREQUENCY - MAX | 500 Hz |
| OUTPUT FREQUENCY - MIN | 0 Hz |
| SHORT-CIRCUIT PROTECTION (EXTERNAL OUTPUT CIRCUITS) | Type 1 coordination via the power bus' feeder unit, Main circuit |
| SHOCK RESISTANCE | 15 g, Mechanical, According to IEC/EN 60068-2-27, 11 ms, Half-sinusoidal shock 11 ms, 1000 shocks per shaft |
| SWITCHING FREQUENCY | 8 kHz, 4 - 32 kHz adjustable, fPWM, Power section, Main circuit |
| RATED OPERATIONAL CURRENT (IE) | 4.3 A at 150% overload (at an operating frequency of |

| | |
|--|--|
| | 8 kHz and an ambient air temperature of +40 °C) |
| RATED OPERATIONAL VOLTAGE | 480 V AC, 3-phase 400 V AC, 3-phase |
| VIBRATION | Resistance: 6 Hz, Amplitude 0.15 mm Resistance: 10 - 150 Hz, Oscillation frequency Resistance: According to IEC/EN 60068-2-6 Resistance: 57 Hz, Amplitude transition frequency on acceleration |
| HEAT DISSIPATION AT CURRENT/SPEED | 32.3 W at 25% current and 0% speed 33.2 W at 25% current and 50% speed 35.2 W at 50% current and 90% speed 36.2 W at 50% current and 0% speed 37.6 W at 50% current and 50% speed 46.3 W at 100% current and 90% speed 48.7 W at 100% current and 0% speed 48.7 W at 100% current and 50% speed |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□□
Eaton.com

© 2025 □□ □□□□□□□□

Follow us on social media to get the latest product and support information.

