



□□□□□

Eaton 198925

Eaton Moeller® series Rapid Link - Speed controllers, 8.5 A, 4 kW, Sensor input 4, Actuator output 2, 180/207 V DC, Ethernet IP, HAN Q4/2, with manual override switch, STO (Safe Torque Off), with fan

□□□□

PRODUCT NAME	Eaton Rapid Link Speed controller
---------------------	-----------------------------------

CATALOG NUMBER	198925
-----------------------	--------

PRODUCT LENGTH/DEPTH	195 mm
-----------------------------	--------

PRODUCT HEIGHT	270 mm
-----------------------	--------

PRODUCT WIDTH	220 mm
----------------------	--------

PRODUCT WEIGHT	3.8 kg
-----------------------	--------

CERTIFICATIONS	IEC/EN 61800-5-1 CE UL 61800-5-1 UL approval RoHS
-----------------------	---

CATALOG NOTES

- 3 fixed speeds and 1 potentiometer speed
- can be switched over from U/f to (vector) speed control
- Connection of supply voltage via adapter cable on round or flexible busbar junction
- Diagnostics and reset on the device and via Ethernet IP
- integrated PTC thermistor monitoring and Thermoclick with safe isolation
- optional: 4 sensor inputs with M12-Y adapter for switchover to creep



Powering Business Worldwide

speed

- optional: Faster stop if external 24 V fails
- Two sensor inputs through M12 sockets (max. 150 mA) for quick stop and interlocked manual operation
- with AUTO - OFF/RESET - HAND key switches
- with selector switch REV - OFF - FWD

FEATURES

Parameterization:
drivesConnect
Internal and on heat sink,
temperature-controlled
Fan
Parameterization: Keypad
Parameterization:
drivesConnect mobile
(App)
Parameterization: Fieldbus

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

Meets the product standard's requirements.

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to

DECLARATIONS OF CONFORMITY

[eaton-speed-controller-declaration-of-conformity-uk251323en.pdf](#)

ECAD MODEL

[ETN.RASP5-8421EIP-412R011S1.edz](#)

MCAD MODEL

[rasp5_v34.stp](#)
[ramo5_v34.dwg](#)

□□□□□

[eaton-powerxl-speed-control-unit-ethernet-profinet-rasp5-il034093zu.pdf](#)

□□□□

[eaton-rapid-link-5-brochure-br040014en-en-us.pdf](#)

□□□□

[eaton-rapid-link-5-mn034004en-us.pdf](#)

□□

[eaton-bus-adapter-rapidlink-speed-controller-dimensions-002.eps](#)

[eaton-bus-adapter-rapidlink-speed-controller-dimensions-005.eps](#)

[eaton-bus-adapter-rapidlink-speed-controller-dimensions-004.eps](#)

[eaton-bus-adapter-rapidlink-speed-controller-dimensions-003.eps](#)

	be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Control unit PC connection IGBT inverter Two sensor inputs through M12 sockets (max. 150 mA) for quick stop and interlocked manual operation Thermo-click with safe isolation 2 Actuator outputs Internal DC link Key switch position AUTO Key switch position HAND Selector switch (Positions: REV - OFF - FWD) PTC thermistor monitoring Fan Key switch position OFF/RESET Manual override switch
CLIMATIC PROOFING	In accordance with IEC/EN 50178 < 95 %, no condensation
OPERATING MODE	U/f control Sensorless vector control

	(SLV) BLDC motors Synchronous reluctance motors PM and LSPM motors
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	2000 V
ALTITUDE	Max. 2000 m Above 1000 m with 1 % performance reduction per 100 m
APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED	Yes
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 60 seconds
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-10 °C
MAINS VOLTAGE - MAX	480 V
OUTPUT VOLTAGE - MAX	500 V
RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes
MAINS VOLTAGE TOLERANCE	380 - 480 V (-10 %/+10 %, at 50/60 Hz)
PRODUCT CATEGORY	Speed controller
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
RESOLUTION	0.1 Hz (Frequency resolution, setpoint value)
MOUNTING POSITION	Vertical
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	10 kA
OVERVOLTAGE	III

CATEGORY	
COMMUNICATION INTERFACE	Ethernet IP, built in
CONNECTION	Plug type: HAN Q4/2
CONVERTER TYPE	U converter
DEGREE OF PROTECTION	IP65 NEMA 12
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	5 HP
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
INPUT CURRENT ILN AT 150% OVERLOAD	7.8 A
MAINS CURRENT DISTORTION	120 %
PROTOCOL	EtherNet/IP
OVERLOAD CURRENT	At 40 °C For 60 s every 600 s
OVERLOAD CURRENT IL AT 150% OVERLOAD	12.7 A
RATED FREQUENCY - MAX	66 Hz
RATED FREQUENCY - MIN	45 Hz
RATED OPERATIONAL POWER AT 380/400 V, 50 HZ, 3-PHASE	1.5 kW
ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 150% OVERLOAD	8.5 A
ASSIGNED MOTOR CURRENT IM AT 440 - 480 V, 60 HZ, 150% OVERLOAD	8.5 A
SYSTEM CONFIGURATION TYPE	AC voltage Center-point earthed star network (TN-S network) Phase-earthed AC supply systems are not permitted.
BRAKING CURRENT	≤ 0.6 A (max. 6 A for 120 ms), Actuator for external motor brake
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
CURRENT LIMITATION	0.8 - 8.5 A, motor, main circuit Adjustable, motor, main

	circuit
BRAKING TORQUE	$\leq 30\%$ (I/Ie) Adjustable to 100 % (I/Ie), DC - Main circuit
BRAKING VOLTAGE	280/207 V DC -15 % / +10 % Actuator for external motor brake
CABLE LENGTH	C1 ≤ 1 m, maximum motor cable length C3 ≤ 25 m, maximum motor cable length C2 ≤ 5 m, maximum motor cable length
FUNCTIONS	STO (Safe Torque Off) 3 fixed speeds 1 potentiometer speed For actuation of motors with mechanical brake
DELAY TIME	< 10 ms, Off-delay < 10 ms, On-delay
NUMBER OF INPUTS (ANALOG)	0
NUMBER OF INPUTS (DIGITAL)	4
RADIO INTERFERENCE CLASS	C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. C1: for conducted emissions only
NUMBER OF OUTPUTS (DIGITAL)	2
STARTING CURRENT - MAX	200 %, IH, max. starting current (High Overload), For 2 seconds every 20 seconds, Power section
NUMBER OF PHASES (INPUT)	3
NUMBER OF PHASES (OUTPUT)	3
POWER CONSUMPTION	95 W
INTERFACES	Number of slave addresses: 31 (AS-Interface®) Max. total power consumption from AS-Interface® power supply unit (30 V): 250 mA Specification: S-7.4 (AS-Interface®)

EFFICIENCY	98 % (η)
RATED CONTROL VOLTAGE (UC)	24 V DC (-15 %/+20 %, external via AS-Interface® plug) 180/207 V DC (external brake 50/60 Hz)
SUPPLY FREQUENCY	50/60 Hz
LEAKAGE CURRENT AT GROUND IPE - MAX	3.5 mA
MAINS VOLTAGE - MIN	380 V
NOMINAL OUTPUT CURRENT I2N	8.5 A
NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)	2
NUMBER OF HW-INTERFACES (OTHER)	0
NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF OUTPUTS (ANALOG)	0
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	4 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	4 kW
OUTPUT FREQUENCY - MAX	500 Hz
OUTPUT FREQUENCY - MIN	0 Hz
SHORT-CIRCUIT PROTECTION (EXTERNAL OUTPUT CIRCUITS)	Type 1 coordination via the power bus' feeder unit, Main circuit
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, 11 ms, Half-sinusoidal shock 11 ms, 1000 shocks per shaft

SWITCHING FREQUENCY	8 kHz, 4 - 32 kHz adjustable, fPWM, Power section, Main circuit
RATED OPERATIONAL CURRENT (IE)	8.5 A at 150% overload (at an operating frequency of 8 kHz and an ambient air temperature of +40 °C)
RATED OPERATIONAL VOLTAGE	400 V AC, 3-phase 480 V AC, 3-phase
VIBRATION	Resistance: 6 Hz, Amplitude 0.15 mm Resistance: According to IEC/EN 60068-2-6 Resistance: 57 Hz, Amplitude transition frequency on acceleration Resistance: 10 - 150 Hz, Oscillation frequency
HEAT DISSIPATION AT CURRENT/SPEED	51.6 W at 25% current and 0% speed 53.8 W at 25% current and 50% speed 60.9 W at 50% current and 0% speed 64 W at 50% current and 90% speed 65.4 W at 50% current and 50% speed 85.1 W at 100% current and 0% speed 94 W at 100% current and 50% speed 95.3 W at 100% current and 90% speed

□□□□:
□□□□:
□□□:
□□: