



□□□□

Eaton 197718

Eaton Moeller series E57G General purpose series, Proximity switch, 6 - 48 V DC, d=18 mm, 1 N/C, 3-wire, Plug-in connection M12 x 1, Sn= 8 mm, Flush mounting, PNP, Stainless steel

□□□□

PRODUCT NAME	Eaton Moeller® series E57G Proximity switch
CATALOG NUMBER	197718
PRODUCT LENGTH/DEPTH	69.2 mm
PRODUCT HEIGHT	18 mm
PRODUCT WIDTH	18 mm
PRODUCT WEIGHT	0.05 kg
CERTIFICATIONS	UL Category Control No.: NRKH, NRKH7 UL File No.: E166051 Certified by UL for use in Canada IEC/EN 60947-5-2 CSA-C22.2 No. 14 UL Listed UL 508



Powering Business Worldwide



TYPE	Inductive sensor
ELECTRIC CONNECTION TYPE	Connector M12
ENCLOSURE MATERIAL FINISHING	Other
ACTUATION TYPE	Metallic Target
ENCLOSURE MATERIAL	Metal
ENCLOSURE TYPE	Cylinder, screw-thread
CATEGORY (EN 954-1)	B
EXPLOSION SAFETY CATEGORY FOR DUST	None
EXPLOSION SAFETY CATEGORY FOR GAS	None
SAFETY PERFORMANCE LEVEL (EN ISO 13849-1)	None
SIL (IEC 61508)	None
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
DIAMETER SENSOR	18 mm
NUMBER OF CONTACT ENERGIZED OUTPUTS WITH SIGNALLING FUNCTION	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF OUTPUTS (PROTECTED CONTACT ENERGIZED)	0
NUMBER OF OUTPUTS (PROTECTED SEMICONDUCTOR)	0
NUMBER OF OUTPUTS (SEMICONDUCTOR WITH SIGNALING FUNCTION)	1
OPERATIONAL CURRENT (IB) IN THE SWITCHED STATE AT 24 V DC	10 A
FUNCTIONS	Short-circuit protection
VOLTAGE TYPE	DC
MOUNTING METHOD	Flush mounting
MATERIAL	Stainless steel
CONNECTION TYPE	3-wire Plug-in connection M12 x 1



