

## Eaton 198593

Eaton Moeller® series M22 Potentiometer  
10K, without inscription M22-R10K-BLANK

|                                 |   |
|---------------------------------|---|
|                                 |   |
| <b>PRODUCT NAME</b>             | Eaton Moeller® series<br>M22 Potentiometer  |
| <b>CATALOG NUMBER</b>           | 198593  |
| <b>PRODUCT<br/>LENGTH/DEPTH</b> | 65 mm   |
| <b>PRODUCT HEIGHT</b>           | 29 mm   |
| <b>PRODUCT WIDTH</b>            | 29 mm   |
| <b>PRODUCT WEIGHT</b>           | 0.034 kg  |
| <b>CERTIFICATIONS</b>           | CSA Class No.: 3211-03<br>CSA file No. 012528<br>DNV<br>GL<br>IEC/EN 60947<br>IEC/EN 60947-5<br>UL 508<br>CSA-C22.2 No. 14-05<br>CSA-C22.2 No. 94-91<br>CE marking<br>LR<br>UL Category Control No.:<br>NKCR<br>UL File No.: E29184<br>UL Listed<br>CSA certified<br>VDE 0660 |

| TYPE   |   |
|--|---|
| 10.10 TEMPERATURE RISE   | Potentiometer<br><br>The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices. |
| 10.11 SHORT-CIRCUIT RATING   | Is the panel builder's responsibility. The specifications for the switchgear must be observed.  |
| 10.12 ELECTROMAGNETIC COMPATIBILITY  | Is the panel builder's responsibility. The specifications for the switchgear must be observed.  |
| 10.13 MECHANICAL FUNCTION  | The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.  |
| 10.2.2 CORROSION RESISTANCE  | Meets the product standard's requirements.  |
| 10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES                         | Meets the product standard's requirements.  |
| 10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT       | Meets the product standard's requirements.  |
| 10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS | Meets the product standard's requirements.  |
| 10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION                                 | Please enquire  |
| 10.2.5 LIFTING   | Does not apply, since the entire switchgear needs to be evaluated.  |
| 10.2.6 MECHANICAL IMPACT   | Does not apply, since the entire switchgear needs to be evaluated.  |
| 10.2.7 INSCRIPTIONS  | Meets the product standard's requirements.  |
| 10.3 DEGREE OF PROTECTION OF   | Does not apply, since the entire switchgear needs to  |

|  |  |
|--|--|
| <a href="#">IL04716002Z</a> <a href="#">IL047030ZU</a> |  |
| /  | <a href="#">RMQ small E-Stop emergency-stop button</a> |

|   |  |
|---|--|
| <b>ASSEMBLIES</b>   | be evaluated.  |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.                         |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated. |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.                             |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.                             |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.                             |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.                             |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.                             |
| <b>ELECTRIC CONNECTION TYPE</b>                                 | Screw connection   |
| <b>FITTED WITH:</b>   | 3 individual screw terminals                                       |
| <b>POLLUTION DEGREE</b>   | 3  |
| <b>ACCURACY</b>   | ± 10 % (linear), Resistance value                                  |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>                   | 4000 V AC  |
| <b>BEZEL COLOR</b>  | Titanium   |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                      | 70 °C  |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                      | -25 °C   |
| <b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>       | 0 W  |
| <b>HEAT DISSIPATION CAPACITY PDISS</b>                          | 0 W  |
| <b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>        | 0 W  |
| <b>NUMBER OF REVOLUTIONS - MAX</b>                              | 1  |
| <b>NUMBER OF</b>  | 1  |

|   |                           |
|---|---------------------------|
| REVOLUTIONS - MIN   |                           |
| OPENING DIAMETER  | 22.5 mm                   |
| RATED INSULATION VOLTAGE (UI)                                 | 250 V                     |
| RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN) | 0 A                       |
| RATED POWER   | 0.5 VA                    |
| STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS            | 0.5 W                     |
| DESIGN  | Classical                 |
| MOUNTING POSITION   | As required               |
| OVERVOLTAGE CATEGORY  | III                       |
| DEGREE OF PROTECTION  | IP66<br>NEMA Other        |
| POWER CONSUMPTION   | 0.5 W                     |
| LIFESPAN, MECHANICAL  | 25,000 Operations         |
| RESISTANCE  | 10000 Ohm                 |
| TERMINAL CAPACITY (SOLID)                                     | 0.5 - 1.5 mm <sup>2</sup> |
| TERMINAL CAPACITY (STRANDED)                                  | 0.5 - 1.5 mm <sup>2</sup> |
| TIGHTENING TORQUE   | 0.5 Nm, Screw terminals   |

|                 |
|-----------------|
| PROJECT NAME:   |
| PROJECT NUMBER: |
| PREPARED BY:    |
| :               |