



□□□□□

## Eaton 198850

Eaton Moeller® series Rapid Link - Speed controllers, 8.5 A, 4 kW, Sensor input 4, 230/277 V AC, AS-Interface®, S-7.4 for 31 modules, HAN Q4/2, with braking resistance, STO (Safe Torque Off), with fan

### □□□□

|                             |   |
|-----------------------------|---|
| <b>PRODUCT NAME</b>         | Eaton Rapid Link Speed controller                             |
| <b>CATALOG NUMBER</b>       | 198850  |
| <b>PRODUCT LENGTH/DEPTH</b> | 195 mm  |
| <b>PRODUCT HEIGHT</b>       | 270 mm  |
| <b>PRODUCT WIDTH</b>        | 220 mm  |
| <b>PRODUCT WEIGHT</b>       | 3.62 kg   |
| <b>CERTIFICATIONS</b>       | UL 61800-5-1<br>UL approval<br>CE<br>IEC/EN 61800-5-1<br>RoHS |

### CATALOG NOTES

- 3 fixed speeds and 1 potentiometer speed
- can be switched over from U/f to (vector) speed control
- Connection of supply voltage via adapter cable on round or flexible busbar junction
- Diagnostics and reset on device and via AS-Interface
- integrated PTC thermistor monitoring and Thermoclick with safe isolation
- optional: 4 sensor inputs with M12-Y adapter for switchover to creep



Powering Business Worldwide

speed

- optional: Faster stop if external 24 V fails
- Two sensor inputs through M12 sockets (max. 150 mA) for quick stop and interlocked manual operation
- with AUTO - OFF/RESET - HAND key switches
- with selector switch REV - OFF - FWD

## FEATURES

Parameterization:  
drivesConnect  
Internal and on heat sink,  
temperature-controlled  
Fan  
Parameterization:  
drivesConnect mobile  
(App)  
Diagnostics and reset on  
device and via AS-Interface

Parameterization: Fieldbus

Parameterization: Keypad

## 10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

## 10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

## 10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

## 10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

## 10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

## 10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

## 10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

## 10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

## 10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

Meets the product standard's requirements.

## 10.2.5 LIFTING

Does not apply, since the entire switchgear needs to

## DECLARATIONS OF CONFORMITY

[eaton-speed-controller-declaration-of-conformity-uk251124en.pdf](#)

## ECAD MODEL

[ETN.RASP5-8402A31-4120111S1.edz](#)

## MCAD MODEL

[ramo5\\_v28.dwg](#)

## □□□□□

[eaton-powerxl-speed-control-unit-as-interface-rasp5-il034085zu.pdf](#)

## □□□□

[eaton-rapid-link-5-brochure-br040014en-en-us.pdf](#)

## □□□□

[eaton-rapid-link-5-mn034004en-us.pdf](#)

[eaton-bus-adapter-rapidlink-speed-controller-dimensions-002.eps](#)

[eaton-bus-adapter-rapidlink-speed-controller-dimensions-004.eps](#)

## □□

[eaton-bus-adapter-rapidlink-speed-controller-dimensions.eps](#)

[eaton-bus-adapter-rapidlink-speed-controller-dimensions-003.eps](#)

|   |   |
|---|---|
|   | be evaluated.   |
| <b>10.2.6 MECHANICAL IMPACT</b>                                 | Does not apply, since the entire switchgear needs to be evaluated.  |
| <b>10.2.7 INSCRIPTIONS</b>                                      | Meets the product standard's requirements.  |
| <b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>                  | Does not apply, since the entire switchgear needs to be evaluated.  |
| <b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>                   | Meets the product standard's requirements.  |
| <b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>                   | Does not apply, since the entire switchgear needs to be evaluated.  |
| <b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>   | Does not apply, since the entire switchgear needs to be evaluated.  |
| <b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>        | Is the panel builder's responsibility.  |
| <b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>                 | Is the panel builder's responsibility.  |
| <b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>                 | Is the panel builder's responsibility.  |
| <b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>                         | Is the panel builder's responsibility.  |
| <b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b> | Is the panel builder's responsibility.  |
| <b>FITTED WITH:</b>   | Control unit<br>PC connection<br>Key switch position AUTO<br>Key switch position HAND<br>Two sensor inputs through M12 sockets (max. 150 mA) for quick stop and interlocked manual operation<br>Braking resistance<br>Breaking resistance<br>IGBT inverter<br>Selector switch (Positions: REV - OFF - FWD)<br>Internal DC link<br>Key switch position OFF/RESET<br>PTC thermistor monitoring<br><br>Thermo-click with safe isolation<br>Fan |
| <b>CLIMATIC PROOFING</b>  | In accordance with IEC/EN 50178   |

|  |  |
|--|--|
|  | < 95 %, no condensation  |
| <b>OPERATING MODE</b>  | BLDC motors<br>PM and LSPM motors<br>Synchronous reluctance motors<br>U/f control<br>Sensorless vector control (SLV) |
| <b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>                | 2000 V   |
| <b>ALTITUDE</b>  | Max. 2000 m<br>Above 1000 m with 1 % performance reduction per 100 m   |
| <b>APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED</b> | Yes  |
| <b>MAINS SWITCH-ON FREQUENCY</b>                             | Maximum of one time every 60 seconds   |
| <b>AMBIENT OPERATING TEMPERATURE - MAX</b>                   | 40 °C  |
| <b>AMBIENT OPERATING TEMPERATURE - MIN</b>                   | -10 °C   |
| <b>MAINS VOLTAGE - MAX</b>                                   | 480 V  |
| <b>OUTPUT VOLTAGE - MAX</b>                                  | 500 V  |
| <b>RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE</b>            | 10 %   |
| <b>RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE</b>              | 10 %   |
| <b>AMBIENT STORAGE TEMPERATURE - MAX</b>                     | 70 °C  |
| <b>AMBIENT STORAGE TEMPERATURE - MIN</b>                     | -40 °C   |
| <b>APPLICATION IN INDUSTRIAL AREA PERMITTED</b>              | Yes  |
| <b>MAINS VOLTAGE TOLERANCE</b>                               | 380 - 480 V (-10 %/+10 %, at 50/60 Hz)   |
| <b>PRODUCT CATEGORY</b>                                      | Speed controller   |
| <b>PROTECTION</b>  | Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)                                      |
| <b>RESOLUTION</b>  | 0.1 Hz (Frequency resolution, setpoint value)  |
| <b>SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR</b>        | 765 VDC  |

|   |  |
|---|--|
| <b>MOUNTING POSITION</b>  | Vertical   |
| <b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>                   | 10 kA  |
| <b>OVERVOLTAGE CATEGORY</b>   | III  |
| <b>COMMUNICATION INTERFACE</b>  | AS-Interface   |
| <b>CONNECTION</b>   | Plug type: HAN Q4/2  |
| <b>CONVERTER TYPE</b>   | U converter  |
| <b>DEGREE OF PROTECTION</b>   | IP65<br>NEMA 12  |
| <b>ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE</b>              | 5 HP   |
| <b>HEAT DISSIPATION CAPACITY PDISS</b>                                | 0 W  |
| <b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>              | 0 W  |
| <b>INPUT CURRENT ILN AT 150% OVERLOAD</b>                             | 7.8 A  |
| <b>MAINS CURRENT DISTORTION</b>                                       | 120 %  |
| <b>PROTOCOL</b>   | ASI<br>AS-Interface profile cable:<br>S-7.4 for 31 modules   |
| <b>OVERLOAD CURRENT</b>   | At 40 °C<br>For 60 s every 600 s   |
| <b>OVERLOAD CURRENT IL AT 150% OVERLOAD</b>                           | 12.7 A   |
| <b>RATED FREQUENCY - MAX</b>  | 66 Hz  |
| <b>RATED FREQUENCY - MIN</b>  | 45 Hz  |
| <b>RATED OPERATIONAL POWER AT 380/400 V, 50 HZ, 3-PHASE</b>           | 4 kW   |
| <b>ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 150% OVERLOAD</b>       | 8.5 A  |
| <b>ASSIGNED MOTOR CURRENT IM AT 440 - 480 V, 60 HZ, 150% OVERLOAD</b> | 8.5 A  |
| <b>SYSTEM CONFIGURATION TYPE</b>                                      | AC voltage<br>Phase-earthed AC supply systems are not permitted.<br>Center-point earthed star network (TN-S network) |
| <b>BRAKING CURRENT</b>  | ≤ 0.6 A (max. 6 A for 120  |

|                                      |   |
|--------------------------------------|---|
|                                      | ms), Actuator for external motor brake  |
| <b>ELECTROMAGNETIC COMPATIBILITY</b> | 1st and 2nd environments (according to EN 61800-3)  |
| <b>CURRENT LIMITATION</b>            | 0.8 - 8.5 A, motor, main circuit<br>Adjustable, motor, main circuit   |
| <b>BRAKING TORQUE</b>                | $\leq 30\%$ (I/Ie)<br>Adjustable to 100 % (I/Ie), DC - Main circuit   |
| <b>BRAKING VOLTAGE</b>               | 230/277 V AC -15 % / +10 %, Actuator for external motor brake   |
| <b>CABLE LENGTH</b>                  | C1 $\leq 1$ m, maximum motor cable length<br>C2 $\leq 5$ m, maximum motor cable length<br>C3 $\leq 25$ m, maximum motor cable length  |
| <b>FUNCTIONS</b>                     | For actuation of motors with mechanical brake<br>3 fixed speeds<br>1 potentiometer speed<br>STO (Safe Torque Off)<br>Brake chopper with braking resistance for dynamic braking<br>4-quadrant operation possible |
| <b>DELAY TIME</b>                    | < 10 ms, On-delay<br>< 10 ms, Off-delay   |
| <b>NUMBER OF INPUTS (ANALOG)</b>     | 0   |
| <b>NUMBER OF INPUTS (DIGITAL)</b>    | 4   |
| <b>RADIO INTERFERENCE CLASS</b>      | C1: for conducted emissions only<br>C2, C3: depending on the motor cable length, the connected load, and ambient conditions.<br>External radio interference suppression filters (optional) may be necessary.    |
| <b>NUMBER OF OUTPUTS (DIGITAL)</b>   | 0   |
| <b>STARTING CURRENT - MAX</b>        | 200 %, I <sub>H</sub> , max. starting current (High Overload), For 2 seconds every 20 seconds, Power section  |
| <b>NUMBER OF PHASES (INPUT)</b>      | 3   |

|   |   |
|---|---|
| <b>NUMBER OF PHASES (OUTPUT)</b>                              | 3   |
| <b>POWER CONSUMPTION</b>                                      | 95 W  |
| <b>INTERFACES</b>   | Number of slave addresses: 31 (AS-Interface®)<br>Specification: S-7.4 (AS-Interface®)<br>Max. total power consumption from AS-Interface® power supply unit (30 V): 190 mA |
| <b>EFFICIENCY</b>   | 98 % ( $\eta$ )   |
| <b>RATED CONTROL VOLTAGE (UC)</b>                             | 24 V DC (-15 %/+20 %, external via AS-Interface® plug)<br>230/277 V AC (external brake 50/60 Hz)  |
| <b>SUPPLY FREQUENCY</b>                                       | 50/60 Hz  |
| <b>LEAKAGE CURRENT AT GROUND IPE - MAX</b>                    | 3.5 mA  |
| <b>MAINS VOLTAGE - MIN</b>                                    | 380 V   |
| <b>NOMINAL OUTPUT CURRENT I2N</b>                             | 8.5 A   |
| <b>NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET)</b>          | 0   |
| <b>NUMBER OF HW-INTERFACES (OTHER)</b>                        | 1   |
| <b>NUMBER OF HW-INTERFACES (PARALLEL)</b>                     | 0   |
| <b>NUMBER OF HW-INTERFACES (RS-232)</b>                       | 0   |
| <b>NUMBER OF HW-INTERFACES (RS-422)</b>                       | 0   |
| <b>NUMBER OF HW-INTERFACES (RS-485)</b>                       | 1   |
| <b>NUMBER OF HW-INTERFACES (SERIAL TTY)</b>                   | 0   |
| <b>NUMBER OF HW-INTERFACES (USB)</b>                          | 0   |
| <b>NUMBER OF INTERFACES (PROFINET)</b>                        | 0   |
| <b>NUMBER OF OUTPUTS (ANALOG)</b>                             | 0   |
| <b>OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX</b>    | 4 kW  |
| <b>OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX</b> | 4 kW  |



|  |  |
|--|--|
| <b>OUTPUT FREQUENCY - MAX</b>                              | 500 Hz   |
| <b>OUTPUT FREQUENCY - MIN</b>                              | 0 Hz   |
| <b>SHORT-CIRCUIT PROTECTION (EXTERNAL OUTPUT CIRCUITS)</b> | Type 1 coordination via the power bus' feeder unit, Main circuit   |
| <b>SHOCK RESISTANCE</b>                                    | 15 g, Mechanical,<br>According to IEC/EN 60068-2-27, 11 ms, Half-sinusoidal shock 11 ms, 1000 shocks per shaft   |
| <b>SWITCHING FREQUENCY</b>                                 | 8 kHz, 4 - 32 kHz adjustable, fPWM, Power section, Main circuit  |
| <b>RATED OPERATIONAL CURRENT (IE)</b>                      | 8.5 A at 150% overload (at an operating frequency of 8 kHz and an ambient air temperature of +40 °C)   |
| <b>RATED OPERATIONAL VOLTAGE</b>                           | 400 V AC, 3-phase<br>480 V AC, 3-phase   |
| <b>VIBRATION</b>   | Resistance: According to IEC/EN 60068-2-6<br>Resistance: 6 Hz, Amplitude 0.15 mm<br>Resistance: 10 - 150 Hz, Oscillation frequency<br>Resistance: 57 Hz, Amplitude transition frequency on acceleration  |
| <b>HEAT DISSIPATION AT CURRENT/SPEED</b>                   | 51.6 W at 25% current and 0% speed<br>53.8 W at 25% current and 50% speed<br>60.9 W at 50% current and 0% speed<br>64 W at 50% current and 90% speed<br>65.4 W at 50% current and 50% speed<br>85.1 W at 100% current and 0% speed<br>94 W at 100% current and 50% speed<br>95.3 W at 100% current and 90% speed |

