



□□□□□

Eaton 199025

Eaton Moeller® series Rapid Link - Speed controllers, 5.6 A, 2.2 kW, Sensor input 4, Actuator output 2, 180/207 V DC, PROFINET, HAN Q4/2, with manual override switch, with braking resistance, STO (Safe Torque Off)

□□□□

| | |
|-----------------------------|---|
| PRODUCT NAME | Eaton Rapid Link Speed controller |
| CATALOG NUMBER | 199025 |
| PRODUCT LENGTH/DEPTH | 157 mm |
| PRODUCT HEIGHT | 270 mm |
| PRODUCT WIDTH | 220 mm |
| PRODUCT WEIGHT | 3.63 kg |
| CERTIFICATIONS | CE RoHS UL approval UL 61800-5-1 IEC/EN 61800-5-1 |
| CATALOG NOTES | <ul style="list-style-type: none">• 3 fixed speeds and 1 potentiometer speed• can be switched over from U/f to (vector) speed control• Connection of supply voltage via adapter cable on round or flexible busbar junction• Diagnostics and reset on the device and via PROFINET• integrated PTC thermistor monitoring and Thermoclick with safe isolation• optional: 4 sensor inputs with M12-Y adapter for |



Powering Business Worldwide

switchover to creep speed

- optional: Faster stop if external 24 V fails
- Two sensor inputs through M12 sockets (max. 150 mA) for quick stop and interlocked manual operation
- with AUTO - OFF/RESET - HAND key switches
- with selector switch REV - OFF - FWD

FEATURES

Parameterization: Keypad
Parameterization:
drivesConnect
Parameterization: Fieldbus

Parameterization:
drivesConnect mobile
(App)

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

Meets the product standard's requirements.

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 INSCRIPTIONS

Meets the product

DECLARATIONS OF CONFORMITY

[eaton-speed-controller-declaration-of-conformity-uk251323en.pdf](#)

ECAD MODEL

[ETN.RASP5-5421PNT-412R110S1.edz](#)

MCAD MODEL

[rasp5_v33.stp](#)
[ramo5_v33.dwg](#)

000000

[eaton-powerxl-speed-control-unit-ethernet-profinet-rasp5-il034093zu.pdf](#)

0000

[eaton-rapid-link-5-brochure-br040014en-en-us.pdf](#)

0000

[eaton-rapid-link-5-mn034004en-us.pdf](#)

[eaton-bus-adapter-rapidlink-speed-controller-dimensions-002.eps](#)

[eaton-bus-adapter-rapidlink-speed-controller-dimensions-005.eps](#)

00

[eaton-bus-adapter-rapidlink-speed-controller-dimensions-003.eps](#)

[eaton-bus-adapter-rapidlink-speed-controller-dimensions-004.eps](#)

| | |
|---|--|
| | standard's requirements. |
| 10.3 DEGREE OF PROTECTION OF ASSEMBLIES | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.4 CLEARANCES AND CREEPAGE DISTANCES | Meets the product standard's requirements. |
| 10.5 PROTECTION AGAINST ELECTRIC SHOCK | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS | Does not apply, since the entire switchgear needs to be evaluated. |
| 10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS | Is the panel builder's responsibility. |
| 10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS | Is the panel builder's responsibility. |
| 10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH | Is the panel builder's responsibility. |
| 10.9.3 IMPULSE WITHSTAND VOLTAGE | Is the panel builder's responsibility. |
| 10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL | Is the panel builder's responsibility. |
| FITTED WITH: | <p>Key switch position AUTO PTC thermistor monitoring</p> <p>Control unit Manual override switch Two sensor inputs through M12 sockets (max. 150 mA) for quick stop and interlocked manual operation Internal DC link Braking resistance 2 Actuator outputs Key switch position OFF/RESET Thermo-click with safe isolation Selector switch (Positions: REV - OFF - FWD) PC connection Breaking resistance IGBT inverter Key switch position HAND</p> |
| CLIMATIC PROOFING | <p>< 95 %, no condensation In accordance with IEC/EN 50178</p> |
| OPERATING MODE | <p>BLDC motors U/f control Sensorless vector control (SLV)</p> |

| | |
|--|--|
| | PM and LSPM motors Synchronous reluctance motors |
| RATED IMPULSE WITHSTAND VOLTAGE (UIMP) | 2000 V |
| ALTITUDE | Max. 2000 m Above 1000 m with 1 % performance reduction per 100 m |
| APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED | Yes |
| MAINS SWITCH-ON FREQUENCY | Maximum of one time every 60 seconds |
| AMBIENT OPERATING TEMPERATURE - MAX | 40 °C |
| AMBIENT OPERATING TEMPERATURE - MIN | -10 °C |
| MAINS VOLTAGE - MAX | 480 V |
| OUTPUT VOLTAGE - MAX | 500 V |
| RATED OPERATIONAL POWER AT 220/230 V, 50 HZ, 3-PHASE | 1.5 kW |
| RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE | 10 % |
| RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE | 10 % |
| AMBIENT STORAGE TEMPERATURE - MAX | 70 °C |
| AMBIENT STORAGE TEMPERATURE - MIN | -40 °C |
| APPLICATION IN INDUSTRIAL AREA PERMITTED | Yes |
| MAINS VOLTAGE TOLERANCE | 380 - 480 V (-10 %/+10 %, at 50/60 Hz) |
| PRODUCT CATEGORY | Speed controller |
| PROTECTION | Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4) |
| RESOLUTION | 0.1 Hz (Frequency resolution, setpoint value) |
| SWITCH-ON THRESHOLD FOR THE BRAKING TRANSISTOR | 765 VDC |
| MOUNTING POSITION | Vertical |

| | |
|---|--|
| RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ) | 10 kA |
| OVERVOLTAGE CATEGORY | III |
| COMMUNICATION INTERFACE | PROFINET, optional |
| CONNECTION | Plug type: HAN Q4/2 |
| CONVERTER TYPE | U converter |
| DEGREE OF PROTECTION | NEMA 12 IP65 |
| ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE | 3 HP |
| HEAT DISSIPATION CAPACITY PDISS | 0 W |
| HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID | 0 W |
| INPUT CURRENT ILN AT 150% OVERLOAD | 5.3 A |
| MAINS CURRENT DISTORTION | 120 % |
| PROTOCOL | PROFINET IO |
| OVERLOAD CURRENT | At 40 °C For 60 s every 600 s |
| OVERLOAD CURRENT IL AT 150% OVERLOAD | 8.4 A |
| RATED FREQUENCY - MAX | 66 Hz |
| RATED FREQUENCY - MIN | 45 Hz |
| ASSIGNED MOTOR CURRENT IM AT 400 V, 50 HZ, 150% OVERLOAD | 5.6 A |
| ASSIGNED MOTOR CURRENT IM AT 440 - 480 V, 60 HZ, 150% OVERLOAD | 5.6 A |
| SYSTEM CONFIGURATION TYPE | AC voltage Center-point earthed star network (TN-S network) Phase-earthed AC supply systems are not permitted. |
| BRAKING CURRENT | ≤ 0.6 A (max. 6 A for 120 ms), Actuator for external motor brake |
| ELECTROMAGNETIC COMPATIBILITY | 1st and 2nd environments (according to EN 61800-3) |
| CURRENT LIMITATION | Adjustable, motor, main circuit |

| | |
|------------------------------------|---|
| | 0.5 - 5.6 A, motor, main circuit |
| BRAKING TORQUE | Adjustable to 100 % (I/I _e), DC - Main circuit ≤ 30 % (I/I _e) |
| BRAKING VOLTAGE | 280/207 V DC -15 % / +10 %, Actuator for external motor brake |
| CABLE LENGTH | C2 ≤ 5 m, maximum motor cable length C1 ≤ 1 m, maximum motor cable length C3 ≤ 25 m, maximum motor cable length |
| FUNCTIONS | 4-quadrant operation possible Brake chopper with braking resistance for dynamic braking 1 potentiometer speed For actuation of motors with mechanical brake 3 fixed speeds STO (Safe Torque Off) |
| DELAY TIME | < 10 ms, Off-delay < 10 ms, On-delay |
| NUMBER OF INPUTS (ANALOG) | 0 |
| NUMBER OF INPUTS (DIGITAL) | 4 |
| RADIO INTERFERENCE CLASS | C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary. C1: for conducted emissions only |
| NUMBER OF OUTPUTS (DIGITAL) | 2 |
| STARTING CURRENT - MAX | 200 %, I _H , max. starting current (High Overload), For 2 seconds every 20 seconds, Power section |
| NUMBER OF PHASES (INPUT) | 3 |
| NUMBER OF PHASES (OUTPUT) | 3 |
| POWER CONSUMPTION | 58 W |
| INTERFACES | Specification: S-7.4 (AS-Interface®) Number of slave |

| | |
|---|---|
| | addresses: 31 (AS-Interface®) Max. total power consumption from AS-Interface® power supply unit (30 V): 250 mA |
| EFFICIENCY | 98 % (η) |
| RATED CONTROL VOLTAGE (UC) | 180/207 V DC (external brake 50/60 Hz) 24 V DC (-15 %/+20 %, external via AS-Interface® plug) |
| SUPPLY FREQUENCY | 50/60 Hz |
| LEAKAGE CURRENT AT GROUND IPE - MAX | 3.5 mA |
| MAINS VOLTAGE - MIN | 380 V |
| NOMINAL OUTPUT CURRENT I2N | 5.6 A |
| NUMBER OF HW-INTERFACES (INDUSTRIAL ETHERNET) | 0 |
| NUMBER OF HW-INTERFACES (OTHER) | 0 |
| NUMBER OF HW-INTERFACES (PARALLEL) | 0 |
| NUMBER OF HW-INTERFACES (RS-232) | 0 |
| NUMBER OF HW-INTERFACES (RS-422) | 0 |
| NUMBER OF HW-INTERFACES (RS-485) | 1 |
| NUMBER OF HW-INTERFACES (SERIAL TTY) | 0 |
| NUMBER OF HW-INTERFACES (USB) | 0 |
| NUMBER OF INTERFACES (PROFINET) | 2 |
| NUMBER OF OUTPUTS (ANALOG) | 0 |
| OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX | 2.2 kW |
| OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX | 2.2 kW |
| OUTPUT FREQUENCY - MAX | 500 Hz |
| OUTPUT FREQUENCY - MIN | 0 Hz |
| SHORT-CIRCUIT PROTECTION (EXTERNAL) | Type 1 coordination via the power bus' feeder |

| | |
|--|--|
| OUTPUT CIRCUITS) | unit, Main circuit |
| SHOCK RESISTANCE | 15 g, Mechanical, According to IEC/EN 60068-2-27, 11 ms, Half- sinusoidal shock 11 ms, 1000 shocks per shaft |
| SWITCHING FREQUENCY | 8 kHz, 4 - 32 kHz adjustable, fPWM, Power section, Main circuit |
| RATED OPERATIONAL CURRENT (IE) | 5.6 A at 150% overload (at an operating frequency of 8 kHz and an ambient air temperature of +40 °C) |
| RATED OPERATIONAL VOLTAGE | 480 V AC, 3-phase 400 V AC, 3-phase |
| VIBRATION | Resistance: According to IEC/EN 60068-2-6 Resistance: 10 - 150 Hz, Oscillation frequency Resistance: 6 Hz, Amplitude 0.15 mm Resistance: 57 Hz, Amplitude transition frequency on acceleration |
| HEAT DISSIPATION AT CURRENT/SPEED | 36.6 W at 25% current and 0% speed 38.1 W at 25% current and 50% speed 42 W at 50% current and 0% speed 42.5 W at 50% current and 90% speed 44.2 W at 50% current and 50% speed 55.9 W at 100% current and 0% speed 58.3 W at 100% current and 90% speed 60.4 W at 100% current and 50% speed |

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□: