

Eaton 199112

Eaton Moeller® series Rapid Link - Reversing starter, 6.6 A, Sensor input 2, 400/480 V AC, AS-Interface®, S-7.A.E. for 62 modules, HAN Q4/2, with manual override switch

PRODUCT NAME	Eaton Rapid Link Reversing starter
CATALOG NUMBER	199112
PRODUCT LENGTH/DEPTH	120 mm
PRODUCT HEIGHT	270 mm
PRODUCT WIDTH	220 mm
PRODUCT WEIGHT	1.8 kg
CERTIFICATIONS	RoHS UL approval UL 60947-4-2 CCC CE IEC/EN 60947-4-2 UL 60947-4-2
CATALOG NOTES	Assigned motor rating: for normal internally and externally ventilated 4 pole, three-phase asynchronous motors with 1500 rpm at 50 Hz or 1800 min at 60 Hz

TYPE	Reversing starter
FEATURES	Parameterization: drivesConnect Parameterization: drivesConnect mobile (App) Parameterization: Keypad Diagnostics and reset on device and via AS-Interface Parameterization: Fieldbus
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the

ECAD MODEL	ETN.RAMO5-W204A32-412RS1.edz
MCAD MODEL	ramo5_v11.dwg ramo5_v11.stp
	IL034084ZU
	eaton-rapid-link-5-brochure-br040014en-en-us.pdf
	eaton-bus-adapter-rapidlink-reversing-starter-dimensions-002.eps eaton-bus-adapter-rapidlink-reversing-starter-dimensions-003.eps

	entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Key switch position AUTO Two sensor inputs through M12 sockets (max. 150 mA) for quick stop and interlocked manual operation Thermistor monitoring PTC Thermo-click Manual override switch Key switch position OFF/RESET Electronic motor protection Key switch position HAND Short-circuit release
CLASS	CLASS 10 A
LIFESPAN, ELECTRICAL	10,000,000 Operations (at AC-3)

CLIMATIC PROOFING	< 95 %, no condensation In accordance with IEC/EN 50178
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V
MODEL	Reversing starter
ALTITUDE	Max. 2000 m Above 1000 m with 1 % performance reduction per 100 m Max. 1000 m
LIFESPAN, MECHANICAL	10,000,000 Operations (at AC-3)
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 60 seconds
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Plug-in connection
MAINS VOLTAGE TOLERANCE	380 - 480 V (-15 %/+10 %, at 50/60 Hz)
VOLTAGE TYPE	DC
MOUNTING POSITION	Vertical
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	10 kA
OVERVOLTAGE CATEGORY	III
CONNECTION	Connections pluggable in power section
OFF-DELAY	20 - 35 ms
FUNCTIONS	For actuation of motors with mechanical brake External reset possible Temperature compensated overload protection
ON-DELAY	20 - 35 ms
SYSTEM CONFIGURATION TYPE	Center-point earthed star network (TN-S network) Phase-earthed AC supply systems are not permitted. AC voltage
BRAKING CURRENT	≤ 0.6 A (max. 6 A for 120 ms), Actuator for external motor brake
ELECTROMAGNETIC COMPATIBILITY	Class A

CURRENT LIMITATION	0.3 - 6.6 A, motor, main circuit Adjustable, motor, main circuit
OUTPUT FREQUENCY	50/60 Hz
BRAKING VOLTAGE	400/480 V AC -15 % / +10 %, Actuator for external motor brake
OVERLOAD CYCLE	AC-53a
OVERLOAD RELEASE CURRENT SETTING - MIN	0.3 A
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ), TYPE 2, 230 V	0 A
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ), TYPE 2, 380 V, 400 V, 415 V	0 A
RATED CONDITIONAL SHORT-CIRCUIT CURRENT, TYPE 1, 480 V/277 V	10000 A
RATED CONDITIONAL SHORT-CIRCUIT CURRENT, TYPE 1, 600 V/347 V	0 A
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	0 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	0 V
RATED FREQUENCY - MAX	63 Hz
RATED FREQUENCY - MIN	47 Hz
RATED OPERATIONAL CURRENT (IE) AT 150% OVERLOAD	6.6 A

RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	6.6 A
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, 11 ms, Half-sinusoidal shock 11 ms, 1000 shocks per shaft
INTERFACES	Specification: S-7.A.E. (AS-Interface®) Number of slave addresses: 62 (AS-Interface®) Max. total power consumption from AS-Interface® power supply unit (30 V): 190 mA
PROTOCOL	AS-Interface profile cable: S-7.4 for 62 modules ASI
RATED CONTROL VOLTAGE (UC)	24 V DC (-15 %/+20 %, external via AS-Interface® plug) 400/480 V AC (external brake 50/60 Hz)
SUPPLY FREQUENCY	50/60 Hz, fLN, Main circuit
RATED OPERATIONAL CURRENT (IE)	6.6 A
RATED OPERATIONAL POWER AT 380/400 V, 50 HZ - MAX	3 kW
RATED OPERATIONAL POWER AT 380/400 V, 50 HZ - MIN	0.09 kW
RATED OPERATIONAL VOLTAGE	400 V AC, 3-phase 480 V AC, 3-phase
SHORT-CIRCUIT PROTECTION (EXTERNAL OUTPUT CIRCUITS)	Type 1 coordination via the power bus' feeder unit, Main circuit
VIBRATION	Resistance: 10 - 150 Hz, Oscillation frequency Resistance: 6 Hz, Amplitude 0.15 mm Resistance: According to IEC/EN 60068-2-6 Resistance: 57 Hz, Amplitude transition frequency on acceleration
AMBIENT OPERATING TEMPERATURE - MAX	55 °C
AMBIENT OPERATING	-10 °C

TEMPERATURE - MIN	
AMBIENT STORAGE TEMPERATURE - MAX	70 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	3 HP
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF COMMAND POSITIONS	2
NUMBER OF PILOT LIGHTS	0
OVERLOAD RELEASE CURRENT SETTING - MAX	6.6 A
RATED OPERATIONAL POWER AT AC-3, 220/230 V, 50 HZ	0 kW
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	3 kW
RATED POWER AT 460 V, 60 HZ, 3-PHASE	2.238 kW
RATED POWER AT 575 V, 60 HZ, 3-PHASE	0 kW
PRODUCT CATEGORY	Motor starter
CABLE LENGTH	10 m, Radio interference level, maximum motor cable length
COORDINATION CLASS (IEC 60947-4-3)	Class 1
DEGREE OF PROTECTION	NEMA 12 IP65
ELECTRICAL CONNECTION TYPE FOR AUXILIARY- AND CONTROL-CURRENT CIRCUIT	Plug-in connection
INPUT CURRENT	6.6 A (at 150 % Overload)
POWER CONSUMPTION	8 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

