



Eaton 199152

Eaton Moeller® series PKZM0 Motor-protective circuit-breaker, 0.25 kW, 0.63 - 1 A, Push in terminals

□□□□

PRODUCT NAME	Eaton Moeller® series PKZM0 Motor-protective circuit-breaker
CATALOG NUMBER	199152
PRODUCT LENGTH/DEPTH	75 mm
PRODUCT HEIGHT	109 mm
PRODUCT WIDTH	45 mm
PRODUCT WEIGHT	0.3 kg
CERTIFICATIONS	IEC/EN 60947 VDE 0660 UL CSA IEC/EN 60947-4-1 UL 60947-4-1 CSA-C22.2 No. 60947-4-1-14 CE UL File No.: E36332 UL Category Control No.: NLRV CSA File No.: 165628 CSA Class No.: 3211-05

□□□□

USED WITH	Motor starter combinations type MSC...
FEATURES	Phase-failure sensitivity (according to IEC/EN 60947-4-1, VDE 0660 Part 102)
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

□□

DECLARATIONS OF CONFORMITY	eaton-motor-protective-circuit-breaker-declaration-of-conformity-uk251170en.pdf
MCAD MODEL	eaton-motor-protective-circuit-breakers-mcad-3d-models-pkzm0-pi.stp motorschutzschalter_bis_32a_pi.dwg
□□□□□	IL122024ZU
□□	eaton-manual-motor-starters-pkzm-pkzm0-dimensions.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
OPERATING FREQUENCY	40 Operations/h
POLLUTION DEGREE	3
LIFESPAN, MECHANICAL	100,000 Operations
MOUNTING METHOD	DIN rail (top hat rail) mounting optional
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
ACTUATOR TYPE	Turn button
TRIPPING CHARACTERISTIC	Overload trigger: tripping class 10 A
ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MAX	0 A
ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MIN	0 A
ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE - MAX	15.5 A
ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE - MIN	15.5 A
AMBIENT OPERATING	55 °C

TEMPERATURE - MAX	
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	5.33 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	1.8 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
ALTITUDE	Max. 2000 m
DEVICE CONSTRUCTION	Built-in device fixed built-in technique
CONNECTION	Push in terminals
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Spring clamp connection
MOUNTING POSITION	Can be snapped on to IEC/EN 60715 top-hat rail with 7.5 or 15 mm height.
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION	IP20
NUMBER OF POLES	Three-pole
LIFESPAN, ELECTRICAL	100,000 operations
SHOCK RESISTANCE	25 g, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms
FUNCTIONS	Phase failure sensitive Motor protection
SWITCHING CAPACITY	1 A, AC-3 up to 690 V
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY	0

CONTACTS (NORMALLY CLOSED CONTACTS)	
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
OVERLOAD RELEASE CURRENT SETTING - MAX	1 A
OVERLOAD RELEASE CURRENT SETTING - MIN	0.63 A
RATED FREQUENCY - MAX	60 Hz
RATED FREQUENCY - MIN	50 Hz
RATED OPERATIONAL VOLTAGE (UE) - MAX	690 V
RATED OPERATIONAL VOLTAGE (UE) - MIN	690 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	1 A
RATED OPERATIONAL POWER AT AC-3E, 220/230 V, 50 HZ	0.12 kW
RATED OPERATIONAL POWER AT AC-3E, 380/400 V, 50 HZ	0.25 kW
RATED UNINTERRUPTED CURRENT (IU)	1 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
STRIPPING LENGTH (MAIN CABLE)	12 mm
PRODUCT CATEGORY	Motor protective circuit breaker
PROTECTION	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
RATED OPERATIONAL POWER AT AC-3E, 440 V, 50 HZ	0.25 kW
RATED OPERATIONAL POWER AT AC-3E, 500 V, 50 HZ	0.37 kW
RATED OPERATIONAL POWER AT AC-3E, 690 V, 50 HZ	0.55 kW
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU AT 400 V AC	150 kA

RATED SHORT-CIRCUIT BREAKING CAPACITY ICS AT 400 V AC	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU AT 440 V AC	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS AT 440 V AC	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU AT 500 V AC	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS AT 500 V AC	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU AT 690 V AC	150 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS AT 690 V AC	150 kA
SUITABLE FOR	Also motors with efficiency class IE3 Branch circuit: Manual type E if used with terminal, or suitable for group installations, (UL/CSA)
SHORT-CIRCUIT RELEASE	Basic device fixed 15.5 x lu ± 20% tolerance 15.5 A, I _{rm}
TERMINAL CAPACITY (SOLID)	1 x (1 - 6) mm ² , Push-in terminals 2 x (1 - 6) mm ² , Push-in terminals 1 x (1 - 6) mm ² 2 x (1 - 6) mm ²
RATED OPERATIONAL CURRENT (IE)	1 A
TEMPERATURE COMPENSATION	-5 - 40 °C to IEC/EN 60947, VDE 0660 ≤ 0.25 %/K, residual error for T > 40° -25 - 55 °C, Operating range
SHORT-CIRCUIT CURRENT RATING (GROUP PROTECTION)	50 kA, 600 V High Fault, Fuse, SCCR (UL/CSA) with 600 A, 600 V High Fault, Fuse, SCCR (UL/CSA) 50 kA, 600 V High Fault, CB, SCCR (UL/CSA) with 600 A, 600 V High Fault, CB, SCCR (UL/CSA)

SHORT-CIRCUIT CURRENT RATING (TYPE E)	50 kA, 600 Y/347 V, SCCR (UL/CSA)
	65 kA, 240 V, SCCR (UL/CSA)
	65 kA, 480 Y/277 V, SCCR (UL/CSA)
SWITCH OFF TECHNIQUE	Thermomagnetic
POWER LOSS	5.33 W
