



□□□□□

Eaton 199414

Eaton DC1 Variable frequency drive, 230 V AC, 3-phase, 4.3 A, 0.75 kW, IP66/NEMA 4X, Radio interference suppression filter, 7-digit digital display assembly, Local controls, Additional PCB protection, UV resistant, FS1

□□□□

PRODUCT NAME	Eaton DC1 Variable frequency drive
CATALOG NUMBER	199414
PRODUCT LENGTH/DEPTH	162 mm
PRODUCT HEIGHT	232 mm
PRODUCT WIDTH	161 mm
PRODUCT WEIGHT	2.5 kg
CERTIFICATIONS	IEC/EN 61800-5-1 IEC/EN61800-5 UL report applies to both US and Canada CE marking CSA-C22.2 No. 14 UkrSEPRO IEC/EN 61800-3 IEC/EN 61800-2 UL File No.: E172143 UL Listed EAC UL 508C CE UL Category Control No.: NMMS, NMMS7 CUL UL RCM Certified by UL for use in Canada RoHS, ISO 9001
CATALOG NOTES	• Environmental class: 3C3, 3S3 • Overload cycle for 60 s every 600 s • For normal internally and externally

ventilated four-pole
three-phase
asynchronous
motors with 1500
rpm at 50 Hz and
1800 rpm at 60 Hz

Parameterization: Fieldbus

FEATURES

Parameterization:
drivesConnect
Parameterization:
drivesConnect mobile
(App)
Parameterization: Keypad

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

Meets the product standard's requirements.

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 INSCRIPTIONS

Meets the product

	standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Additional PCB protection PC connection IGBT inverter 7-digital display assembly Control unit Internal DC link UV resistance Radio interference suppression filter Local controls
CLIMATIC PROOFING	< 95 average relative humidity (RH), no condensation, no corrosion
CONNECTION TO SMARTWIRE-DT	No
OPERATING MODE	PM motors U/f control Speed control with slip compensation BLDC motors Sensorless vector control (SLV) Synchronous reluctance motors
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	2000 V
FRAME SIZE	FS1

ALTITUDE	Max. 4000 m Above 1000 m with 1 % derating per 100 m
APPLICATION IN DOMESTIC AND COMMERCIAL AREA PERMITTED	Yes
MAINS SWITCH-ON FREQUENCY	Maximum of one time every 30 seconds
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-20 °C
MAINS VOLTAGE - MAX	240 V
OUTPUT VOLTAGE - MAX	250 V
RATED OPERATIONAL POWER AT 220/230 V, 50 HZ, 3-PHASE	0.75 kW
RELATIVE SYMMETRIC NET FREQUENCY TOLERANCE	10 %
RELATIVE SYMMETRIC NET VOLTAGE TOLERANCE	10 %
AMBIENT STORAGE TEMPERATURE - MAX	60 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
APPARENT POWER AT 230 V	1.71 kVA
APPARENT POWER AT 240 V	1.79 kVA
APPLICATION IN INDUSTRIAL AREA PERMITTED	Yes
PRODUCT CATEGORY	Variable frequency drives
PROTECTION	Finger and back-of-hand proof, Protection against direct contact (BGV A3, VBG4)
RESOLUTION	0.1 Hz (Frequency resolution, setpoint value)
VOLTAGE RATING - MAX	240 V
MOUNTING POSITION	Vertical
OVERVOLTAGE CATEGORY	III
COMMUNICATION INTERFACE	Modbus RTU, built in SmartWire-DT, optional CANopen®, built in OP-Bus (RS485), built in
CONVERTER TYPE	U converter

DEGREE OF PROTECTION	NEMA 4X IP66
ASSIGNED MOTOR POWER AT 220/230 V, 60 HZ, 3-PHASE	1 HP
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID	0 W
INPUT CURRENT ILN AT 150% OVERLOAD	5.6 A
MAINS CURRENT DISTORTION	120 %
ASSIGNED MOTOR CURRENT IM AT 220 - 240 V, 60 HZ, 150% OVERLOAD	4.2 A
ASSIGNED MOTOR CURRENT IM AT 230 V, 50 HZ, 150% OVERLOAD	3.2 A
PROTOCOL	CAN EtherNet/IP Other bus systems MODBUS
OVERLOAD CURRENT IL AT 150% OVERLOAD	6.45 A
RATED FREQUENCY - MAX	62 Hz
RATED FREQUENCY - MIN	48 Hz
RATED OPERATIONAL POWER AT 380/400 V, 50 HZ, 3-PHASE	0.75 kW
SYSTEM CONFIGURATION TYPE	AC supply systems with earthed center point
BRAKING CURRENT	≤ 0.6 A (max. 6 A for 120 ms), Actuator for external motor brake
ELECTROMAGNETIC COMPATIBILITY	1st and 2nd environments (according to EN 61800-3)
BRAKING TORQUE	Max. 100 % of rated operational current I _e , variable, DC - Main circuit Max. 30 % MN, Standard - Main circuit
CABLE LENGTH	150 m, unscreened, with motor choke, maximum permissible, Motor feeder 50 m, screened, maximum permissible, Motor feeder 100 m, screened, with motor choke, maximum permissible, Motor feeder

	75 m, unscreened, maximum permissible, Motor feeder
OUTPUT VOLTAGE (U2)	230 V AC, 3-phase 240 V AC, 3-phase
DELAY TIME	< 10 ms, On-delay < 10 ms, Off-delay
NUMBER OF INPUTS (ANALOG)	2 (parameterizable, 0 - 10 V DC, 0/4 - 20 mA)
NUMBER OF INPUTS (DIGITAL)	4 (parameterizable, 10 - 30 V DC)
RADIO INTERFERENCE CLASS	Optional external radio interference suppression filter for longer motor cable lengths and for use in different EMC environments C2, C3: depending on the motor cable length, the connected load, and ambient conditions. External radio interference suppression filters (optional) may be necessary.
NUMBER OF OUTPUTS (DIGITAL)	1
STARTING CURRENT - MAX	175 % I _H
NUMBER OF PHASES (INPUT)	3
NUMBER OF RELAY OUTPUTS	1 (parameterizable, N/O, 6 A (250 V, AC-1) / 5 A (30 V, DC-1))
NUMBER OF PHASES (OUTPUT)	3
POWER CONSUMPTION	39.75 W
RATED CONTROL SUPPLY VOLTAGE	10 V DC (U _s , max. 10 mA)
EFFICIENCY	97 % (η)
SUPPLY FREQUENCY	50/60 Hz
LEAKAGE CURRENT AT GROUND IPE - MAX	7.5 mA
MAINS VOLTAGE - MIN	200 V
NOMINAL OUTPUT CURRENT I_{2N}	2.3 A
NUMBER OF HW- INTERFACES (INDUSTRIAL ETHERNET)	0
NUMBER OF HW- INTERFACES (OTHER)	0

NUMBER OF HW-INTERFACES (PARALLEL)	0
NUMBER OF HW-INTERFACES (RS-232)	0
NUMBER OF HW-INTERFACES (RS-422)	0
NUMBER OF HW-INTERFACES (RS-485)	1
NUMBER OF HW-INTERFACES (SERIAL TTY)	0
NUMBER OF HW-INTERFACES (USB)	0
NUMBER OF INTERFACES (PROFINET)	0
NUMBER OF OUTPUTS (ANALOG)	1
OUTPUT AT LINEAR LOAD AT RATED OUTPUT VOLTAGE - MAX	0.37 kW
OUTPUT AT QUADRATIC LOAD AT RATED OUTPUT VOLTAGE - MAX	0.37 kW
OUTPUT FREQUENCY - MAX	500 Hz
OUTPUT FREQUENCY - MIN	0 Hz
SHORT-CIRCUIT PROTECTION (EXTERNAL OUTPUT CIRCUITS)	Type 1 coordination via the power bus' feeder unit, Main circuit
SUITABLE FOR	Branch circuits, (UL/CSA)
SWITCHING FREQUENCY	8 kHz, 4 - 32 kHz adjustable (audible), fPWM, Power section, Main circuit
RATED OPERATIONAL CURRENT (IE)	4.3 A at 150% overload (at an operating frequency of 6 kHz and an ambient air temperature of +40 °C)
RATED OPERATIONAL VOLTAGE	240 V AC, 3-phase 230 V AC, 3-phase
SHORT-CIRCUIT PROTECTION RATING	6 A, UL (Class CC or J), Safety device (fuse or miniature circuit-breaker), Power Wiring
HEAT DISSIPATION AT CURRENT/SPEED	26.55 W at 25% current and 0% speed 27.04 W at 100% current and 0% speed 27.11 W at 50% current and 0% speed 30.8 W at 25% current and 50% speed

31.78 W at 50% current
and 50% speed
36.5 W at 50% current and
90% speed
39.99 W at 100% current
and 50% speed
46.1 W at 100% current
and 90% speed

□□

DECLARATIONS
OF
CONFORMITY [eaton-variable-frequency-drive-
declaration-of-conformity-
uk251078en.pdf](#)

INSTALLATION
VIDEOS [Video PowerXL DA1](#)

MCAD MODEL [e3_s1_ip66_mit_bedienelementen.stp](#)
[e3_s1_ip66_mit_bedienelementen.dwg](#)

□□□□ [eaton-powerxl-variable-frequency-
drives-dc1-da1-brochure-br040001en-
en-us.pdf](#)

□□ [eaton-frequency-inverter-dc1-
dimensions.eps](#)

□□□□□□ [The OP System Bus - Parameterizing -
Control](#)

[DX-COM-STICK3 Connection](#)
[How does the internal motor
protection work?](#)

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

□□:



□□□□
Eaton House
30 Pembroke Road
Dublin 4, □□□
Eaton.com

© 2025 □□ □□□□□□□□

Follow us on social media to get the
latest product and support
information.

