

Eaton 199201

Eaton Moeller® series PKZM0 Motor-protective circuit-breaker, 9 kW, 16 - 20 A, Feed-side screw terminals/output-side push-in terminals, MSC

PRODUCT NAME	Eaton Moeller® series PKZM0 Motor-protective circuit-breaker
CATALOG NUMBER	199201
PRODUCT LENGTH/DEPTH	75 mm
PRODUCT HEIGHT	102 mm
PRODUCT WIDTH	45 mm
PRODUCT WEIGHT	0.323 kg
CERTIFICATIONS	IEC/EN 60947 VDE 0660 UL File No.: E36332 IEC/EN 60947-4-1 CSA File No.: 165628 UL Category Control No.: NLRV UL CSA-C22.2 No. 60947-4-1-14 CSA Class No.: 3211-05 CSA UL 60947-4-1 CE

USED WITH	Motor starter combinations type MSC...
FEATURES	Phase-failure sensitivity (according to IEC/EN 60947-4-1, VDE 0660 Part 102)
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.

MCAD MODEL	pkzm0_s32_pi.dwg
	pkzm0_s32_pi.stp
	IL122024ZU
	eaton-manual-motor-starters-pkzm-pkzm0-dimensions-003.eps

10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
OPERATING FREQUENCY	40 Operations/h
POLLUTION DEGREE	3
MOUNTING METHOD	DIN rail (top hat rail) mounting optional
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
ACTUATOR TYPE	Turn button
TRIPPING CHARACTERISTIC	Overload trigger: tripping class 10 A
ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MAX	0 A
ADJUSTMENT RANGE SHORT-TERM DELAYED SHORT-CIRCUIT RELEASE - MIN	0 A
ADJUSTMENT RANGE UNDELAYED SHORT-CIRCUIT RELEASE - MAX	310 A
ADJUSTMENT RANGE	310 A

UNDELAYED SHORT-CIRCUIT RELEASE - MIN	
AMBIENT OPERATING TEMPERATURE - MAX	55 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE	1.5 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	5 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	3 HP
ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE	15 HP
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	5.82 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	1.9 W
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
ALTITUDE	Max. 2000 m
DEVICE CONSTRUCTION	Built-in device fixed built-in technique
CONNECTION	Push-in terminals on output side Screw terminals on feed side
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw-/spring clamp connection

MOUNTING POSITION	Can be snapped on to IEC/EN 60715 top-hat rail with 7.5 or 15 mm height.
LIFESPAN, MECHANICAL	100,000 Operations
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION	Terminals: IP00 IP20
NUMBER OF POLES	Three-pole
LIFESPAN, ELECTRICAL	100,000 operations
SHOCK RESISTANCE	25 g, Mechanical, according to IEC/EN 60068-2-27, Half-sinusoidal shock 10 ms
FUNCTIONS	Motor protection Phase failure sensitive
TERMINAL CAPACITY (SOLID/STRANDED AWG)	18 - 10, screw terminals 18 - 8, Push-in terminals
SWITCHING CAPACITY	20 A, AC-3 up to 690 V
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
OVERLOAD RELEASE CURRENT SETTING - MAX	20 A
OVERLOAD RELEASE CURRENT SETTING - MIN	16 A
RATED FREQUENCY - MAX	60 Hz
RATED FREQUENCY - MIN	50 Hz
RATED OPERATIONAL VOLTAGE (UE) - MAX	690 V
RATED OPERATIONAL VOLTAGE (UE) - MIN	690 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	20 A
RATED OPERATIONAL POWER AT AC-3E, 220/230 V, 50 HZ	5.5 kW
RATED OPERATIONAL POWER AT AC-3E, 380/400 V, 50 HZ	9 kW

RATED UNINTERRUPTED CURRENT (IU)	20 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
STRIPPING LENGTH (MAIN CABLE)	12 mm
PRODUCT CATEGORY	Motor protective circuit breaker
PROTECTION	Finger and back-of-hand proof, Protection against direct contact when actuated from front (EN 50274)
RATED OPERATIONAL POWER AT AC-3E, 440 V, 50 HZ	11 kW
RATED OPERATIONAL POWER AT AC-3E, 500 V, 50 HZ	12.5 kW
RATED OPERATIONAL POWER AT AC-3E, 690 V, 50 HZ	15 kW
TERMINAL CAPACITY (FLEXIBLE WITH UNISOLATED FERRULE)	1 x (1 - 6) mm ² , Screw terminals 2 x (1 - 6) mm ² , Screw terminals 1 x (1 - 6) mm ² , Push-in terminals 2 x (1 - 6) mm ² , Push-in terminals
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU AT 400 V AC	50 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS AT 400 V AC	38 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU AT 440 V AC	10 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS AT 440 V AC	3 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICU AT 500 V AC	3 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS AT 500 V AC	3 kA

RATED SHORT-CIRCUIT BREAKING CAPACITY ICU AT 690 V AC	3 kA
RATED SHORT-CIRCUIT BREAKING CAPACITY ICS AT 690 V AC	1 kA
TERMINAL CAPACITY (FLEXIBLE WITH ULTRASONIC WELDED CABLE END)	1 x (1 - 10) mm ² 2 x (1 - 6) mm ² 1 x (1 - 6) mm ² , Screw terminals 2 x (1 - 6) mm ² , Screw terminals 1 x (1 - 10) mm ² , Push-in terminals 2 x (1 - 6) mm ² , Push-in terminals
SUITABLE FOR	Also motors with efficiency class IE3 Branch circuit: Manual type E in combination with contactor DILM and terminal BK25/3-PKZ0-E, or suitable for group installations, (UL/CSA)
SHORT-CIRCUIT RELEASE	Basic device fixed 15.5 x lu ± 20% tolerance 310 A, I _{rm}
TERMINAL CAPACITY (SOLID)	1 x (1 - 6) mm ² , Screw terminals 2 x (1 - 6) mm ² , Screw terminals 1 x (1 - 6) mm ² , Push-in terminals 2 x (1 - 6) mm ² , Push-in terminals
RATED OPERATIONAL CURRENT (IE)	20 A
TEMPERATURE COMPENSATION	≤ 0.25 %/K, residual error for T > 40° -5 - 40 °C to IEC/EN 60947, VDE 0660 -25 - 55 °C, Operating range
SHORT-CIRCUIT CURRENT RATING (GROUP PROTECTION)	10 kA, 600 V High Fault, Fuse, SCCR (UL/CSA) with 150 A, 600 V High Fault, Fuse, SCCR (UL/CSA) 10 kA, 600 V High Fault, CB, SCCR (UL/CSA) with 125 A, 600 V High Fault, CB, SCCR (UL/CSA) 18 kA, 600 V High Fault,

	Fuse with CL, SCCR (UL/CSA) with 600 A, 600 V High Fault, Fuse with CL, SCCR (UL/CSA) 18 kA, 600 V High Fault, CB with CL, SCCR (UL/CSA) with 600 A, 600 V High Fault, CB with CL, SCCR (UL/CSA) 18 kA, 480 V High Fault, CB, SCCR (UL/CSA) with 600 A, 480 V High Fault, CB, SCCR (UL/CSA) 18 kA, 480 V High Fault, Fuse, SCCR (UL/CSA) with 600 A, 480 V High Fault, Fuse, SCCR (UL/CSA)
SHORT-CIRCUIT CURRENT RATING (TYPE E)	18 kA, 240 V, SCCR (UL/CSA) with contactor DILM25 18 kA, 480 Y/277 V, SCCR (UL/CSA) with contactor DILM25
TIGHTENING TORQUE	1.7 Nm, Screw terminals, Main cable
SWITCH OFF TECHNIQUE	Thermomagnetic
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (1 - 6) mm², Screw terminals 2 x (1 - 6) mm², Screw terminals 1 x (1 - 6) mm², Push-in terminals, ferrule to DIN 46228-1 2 x (1 - 6) mm², Push-in terminals, ferrule to DIN 46228-1 1 x (1 - 6) mm², Push-in terminals, ferrule to DIN 46228-4 2 x (1 - 4) mm², Push-in terminals, ferrule to DIN 46228-4
TERMINAL CAPACITY (FLEXIBLE)	1 x (1 - 6) mm², Push-in terminals 2 x (1 - 6) mm², Push-in terminals 1 x (1 - 6) mm², Screw terminals 2 x (1 - 6) mm², Screw terminals
POWER LOSS	5.82 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com
© 2025

Follow us on social media to get the latest product and support information.

