

Eaton 199324

Eaton Moeller® series DILA Auxiliary contact module, 1 pole, Ith= 16 A, 1 NC, Side mounted, Push in terminals, DILA, DILM7 - DILM15

PRODUCT NAME	Eaton Moeller® series DILA Accessory Auxiliary contact module
CATALOG NUMBER	199324
PRODUCT LENGTH/DEPTH	47 mm
PRODUCT HEIGHT	72 mm
PRODUCT WIDTH	16 mm
PRODUCT WEIGHT	0.02 kg
CERTIFICATIONS	IEC/EN 60947 VDE 0660 CSA File No.: 012528 CSA Class No.: 3211-03 UL File No.: E29184 UL 508 CSA-C22.2 No. 14-05 CE marking UL CSA UL Category Control No.: NKCR

TYPE	Side-mounting auxiliary contacts
FEATURES	Interlocked opposing contacts within an auxiliary contact module (according to IEC 60947-5-1 Annex L)
ELECTRIC CONNECTION TYPE	Spring clamp connection
FITTED WITH:	Interlocked opposing contacts
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
CONVENTIONAL THERMAL CURRENT ITH AT 60°C (3-POLE, OPEN)	16 A
CONVENTIONAL THERMAL CURRENT ITH OF AUXILIARY CONTACTS (1-POLE, OPEN)	0.1 A
NUMBER OF CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF SWITCHES (FAULT SIGNAL)	0

DECLARATIONS OF CONFORMITY	eaton-accessory-declaration-of-conformity-uk251276en.pdf
MCAD MODEL	dil_a_xhi_s_pi.dwg eaton-contact-blocks-mcad-3d-models-dil-a-xhi-4-pi.stp IL03407151Z2021_06.pdf eaton-contactors-dimensions-007.eps

RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
CONNECTION TYPE	Push in terminals
MOUNTING METHOD	Side mounting
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	$\lambda < 5 \times 1/10^7$ (1 failure at 2,000,000 operations for $U_e = 24$ V DC, $U_{min} = 17$ V, $I_{min} = 5.4$ mA)
DEGREE OF PROTECTION	IP20
MODEL	Top mounting
LAMP HOLDER	None
FUNCTIONS	For standard applications
SAFE ISOLATION	400 V AC, Between coil and auxiliary contacts, According to EN 61140 400 V AC, Between auxiliary contacts, According to EN 61140
RATED OPERATIONAL CURRENT (IE)	3 A at 110 V, DC L/R ≤ 15 ms (with 1 contact in series) 1 A at 220 V, DC L/R ≤ 15 ms (with 1 contact in series) 10 A at 24 V, DC L/R ≤ 15 ms (with 1 contact in series) 6 A at 60 V, DC L/R ≤ 15 ms (with 1 contact in series)
LIFESPAN, ELECTRICAL	1,300,000 Operations (at 230 V, AC-15, 3 A)
TERMINAL CAPACITY (FLEXIBLE WITH UNISOLATED FERRULE)	1 x (0.5 - 2.5) mm ² 2 x (0.5 - 2.5) mm ²
TERMINAL CAPACITY (FLEXIBLE WITH ULTRASONIC WELDED CABLE END)	1 x (0.5 - 2.5) mm ² 2 x (0.5 - 2.5) mm ²
SWITCHING CAPACITY (AUXILIARY CONTACTS, GENERAL USE)	10 A, 600 V AC, (UL/CSA) 1 A, 250 V DC, (UL/CSA)
SWITCHING CAPACITY (AUXILIARY CONTACTS, PILOT DUTY)	A600, AC operated (UL/CSA) P300, DC operated (UL/CSA)
PROTECTION	Finger and back-of-hand proof, Protection against

	direct contact when actuated from front (EN 50274)
NUMBER OF POLES	Single-pole
SHORT-CIRCUIT PROTECTION RATING WITHOUT WELDING	10 A gG/gL, 500 V, Max. Fuse, Contacts
RATED INSULATION VOLTAGE (UI)	690 V
RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V	4 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 380 V, 400 V, 415 V	4 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 500 V	1.5 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 110 V	0.5 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 220 V, 230 V	0.25 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 24 V	2.5 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 60 V	1 A
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	500 V
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	1 x (0.5 - 1.5) mm ² 2 x (0.5 - 1.5) mm ²
TERMINAL CAPACITY (SOLID)	1 x (0.5 - 2.5) mm ² 2 x (0.5 - 2.5) mm ²
TERMINAL CAPACITY (SOLID/STRANDED AWG)	20 - 14
TERMINAL CAPACITY (FLEXIBLE)	1 x (0.5 - 2.5) mm ² 2 x (0.5 - 2.5) mm ²

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

