



□□□□□

Eaton 200N20

Eaton Bussmann series low voltage british standard fuse, 200A, AC 660 V, 49 x 110 mm, gL/gG

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	200N20
PRODUCT LENGTH/DEPTH	52 mm
PRODUCT HEIGHT	52 mm
PRODUCT WIDTH	136 mm
PRODUCT WEIGHT	478 g
COMPLIANCES	CE RoHS Compliant
CERTIFICATIONS	BS88-2 IEC 60269-2

□□□□

AMPERAGE RATING	200 A
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	92.5 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	660 V
CLASS	Class gG/gL
FUSE TYPE	N20
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	15 W
CONNECTION	92.5 mm fixing centre
CONSTRUCTION	BS88
CONSTRUCTION SIZE	Other
FUSE SHAPE	Offset bolted tags
VOLTAGE TYPE	AC
VOLTAGE RATING	660 V
TYPE	Fuse
APPLICATION	industrial
FUSE SYSTEM (ACCORDING TO IEC 60269)	Other

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-british-
standard-fuse-declaration-
of-conformity-
uk250881en.pdf](#)

