



00000

Eaton 207084

Eaton Moeller® series T0 Panic switches, T0, 20 A, surface mounting, 3 pole, with black thumb grip and front plate, Cylinder lock SVA

00000

PRODUCT NAME	Eaton Moeller® series T0 Panic switch
CATALOG NUMBER	207084
PRODUCT LENGTH/DEPTH	137 mm
PRODUCT HEIGHT	102 mm
PRODUCT WIDTH	80 mm
PRODUCT WEIGHT	0.396 kg
CERTIFICATIONS	IEC/EN 60947 VDE 0660 IEC/EN 60204 IEC/EN 60947-3

□□□□

TYPE	Panic switch
PRODUCT CATEGORY	Switch with locking mechanism
ACTUATOR COLOR	Black
ACTUATOR FUNCTION	Maintained
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	UV resistance only in connection with protective shield.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

□□

DECLARATIONS OF CONFORMITY	eaton-step-switch-declaration-of-conformity-uk251327en.pdf
MCAD MODEL	t0zz59.stp
□□□□□	IL03801015Z
□□□	eaton-rotary-switches-on-off-switch-p3-main-switch-wiring-diagram.eps
□□	eaton-rotary-switches-front-plate-t0-on-off-switch-symbol-002.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Black thumb grip and front plate
OPERATING FREQUENCY	1200 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
RATED OPERATIONAL POWER STAR-DELTA AT 500 V, 50 Hz	7.5 kW
RATED OPERATIONAL POWER STAR-DELTA AT 690 V, 50 Hz	5.5 kW
RATED PERMANENT CURRENT AT AC-21, 400 V	20 A
RATED PERMANENT CURRENT AT AC-23, 400 V	13.3 A
RATED UNINTERRUPTED CURRENT (IU)	20 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W

SWITCHING ANGLE	90 °
SWITCHING POWER AT 400 V	5.5 kW
VOLTAGE PER CONTACT PAIR IN SERIES	60 V
ACCESSORIES	2 keys included with supplied equipment.
RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ	5.5 kW
DEVICE CONSTRUCTION	Complete device in housing
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0.32 kA 320 A, Contacts, 1 second
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
DESIGN	1
MOUNTING POSITION	As required
ACTUATOR TYPE	Short thumb-grip
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0.6 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0.6 W
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	0
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	6 kA
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT	1 failure per 100,000

RELIABILITY	switching operations statistically determined, at 24 V DC, 10 mA)
DEGREE OF PROTECTION (FRONT SIDE)	IP65
NUMBER OF POLES	3
MOUNTING METHOD	Surface mounting
DEGREE OF PROTECTION	NEMA 12
SUITABLE FOR	Ground mounting
LOCKING FACILITY	Lockable in the 0 (Off) position (cover interlock)
FUNCTIONS	Interlockable
NUMBER OF SWITCHES	1
SAFE ISOLATION	440 V AC, Between the contacts, According to EN 61140
SCREW SIZE	M3.5, Terminal screw
INSCRIPTION	0-1
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
LIFESPAN, MECHANICAL	400,000 Operations
LOCKING MECHANISM	Cylinder lock SVA
LOAD RATING	2 x I _e (with intermittent operation class 12, 25 % duty factor) 1.6 x I _e (with intermittent operation class 12, 40 % duty factor) 1.3 x I _e (with intermittent operation class 12, 60 % duty factor)
TERMINAL CAPACITY	2 x (0.75 - 2.5) mm ² , flexible with ferrules to DIN 46228 2 x (1 - 2.5) mm ² , solid or stranded 1 x (1 - 2.5) mm ² , solid or stranded 1 x (0.75 - 2.5) mm ² , flexible with ferrules to DIN 46228
SAFETY PARAMETER (EN ISO 13849-1)	B10d values as per EN ISO 13849-1, table C.1
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	0
NUMBER OF CONTACT UNITS	2
NUMBER OF CONTACTS	1

IN SERIES AT DC-21A, 240

V

NUMBER OF CONTACTS

IN SERIES AT DC-23A, 120 3

V

NUMBER OF CONTACTS

IN SERIES AT DC-23A, 24 V 1

NUMBER OF CONTACTS

IN SERIES AT DC-23A, 240 5

V

NUMBER OF CONTACTS

IN SERIES AT DC-23A, 48 V 2

NUMBER OF CONTACTS

IN SERIES AT DC-23A, 60 V 3

RATED BREAKING

CAPACITY AT 220/230 V 100 A

(COS PHI TO IEC 60947-3)

RATED BREAKING

CAPACITY AT 400/415 V 110 A

(COS PHI TO IEC 60947-3)

RATED BREAKING

CAPACITY AT 500 V (COS 80 A

PHI TO IEC 60947-3)

RATED BREAKING

CAPACITY AT 660/690 V 60 A

(COS PHI TO IEC 60947-3)

RATED MAKING

CAPACITY UP TO 690 V 130 A

(COS PHI TO IEC/EN

60947-3)

RATED OPERATING

VOLTAGE (UE) - MAX 690 V

RATED OPERATING

VOLTAGE (UE) - MIN 690 V

RATED OPERATIONAL

VOLTAGE (UE) AT AC - 690 V

MAX

SHORT-CIRCUIT

PROTECTION RATING 20 A gG/gL, Fuse, Contacts

RATED OPERATIONAL

CURRENT (IE) AT AC-21, 20 A

440 V

RATED OPERATIONAL

CURRENT (IE) AT AC-23A, 13.3 A

230 V

RATED OPERATIONAL

CURRENT (IE) AT AC-23A, 13.3 A

400 V, 415 V

RATED OPERATIONAL

CURRENT (IE) AT AC-23A, 13.3 A

500 V

RATED OPERATIONAL

CURRENT (IE) AT AC-23A, 7.6 A

**CURRENT (IE) AT AC-23A,
690 V**

RATED OPERATIONAL

**CURRENT (IE) AT AC-3,
220 V, 230 V, 240 V**

RATED OPERATIONAL

**CURRENT (IE) AT AC-3,
380 V, 400 V, 415 V**

RATED OPERATIONAL

**CURRENT (IE) AT AC-3,
500 V**

RATED OPERATIONAL

**CURRENT (IE) AT AC-3,
660 V, 690 V**

RATED OPERATIONAL

**CURRENT (IE) AT DC-1,
LOAD-BREAK SWITCHES
L/R = 1 MS**

RATED OPERATIONAL

**CURRENT (IE) AT DC-13,
CONTROL SWITCHES L/R
= 50 MS**

RATED OPERATIONAL

**CURRENT (IE) AT DC-21,
240 V**

RATED OPERATIONAL

**CURRENT (IE) AT DC-23A,
120 V**

RATED OPERATIONAL

**CURRENT (IE) AT DC-23A,
24 V**

RATED OPERATIONAL

**CURRENT (IE) AT DC-23A,
240 V**

RATED OPERATIONAL

**CURRENT (IE) AT DC-23A,
48 V**

RATED OPERATIONAL

**CURRENT (IE) AT DC-23A,
60 V**

RATED OPERATIONAL

**CURRENT (IE) STAR-
DELTA AT AC-3, 220/230 V**

RATED OPERATIONAL

**CURRENT (IE) STAR-
DELTA AT AC-3, 380/400 V**

RATED OPERATIONAL

**CURRENT (IE) STAR-
DELTA AT AC-3, 500 V**

RATED OPERATIONAL

**CURRENT (IE) STAR-
DELTA AT AC-3, 690 V**

RATED OPERATIONAL

20 A

**CURRENT FOR SPECIFIED
HEAT DISSIPATION (IN)**

RATED OPERATIONAL

POWER AT AC-23A, 220/230 V, 50 Hz 3 kW

RATED OPERATIONAL

POWER AT AC-23A, 400 V, 50 Hz 5.5 kW

RATED OPERATIONAL

POWER AT AC-23A, 500 V, 50 Hz 7.5 kW

RATED OPERATIONAL

POWER AT AC-23A, 690 V, 50 Hz 5.5 kW

RATED OPERATIONAL

POWER AT AC-3, 380/400 V, 50 Hz 5.5 kW

RATED OPERATIONAL

POWER AT AC-3, 415 V, 50 Hz 5.5 kW

RATED OPERATIONAL

POWER AT AC-3, 690 V, 50 Hz 4 kW

RATED OPERATIONAL

POWER STAR-DELTA AT 220/230 V, 50 Hz 5.5 kW

RATED OPERATIONAL

POWER STAR-DELTA AT 380/400 V, 50 Hz 7.5 kW

TIGHTENING TORQUE

8.8 lb-in, Screw terminals
1 Nm, Screw terminals

UNINTERRUPTED CURRENT

Rated uninterrupted current I_u is specified for max. cross-section.

HOUSING COLOR

Black

HOUSING MATERIAL

Plastic

□□□□:

□□□□:

□□□:

□□: