



## Eaton 199544

Eaton Main switch, 40 A, surface mounting, 3 pole, Emergency switching off function, With red rotary handle and yellow locking ring, Lockable in the 0 (Off) position



<b>PRODUCT NAME</b>	Eaton J-Range enclosed switch-disconnector
<b>CATALOG NUMBER</b>	199544
<b>PRODUCT LENGTH/DEPTH</b>	115 mm
<b>PRODUCT HEIGHT</b>	180 mm
<b>PRODUCT WIDTH</b>	100 mm
<b>PRODUCT WEIGHT</b>	0.447 kg
<b>CERTIFICATIONS</b>	VDE 0660 IEC/EN 60947 IEC/EN 60947-3 IEC/EN 60204
<b>CATALOG NOTES</b>	Rated Short-time Withstand Current (Icw) for a time of 1 second



Powering Business Worldwide

<b>PRODUCT CATEGORY</b>	Main switch
<b>FEATURES</b>	Version as emergency stop installation Version as main switch Version as safety switch Version as maintenance- /service switch
<b>ACTUATOR COLOR</b>	Red
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	UV resistance only in connection with protective shield.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.

DECLARATIONS OF CONFORMITY	<a href="#">eaton-enclosed-switch-disconnector-declaration-of-conformity-uk251001en.pdf</a>
□□□□□	<a href="#">IL008060ZU</a>

<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Red rotary handle and yellow locking ring Assembly sheet screen Push-through cable entry diaphragm
<b>OPERATING FREQUENCY</b>	1200 Operations/h
<b>POLLUTION DEGREE</b>	3
<b>CLIMATIC PROOFING</b>	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
<b>RATED IMPULSE WITHSTAND VOLTAGE (UIMP)</b>	6000 V AC
<b>RATED PERMANENT CURRENT AT AC-21, 400 V</b>	40 A
<b>RATED UNINTERRUPTED CURRENT (IU)</b>	40 A
<b>VOLTAGE PER CONTACT PAIR IN SERIES</b>	60 V
<b>DEVICE CONSTRUCTION</b>	Complete device in housing
<b>RATED SHORT-TIME WITHSTAND CURRENT (ICW)</b>	0.64 kA 640 A, Contacts, 1 second

<b>ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT</b>	Screw connection
<b>MOUNTING POSITION</b>	As required
<b>ACTUATOR TYPE</b>	Door coupling rotary drive
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX</b>	40 °C
<b>AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN</b>	-25 °C
<b>NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)</b>	0
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)</b>	0
<b>RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)</b>	80 kA
<b>OVERVOLTAGE CATEGORY</b>	III
<b>DEGREE OF PROTECTION (FRONT SIDE)</b>	IP65
<b>NUMBER OF POLES</b>	Three-pole
<b>MOUNTING METHOD</b>	Surface mounting
<b>DEGREE OF PROTECTION</b>	NEMA 12
<b>SUITABLE FOR</b>	Ground mounting
<b>LOCKING FACILITY</b>	Lockable in the 0 (Off) position
<b>FUNCTIONS</b>	Interlockable Emergency switching off function
<b>NUMBER OF SWITCHES</b>	1
<b>SAFE ISOLATION</b>	440 V AC, Between the contacts, According to EN 61140
<b>SCREW SIZE</b>	M4, Terminal screw
<b>SHOCK RESISTANCE</b>	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
<b>LIFESPAN, MECHANICAL</b>	300,000 Operations
<b>TERMINAL CAPACITY</b>	2 x (1 - 4) mm <sup>2</sup> , flexible with ferrules to DIN 46228 1 x (1.5 - 10) mm <sup>2</sup> , solid or stranded 1 x (1 - 4) mm <sup>2</sup> , flexible with ferrules to DIN 46228 2 x (1.5 - 6) mm <sup>2</sup> , solid or stranded

<b>SAFETY PARAMETER (EN ISO 13849-1)</b>	B10d values as per EN ISO 13849-1, table C.1
<b>NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)</b>	0
<b>RATED BREAKING CAPACITY AT 220/230 V (COS PHI TO IEC 60947-3)</b>	260 A
<b>RATED BREAKING CAPACITY AT 400/415 V (COS PHI TO IEC 60947-3)</b>	300 A
<b>RATED BREAKING CAPACITY AT 500 V (COS PHI TO IEC 60947-3)</b>	290 A
<b>RATED BREAKING CAPACITY AT 660/690 V (COS PHI TO IEC 60947-3)</b>	250 A
<b>RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947-3)</b>	320 A
<b>RATED OPERATING VOLTAGE (UE) - MAX</b>	690 V
<b>RATED OPERATING VOLTAGE (UE) - MIN</b>	690 V
<b>RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX</b>	690 V
<b>RATED OPERATIONAL CURRENT (IE) AT AC-21, 400 V, 415 V</b>	40 A
<b>SHORT-CIRCUIT PROTECTION RATING</b>	50 A gG/gL, Fuse, Contacts
<b>RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V</b>	40 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-21, 500 V</b>	40 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-21, 690 V</b>	40 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-22, 380 V, 400 V, 415 V</b>	40 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-22, 500 V</b>	40 A
<b>RATED OPERATIONAL CURRENT (IE) AT AC-22, 690 V</b>	40 A
<b>RATED OPERATIONAL</b>	40 A

