

Eaton 200MJ29-6

Eaton Bussmann series low voltage british standard fuse, 200A, AC 415 V, V88/J, 38 x 101 mm, gU

PRODUCT NAME	Eaton Bussmann series low voltage british standard fuse
CATALOG NUMBER	200MJ29-6
PRODUCT LENGTH/DEPTH	110 mm
PRODUCT HEIGHT	42 mm
PRODUCT WIDTH	195 mm
PRODUCT WEIGHT	303.6 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	BS IEC 60269 EAC

AMPERAGE RATING	200 A
FITTED WITH:	Slotted tags
CURRENT TYPE	AC
MOUNTING DIMENSION	M10
CENTER-TO-CENTER DISTANCE OF CONNECTIONS	76 mm
BREAKING CAPACITY	80 kA
RATED SWITCHING CAPACITY	80 kA
RATED VOLTAGE AC	415 V
FUSE TYPE	MJ29
UTILIZATION CATEGORY	gU (utility/distribution protection)
COLOR	None
INTERRUPT RATING	80 kAIC
FUSE INDICATOR	None
INSULATED METAL GRIPPING LUGS (IMGL)	No
WATT LOSSES	16 W
CONNECTION	Bolt-on
CONSTRUCTION	BS88/J
CONSTRUCTION SIZE	J
FUSE SHAPE	Dual slotted bolted tags
VOLTAGE TYPE	AC
VOLTAGE RATING	415 V
TYPE	Fuse
APPLICATION	feeder pillars
FUSE SYSTEM (ACCORDING TO IEC 60269)	Fuse system E

DECLARATIONS OF CONFORMITY	eaton-low-voltage-british- standard-fuse-declaration- of-conformity- uk251033en.pdf

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

