



Eaton 204986

Eaton Moeller® series STN Control transformer, 0.5 kVA, Rated input voltage 400± 5 % V, Rated output voltage 230 V

□□□□

PRODUCT NAME	Eaton Moeller® series STN Control transformer
CATALOG NUMBER	204986
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	124 mm
PRODUCT WIDTH	121 mm
PRODUCT WEIGHT	5.349 kg
CERTIFICATIONS	VDE 0113, VDE 0100 Part 410 VDE 0570 Part 2-2 CSA-C22.2 No. 66.1-06 UL Recognized CSA-C22.2 No. 66 UL Category Control No.: XPTQ2, XPTQ8 UL File No.: E167225 CSA-C22.2 No. 66.2-06 Certified by UL for use in Canada IEC/EN 60204-1, ÖVE-EN 13 UL report applies to both US and Canada CE UL 506 UL5085-1 IEC/EN 61558-2-2 UL 5085-2
CATALOG NOTES	Electrical characteristics: all details for no-load loss, short-circuit loss (copper losses), short-circuit voltage and efficiency values relate to a temperature of 20 °C

TYPE	Single-phase STN control transformers
FEATURES	Fully Vacuum-impregnated Separate windings
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF	Does not apply, since the

DECLARATIONS OF CONFORMITY	eaton-control-transformer-declaration-of-conformity-uk251061en.pdf
SYSTEM OVERVIEW	eaton-general-diagram-sti-control-transformer-explosion-drawing.eps
□□	eaton-general-control-stn-control-transformer-dimensions-013.eps

PROTECTION OF ASSEMBLIES	entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
AMBIENT OPERATING TEMPERATURE - MAX	40 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
APPARENT POWER	500 VA
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
NO-LOAD LOSSES	15 W
PRIMARY VOLTAGE 1 - MAX	400 V
PRIMARY VOLTAGE 1 - MIN	400 V
PRIMARY VOLTAGE 10 - MAX	0 V
PRIMARY VOLTAGE 10 - MIN	0 V
PRIMARY VOLTAGE 2 - MAX	0 V
PRIMARY VOLTAGE 2 - MIN	0 V
PRIMARY VOLTAGE 3 - MAX	0 V

PRIMARY VOLTAGE 3 - MIN	0 V
PRIMARY VOLTAGE 4 - MAX	0 V
PRIMARY VOLTAGE 4 - MIN	0 V
PRIMARY VOLTAGE 5 - MAX	0 V
PRIMARY VOLTAGE 5 - MIN	0 V
PRIMARY VOLTAGE 6 - MAX	0 V
CONDUCTOR MATERIAL	Copper
DEGREE OF PROTECTION	IP00
CONNECTION LUG	Yes for > 115 A
CONNECTION TYPE	Terminations, < 115 A
DUTY FACTOR	100 %
INSULATION MATERIAL TYPE (IEC 85)	B
EFFICIENCY	93 %
RELATIVE SHORT-CIRCUIT VOLTAGE	4.1 %
SUITABLE FOR	Branch circuits, (UL/CSA)
INSULATION CLASS	B
PRIMARY TAPPING	± 5 %
PRIMARY VOLTAGE 6 - MIN	0 V
PRIMARY VOLTAGE 7 - MAX	0 V
PRIMARY VOLTAGE 7 - MIN	0 V
PRIMARY VOLTAGE 8 - MAX	0 V
PRIMARY VOLTAGE 8 - MIN	0 V
PRIMARY VOLTAGE 9 - MAX	0 V
PRIMARY VOLTAGE 9 - MIN	0 V
RATED FREQUENCY - MAX	60 Hz
RATED FREQUENCY - MIN	50 Hz
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
RATED POWER	0.5 VA
SECONDARY VOLTAGE 1 - MAX	230 V

SECONDARY VOLTAGE 1 - MIN	230 V
SECONDARY VOLTAGE 10 - MAX	0 V
SECONDARY VOLTAGE 10 - MIN	0 V
SECONDARY VOLTAGE 2 - MAX	0 V
SECONDARY VOLTAGE 2 - MIN	0 V
SECONDARY VOLTAGE 3 - MAX	0 V
SECONDARY VOLTAGE 3 - MIN	0 V
SECONDARY VOLTAGE 4 - MAX	0 V
PRODUCT CATEGORY	Single-phase control transformers ST
SECONDARY VOLTAGE 4 - MIN	0 V
SECONDARY VOLTAGE 5 - MAX	0 V
SECONDARY VOLTAGE 5 - MIN	0 V
SECONDARY VOLTAGE 6 - MAX	0 V
SECONDARY VOLTAGE 6 - MIN	0 V
SECONDARY VOLTAGE 7 - MAX	0 V
SECONDARY VOLTAGE 7 - MIN	0 V
SECONDARY VOLTAGE 8 - MAX	0 V
SECONDARY VOLTAGE 8 - MIN	0 V
SECONDARY VOLTAGE 9 - MAX	0 V
SECONDARY VOLTAGE 9 - MIN	0 V
SHORT-CIRCUIT LOSSES	27 W
SHORT-TIME RATING	0.88 kVA
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	42 W
VOLTAGE RATING - MAX	600 V
POWER CONSUMPTION IN STANDBY MODE	56 W

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

