



□□□□□

Eaton 207424

Eaton Moeller® series T5B On-Off switch, 6 pole + 1 N/O + 1 N/C, 63 A, 90 °, flush mounting T5B-4-15682/E

□□□□

PRODUCT NAME	Eaton Moeller® series T5B On-off switch
CATALOG NUMBER	207424
PRODUCT LENGTH/DEPTH	141 mm
PRODUCT HEIGHT	88 mm
PRODUCT WIDTH	88 mm
PRODUCT WEIGHT	0.725 kg
CERTIFICATIONS	CSA File No.: 012528 CSA VDE 0660 UL UL Category Control No.: NLRV CSA Class No.: 3211-07 CSA-C22.2 No. 94 UL 60947-4-1 IEC/EN 60204 IEC/EN 60947 CSA-C22.2 No. 60947-4-1-14 IEC/EN 60947-3 UL File No.: E36332 CE
CATALOG NOTES	Rated Short-time Withstand Current (Icw) for a time of 1 second

PRODUCT CATEGORY On-Off switch

ACTUATOR COLOR Black

ACTUATOR FUNCTION Maintained

10.10 TEMPERATURE RISE

The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.

10.11 SHORT-CIRCUIT RATING

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.12 ELECTROMAGNETIC COMPATIBILITY

Is the panel builder's responsibility. The specifications for the switchgear must be observed.

10.13 MECHANICAL FUNCTION

The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.

10.2.2 CORROSION RESISTANCE

Meets the product standard's requirements.

10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES

Meets the product standard's requirements.

10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT

Meets the product standard's requirements.

10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS

Meets the product standard's requirements.

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION

UV resistance only in connection with protective shield.

10.2.5 LIFTING

Does not apply, since the entire switchgear needs to be evaluated.

10.2.6 MECHANICAL IMPACT

Does not apply, since the entire switchgear needs to be evaluated.

10.2.7 INSCRIPTIONS

Meets the product standard's requirements.

10.3 DEGREE OF PROTECTION OF ASSEMBLIES

Does not apply, since the entire switchgear needs to be evaluated.

□□□□□

[IL03801009Z](#)

□□

[eaton-rotary-switches-mounting-t5b-non-standard-switch-dimensions-004.eps](#)

[eaton-rotary-switches-front-plate-t0-on-off-switch-symbol-002.eps](#)

10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Black thumb grip and front plate
OPERATING FREQUENCY	1200 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
RATED OPERATIONAL POWER STAR-DELTA AT 500 V, 50 HZ	37 kW
RATED OPERATIONAL POWER STAR-DELTA AT 690 V, 50 HZ	22 kW
RATED PERMANENT CURRENT AT AC-21, 400 V	63 A
RATED PERMANENT CURRENT AT AC-23, 400 V	63 A
RATED UNINTERRUPTED CURRENT (IU)	63 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
SWITCHING ANGLE	90 °
SWITCHING POWER AT 400 V	30 kW

VOLTAGE PER CONTACT PAIR IN SERIES	60 V
RATED OPERATIONAL POWER AT AC-3, 500 V, 50 HZ	22 kW
DEVICE CONSTRUCTION	Built-in device fixed built-in technique
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	1,3 kA, Contacts, 1 second 1.3 kA
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
DESIGN	15682
MOUNTING POSITION	As required
ACTUATOR TYPE	Short thumb-grip
AMBIENT OPERATING TEMPERATURE - MAX	50 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
ASSIGNED MOTOR POWER AT 115/120 V, 60 HZ, 1-PHASE	3 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 1-PHASE	7.5 HP
ASSIGNED MOTOR POWER AT 200/208 V, 60 HZ, 3-PHASE	15 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 1-PHASE	10 HP
ASSIGNED MOTOR POWER AT 230/240 V, 60 HZ, 3-PHASE	15 HP
ASSIGNED MOTOR POWER AT 460/480 V, 60 HZ, 3-PHASE	40 HP
ASSIGNED MOTOR POWER AT 575/600 V, 60 HZ, 3-PHASE	40 HP
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	4.5 W
HEAT DISSIPATION	0 W

CAPACITY PDISS	
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	4.5 W
NUMBER OF AUXILIARY CONTACTS (CHANGE-OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	1
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	2 kA
OVERVOLTAGE CATEGORY	III
CONTROL CIRCUIT RELIABILITY	1 failure per 100,000 switching operations statistically determined, at 24 V DC, 10 mA)
DEGREE OF PROTECTION (FRONT SIDE)	IP65
NUMBER OF POLES	6
MOUNTING METHOD	Flush mounting
DEGREE OF PROTECTION	NEMA 12
SUITABLE FOR	Front mounting 4-hole Branch circuits, suitable as motor disconnect, (UL/CSA)
NUMBER OF SWITCHES	1
SAFE ISOLATION	440 V AC, Between the contacts, According to EN 61140
SCREW SIZE	M6, Terminal screw
INSCRIPTION	0-1
SHOCK RESISTANCE	15 g, Mechanical, According to IEC/EN 60068-2-27, Half-sinusoidal shock 20 ms
LIFESPAN, MECHANICAL	500,000 Operations
LOAD RATING	1.6 x I _e (with intermittent operation class 12, 40 % duty factor) 2 x I _e (with intermittent operation class 12, 25 % duty factor) 1.3 x I _e (with intermittent operation class 12, 60 % duty factor)
TERMINAL CAPACITY	2 x (1.5 - 10) mm ² , flexible with ferrule to DIN 46228 1 x (1 - 25) mm ² , flexible with ferrules to DIN 46228

	12 - 4 AWG, solid or flexible with ferrule 1 x (2.5 - 35) mm², solid or stranded 2 x (2.5 - 16) mm², solid or stranded
SWITCHING CAPACITY (MAIN CONTACTS, GENERAL USE)	63 A, Rated uninterrupted current max. (UL/CSA)
SAFETY PARAMETER (EN ISO 13849-1)	B10d values as per EN ISO 13849-1, table C.1
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF CONTACT UNITS	4
NUMBER OF CONTACTS IN SERIES AT DC-23A, 120 V	3
NUMBER OF CONTACTS IN SERIES AT DC-23A, 24 V	1
NUMBER OF CONTACTS IN SERIES AT DC-23A, 240 V	6
NUMBER OF CONTACTS IN SERIES AT DC-23A, 48 V	2
NUMBER OF CONTACTS IN SERIES AT DC-23A, 60 V	3
RATED BREAKING CAPACITY AT 220/230 V (COS PHI TO IEC 60947-3)	520 A
RATED BREAKING CAPACITY AT 400/415 V (COS PHI TO IEC 60947-3)	600 A
RATED BREAKING CAPACITY AT 500 V (COS PHI TO IEC 60947-3)	480 A
RATED BREAKING CAPACITY AT 660/690 V (COS PHI TO IEC 60947-3)	340 A
RATED MAKING CAPACITY UP TO 690 V (COS PHI TO IEC/EN 60947-3)	800 A
RATED OPERATING VOLTAGE (UE) - MAX	690 V
RATED OPERATING VOLTAGE (UE) - MIN	690 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	690 V
SHORT-CIRCUIT CURRENT	10 kA, SCCR (UL/CSA)

RATING (HIGH FAULT)	100 A, Class J, max. Fuse, SCCR (UL/CSA)
SHORT-CIRCUIT PROTECTION RATING	80 A gG/gL, Fuse, Contacts
RATED OPERATIONAL CURRENT (IE) AT AC-21, 440 V	63 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 230 V	63 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 400 V, 415 V	63 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 500 V	33 A
RATED OPERATIONAL CURRENT (IE) AT AC-23A, 690 V	23.8 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 220 V, 230 V, 240 V	51 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 380 V, 400 V, 415 V	41 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 500 V	33 A
RATED OPERATIONAL CURRENT (IE) AT AC-3, 660 V, 690 V	17 A
RATED OPERATIONAL CURRENT (IE) AT DC-1, LOAD-BREAK SWITCHES L/R = 1 MS	63 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, CONTROL SWITCHES L/R = 50 MS	25 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 120 V	25 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 24 V	50 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 240 V	20 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A, 48 V	50 A
RATED OPERATIONAL CURRENT (IE) AT DC-23A,	50 A

60 V	
RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 220/230 V	63 A
RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 380/400 V	63 A
RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 500 V	57.2 A
RATED OPERATIONAL CURRENT (IE) STAR-DELTA AT AC-3, 690 V	29.4 A
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	63 A
RATED OPERATIONAL POWER AT AC-23A, 220/230 V, 50 HZ	18.5 kW
RATED OPERATIONAL POWER AT AC-23A, 400 V, 50 HZ	30 kW
RATED OPERATIONAL POWER AT AC-23A, 500 V, 50 HZ	22 kW
RATED OPERATIONAL POWER AT AC-23A, 690 V, 50 HZ	22 kW
RATED OPERATIONAL POWER AT AC-3, 380/400 V, 50 HZ	22 kW
RATED OPERATIONAL POWER AT AC-3, 415 V, 50 HZ	22 kW
RATED OPERATIONAL POWER AT AC-3, 690 V, 50 HZ	15 kW
RATED OPERATIONAL POWER STAR-DELTA AT 220/230 V, 50 HZ	18.5 kW
RATED OPERATIONAL POWER STAR-DELTA AT 380/400 V, 50 HZ	30 kW
TIGHTENING TORQUE	35.4 lb-in, Screw terminals 4 Nm, Screw terminals
UNINTERRUPTED CURRENT	Rated uninterrupted current I _u is specified for max. cross-section.
RATED SWITCHING CAPACITY	10 HP at 240 V AC, single-phase 15 HP at 200 V AC, three-phase 15 HP at 240 V AC, three-

	phase 3 HP at 120 V AC, single- phase 40 HP at 480 V AC, three- phase 40 HP at 600 V AC, three- phase 7.5 HP at 200 V AC, single- phase
HOUSING COLOR	Black
HOUSING MATERIAL	Plastic



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

