

Eaton 208252

Eaton Moeller® series DILM Replacement coil, RA 250: 110 - 250 V 40-60 Hz/110 - 250 V DC, AC and DC operation, For use with: DILM250, DILM300A

PRODUCT NAME	Eaton Moeller® series DILM replacement coil
CATALOG NUMBER	208252
PRODUCT LENGTH/DEPTH	100 mm
PRODUCT HEIGHT	175 mm
PRODUCT WIDTH	135 mm
PRODUCT WEIGHT	1.19 kg
CERTIFICATIONS	UL 508 CSA-C22.2 No. 14-05 IEC/EN 60947-4-1 CSA Class No.: 3211-04 UL File No.: E29096 CE CSA File No.: 1017510 UL CSA UL Category Control No.: NLDX

ACCESSORIES	
Individual coils	
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.

[IL03407194Z](#) [IL03406002Z](#)

10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
VOLTAGE TYPE	AC/DC
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-40 °C
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MAX	250 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 50 HZ - MIN	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MAX	250 V
RATED CONTROL SUPPLY VOLTAGE (US) AT AC, 60 HZ - MIN	110 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MAX	250 V
RATED CONTROL SUPPLY VOLTAGE (US) AT DC - MIN	110 V
PRODUCT CATEGORY	Accessories

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

