



Eaton 20D16

Eaton Bussmann series low voltage D fuse,
Time-delay, 500V, 20A, 50 kAIC, Non
Indicating, fuse, Class C gL/gG, Time delay,
Holder, Blue, Ceramic body

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage D fuse
CATALOG NUMBER	20D16
UPC	051712832311
PRODUCT LENGTH/DEPTH	50 mm
PRODUCT HEIGHT	13 mm
PRODUCT WIDTH	13 mm
PRODUCT WEIGHT	14.6 g
COMPLIANCES	GoST-R CE Marked RoHS Compliant
CERTIFICATIONS	VDE IEC 60269 DIN EN 60269-3 (VDE 0636 Part 30) DIN EN 60269-1 (VDE 0636 Part 10) DIN VDE 0636-301



Powering Business Worldwide

□□□□

AMPERAGE RATING	20 A
FUSE SIZE	DI
BREAKING CAPACITY	50 kA
CONSTRUCTION SIZE (FUSE INSERTS)	DI
RATED VOLTAGE AC	500 V
CLASS	Class C gL/gG
FUSE TYPE	D16 - Time delay
ACCESSORY/SPARE PART TYPE	20GD16 Blue screw cap gauge piece
UTILIZATION CATEGORY	gL/gG (cable protection/equipment protection)
COLOR	Blue
INTERRUPT RATING	50 kAIC
FUSE INDICATOR	Non-indicating
CONNECTION	Other
CONSTRUCTION	D1
CONSTRUCTION SIZE	DI
FUSE SHAPE	Bottle
RESPONSE TIME	Time-delay
SUITABLE FOR	E16/DI Fuse base
MATERIAL	White ceramic body
MOUNTING METHOD	Holder
RELEASE CHARACTERISTIC	Time-lag
QUANTITY	20
VOLTAGE RATING	500 V
TYPE	fuse
SPECIAL FEATURES	Time-delay
APPLICATION	For domestic and general industrial applications

□□

DECLARATIONS OF
CONFORMITY

[eaton-low-voltage-d-fuse-declaration-of-conformity-uk251016en.pdf](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

