

Eaton 20FE

NOT STAND-SPECIAL ORDER

| | |
|-------------------------|--|
| | |
| PRODUCT NAME | Eaton Bussmann series high speed british standard fuse |
| CATALOG NUMBER | 20FE |
| UPC | 051712832380 |
| PRODUCT LENGTH/DEPTH | 150 mm |
| PRODUCT HEIGHT | 90 mm |
| PRODUCT WIDTH | 150 mm |
| PRODUCT WEIGHT | 39.5 g |
| COMPLIANCES | CE Marked RoHS Compliant |
| CERTIFICATIONS | BS88 IEC 60269 EAC Designed and tested to BS88 part 4 IEC 60269-4 |

| | |
|---|--|
| AMPERAGE RATING | 20 A |
| BREAKING CAPACITY | 200 kA |
| FUSE INDICATOR | None |
| INSULATED METAL GRIPPING LUGS (IMGL) | No |
| UTILIZATION CATEGORY | aR (accompanied semiconductor protection) |
| VOLTAGE TYPE | AC/DC |
| RATED SWITCHING CAPACITY | 200 kA |
| RATED VOLTAGE AC | 690 V |
| RATED VOLTAGE DC | 500 V |
| CENTER-TO-CENTER DISTANCE OF CONNECTIONS | 62 mm |
| MOUNTING DIMENSION | M6 |
| CURRENT TYPE | AC/DC |
| CLASS | Class aR |
| FUSE SHAPE | Offset bolted tags |
| COLOR | None |
| INTERRUPT RATING | 200 kA RMS Sym, 50 kA at 500 Vdc |
| CONNECTION | Blade end x blade end |
| CONSTRUCTION SIZE | Other |
| MOUNTING METHOD | Stud |
| VOLTAGE RATING | 690 V (IEC), 700 V (UL) |
| TYPE | Fuse |
| APPLICATION | Semiconductor, DC Common bus, DC drives, power converters/rectifiers |
| FUSE TYPE | FE |
| SUITABLE FOR | EC-600 Trip indicator kit (indicator + clips) TI700 Fuse indicator MAI Microswitch/adaptor MBI Microswitch/adaptor |
| FUSE SYSTEM (ACCORDING TO IEC 60269) | Other |

DECLARATIONS OF CONFORMITY

[eaton-high-speed-british-standard-fuse-declaration-of-conformity-uk250922en.pdf](#)

| |
|-----------------|
| PROJECT NAME: |
| PROJECT NUMBER: |
| PREPARED BY: |
| : |



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

