

Eaton 216545

Eaton Moeller® series M22 Flush mounting plate, 4 mounting locations

PRODUCT NAME	Eaton Moeller® series M22 Accessory Flush mounting plate
CATALOG NUMBER	216545
PRODUCT LENGTH/DEPTH	3 mm
PRODUCT HEIGHT	72 mm
PRODUCT WIDTH	171 mm
PRODUCT WEIGHT	0.161 kg
CERTIFICATIONS	CE CSA Class No.: 3211-03 IEC/EN 60947-5 UL File No.: E29184 CSA-C22.2 No. 94-91 CSA File No.: 012528 UL 508 CSA CSA-C22.2 No. 14-05 UL UL Category Control No.: NKCR

TYPE	Surface mounting enclosure
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION	Does not apply, since the

IL04716003Z	
eaton-operating-mounting-m22-accessory-dimensions-005.eps	
eaton-operating-button-symbol-007.eps	
eaton-operating-mounting-m22-accessory-3d-drawing-004.eps	
/	RMQ small E-Stop emergency-stop button

AGAINST ELECTRIC SHOCK	entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
COLOR	Gray
CONNECTION TO SMARTWIRE-DT	No
DEGREE OF PROTECTION	IP65 Only in conjunction with a suitable enclosure and correct mounting NEMA 4X, 13
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
FORCE FOR POSITIVE OPENING - MIN	0 N
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
NUMBER OF COMMAND POSITIONS	4
NUMBER OF LOCATIONS	4
OPENING DIAMETER	22 mm
RAL-NUMBER	7035
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A

**STATIC HEAT
DISSIPATION, NON-
CURRENT-DEPENDENT
PVS**

0 W

MATERIAL Aluminum

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

