

Eaton 216563

Eaton Moeller® series M22 LED element,
white, front mount, 85-264VAC

PRODUCT NAME	Eaton Moeller® series M22 Accessory LED
CATALOG NUMBER	216563
PRODUCT LENGTH/DEPTH	38 mm
PRODUCT HEIGHT	10 mm
PRODUCT WIDTH	37 mm
PRODUCT WEIGHT	0.011 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	CSA Std. C22.2 No. 14-05 CSA Std. C22.2 No. 94-91 EN 60947-5 UL 508 IEC 60947-5 VDE CSA File No.: 012528 IEC/EN 60947-5 UL Category Control No.: NKCR UL CSA Class No.: 3211-03 CSA-C22.2 No. 94-91 IEC 60947-5-1 CE CSA CSA-C22.2 No. 14-05 UL File No.: E29184

10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.

DECLARATIONS OF CONFORMITY	DA-DC-00004135.pdf
	DA-DC-00004157.pdf
	IL04716002Z
	eaton-operating-devices-rmq-titan-m22-instruction-leaflet-il047018zu.pdf
	eaton-operating-actuation-m22-led-element-dimensions.eps
	eaton-operating-button-symbol-013.eps
/	RMQ small E-Stop emergency-stop button

10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Diode Light source
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	6000 V AC
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
FORCE FOR POSITIVE OPENING - MIN	0 N
HEAT DISSIPATION CAPACITY PDISS	0 W

HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
OPERATING TORQUE	0.8 Nm
RATED INSULATION VOLTAGE (UI)	500 V
RATED OPERATIONAL CURRENT (IE) - MAX	15 mA
RATED OPERATIONAL CURRENT (IE) - MIN	5 mA
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
RATED OPERATIONAL VOLTAGE (UE) AT AC - MAX	264 V
RATED OPERATIONAL VOLTAGE (UE) AT AC - MIN	85 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MAX	0 V
RATED OPERATIONAL VOLTAGE (UE) AT DC - MIN	0 V
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	1 W
COLOR	White
VOLTAGE TYPE	AC
FASTENING TYPE	Front fastening
MOUNTING POSITION	As required
LIGHT COLOR	White
CONNECTION TYPE	Front fixing
LAMP TYPE	LED
OVERVOLTAGE CATEGORY	III
CONNECTION TYPE (AUXILIARY CIRCUIT)	Screw connection
DEGREE OF PROTECTION	IP20
LAMP HOLDER	None
POWER CONSUMPTION	Max. 0.33 W
LIFESPAN, ELECTRICAL	100,000 h (at 25°C, according to EN60064)
TERMINAL CAPACITY (STRANDED)	0.5 - 2.5 mm ²

SHOCK RESISTANCE	30 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
TERMINAL CAPACITY (SOLID)	0.75 - 2.5 mm ²

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

