

Eaton 216616

Eaton Moeller® series M22 Pushbutton,
RMQ-Titan, Flat, maintained, White, Blank,
Bezel: black

PRODUCT NAME	Eaton Moeller® series M22 Pushbutton
CATALOG NUMBER	216616
PRODUCT LENGTH/DEPTH	30 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.011 kg
COMPLIANCES	CE Marked Bureau Veritas GoST-R
CERTIFICATIONS	CSA Certified CCC Marked Lloyd's Register Certified CE CSA File No.: 012528 CSA Class No.: 3211-03 IEC/EN 60947-5 UL File No.: E29184 VDE 0660 CSA-C22.2 No. 14-05 CSA CSA-C22.2 No. 94-91 IEC/EN 60947 UL UL 508 UL Category Control No.: NKCR DNV GL LR
CATALOG NOTES	Includes contact block mounting adapter.

TYPE	Pushbutton actuator
ACTUATOR COLOR	White
BEZEL	Black
ACTUATOR FUNCTION	Maintained Switching function latching
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF	Does not apply, since the entire switchgear needs to

DECLARATIONS OF CONFORMITY	eaton-pushbutton-declaration-of-conformity-uk251341en.pdf eaton-pushbutton-declaration-of-conformity-uk251340en.pdf
	IL04716002Z
	eaton-operating-pushbutton-m22-dimensions-004.eps eaton-operating-actuation-m22-dimensions-002.eps eaton-operating-pushbutton-m22-dimensions-003.eps eaton-operating-samrtwire-m22-3d-drawing.eps eaton-operating-button-symbol-013.eps
/	RMO small E-Stop emergency-stop button

ASSEMBLIES	be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Front ring
OPERATING FREQUENCY	1800 Operations/h
BUTTON COLOR	White
ACTUATOR	Flush, button
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	With SWD-RMQ connections Yes
ACTUATING FORCE	5 N
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
FORCE FOR POSITIVE OPENING - MIN	0 N
HEAT DISSIPATION	0 W

CAPACITY PDISS	
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
NUMBER OF COMMAND POSITIONS	1
OPENING DIAMETER	22.5 mm
OPENING HEIGHT	0 mm
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
ILLUMINATION	Non-illuminated
BEZEL COLOR	Black
SHOCK RESISTANCE	30 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
BEZEL MATERIAL	Plastic
DESIGN	Flat Classical
MOUNTING POSITION	As required
DEGREE OF PROTECTION	NEMA 3R NEMA 4X NEMA 12 IP66 IP69K NEMA 13 IP67
DEGREE OF PROTECTION (FRONT SIDE)	NEMA 4X IP67/IP69K
INSCRIPTION	Blank
FRONT ELEMENT TYPE	Flat
FUNCTIONS	Stay-put/spring-return function can be changed on device
LENS TYPE	Round
LIFESPAN, MECHANICAL	1,000,000 Operations (AC operated)
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
WIDTH OPENING	0 mm
PRODUCT CATEGORY	RMQ-Titan
SIZE	Front dimensions: 22 x 22 mm

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

