



Eaton 216637

Eaton Moeller® series M22 Pushbutton,
RMQ-Titan, Extended, momentary, black,
Blank, Bezel: black

□□□□

PRODUCT NAME	Eaton Moeller® series M22 Pushbutton
CATALOG NUMBER	216637
PRODUCT LENGTH/DEPTH	30 mm
PRODUCT HEIGHT	35 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.012 kg
CERTIFICATIONS	UL CSA CSA File No.: 012528 CSA-C22.2 No. 94-91 IEC/EN 60947-5 UL File No.: E29184 CSA-C22.2 No. 14-05 IEC/EN 60947 UL 508 CE CSA Class No.: 3211-03 UL Category Control No.: NKCR VDE 0660 DNV GL LR

TYPE	Pushbutton actuator
ACTUATOR COLOR	Black
ACTUATOR FUNCTION	Spring-return Momentary
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION	Does not apply, since the

DECLARATIONS OF CONFORMITY	eaton-pushbutton-declaration-of-conformity-uk251340en.pdf eaton-pushbutton-declaration-of-conformity-uk251341en.pdf
□□□□□	IL04716002Z eaton-operating-pushbutton-m22-dimensions.eps eaton-operating-pushbutton-m22-dimensions-005.eps eaton-operating-button-symbol-005.eps eaton-operating-samrtwire-m22-3d-drawing-002.eps
□□	RMQ small E-Stop emergency-stop button

AGAINST ELECTRIC SHOCK	entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Front ring
OPERATING FREQUENCY	3600 Operations/h
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	With SWD-RMQ connections Yes
ACTUATING FORCE	5 N
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	-40 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
FORCE FOR POSITIVE OPENING - MIN	0 N
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
NUMBER OF COMMAND POSITIONS	1
OPENING DIAMETER	22.5 mm
OPENING HEIGHT	0 mm

RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
BEZEL COLOR	Black
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 30 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
BEZEL MATERIAL	Plastic
DESIGN	Extended Classical
MOUNTING POSITION	As required
DEGREE OF PROTECTION	NEMA 12 IP66 IP69K NEMA 13 IP67 NEMA 4X NEMA 3R
DEGREE OF PROTECTION (FRONT SIDE)	IP67/IP69K NEMA 4X
INSCRIPTION	Blank
FRONT ELEMENT TYPE	High
LENS TYPE	Round
LIFESPAN, MECHANICAL	5,000,000 Operations
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	0 W
WIDTH OPENING	0 mm
PRODUCT CATEGORY	RMQ-Titan
SIZE	Front dimensions: 22 x 22 mm

□□□□:
□□□□:
□□□:
□□: