



## Eaton 216661

Eaton Moeller® series M22 Pushbutton, RMQ-Titan, Extended, momentary, White, inscribed, Bezel: titanium

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series M22 pushbutton
<b>CATALOG NUMBER</b>	216661
<b>PRODUCT LENGTH/DEPTH</b>	30 mm
<b>PRODUCT HEIGHT</b>	35 mm
<b>PRODUCT WIDTH</b>	30 mm
<b>PRODUCT WEIGHT</b>	0.012 kg
<b>CERTIFICATIONS</b>	UL 508 CE CSA-C22.2 No. 94-91 IEC/EN 60947-5 CSA CSA Class No.: 3211-03 CSA-C22.2 No. 14-05 VDE 0660 IEC/EN 60947 UL File No.: E29184 UL Category Control No.: NKCR CSA File No.: 012528 UL DNV GL LR



Powering Business Worldwide

□□□□

<b>TYPE</b>	Pushbutton actuator
<b>ACTUATOR COLOR</b>	White
<b>FEATURES</b>	Labelled
<b>ACTUATOR FUNCTION</b>	Momentary Spring-return
<b>10.10 TEMPERATURE RISE</b>	Not applicable.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Please enquire
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.

□□

<b>DECLARATIONS OF CONFORMITY</b>	<a href="#">eaton-pushbutton-declaration-of-conformity-uk251340en.pdf</a> <a href="#">eaton-pushbutton-declaration-of-conformity-uk251341en.pdf</a>
□□□□□	<a href="#">IL04716002Z</a> <a href="#">eaton-operating-pushbutton-m22-dimensions-005.eps</a>
□□	<a href="#">eaton-operating-pushbutton-m22-dimensions.eps</a> <a href="#">eaton-operating-samrtwire-m22-3d-drawing-002.eps</a>

<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>FITTED WITH:</b>	Front ring
<b>OPERATING FREQUENCY</b>	3600 Operations/h
<b>CLIMATIC PROOFING</b>	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
<b>CONNECTION TO SMARTWIRE-DT</b>	Yes With SWD-RMQ connections
<b>ACTUATING FORCE</b>	5 N
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>AMBIENT STORAGE TEMPERATURE - MAX</b>	80 °C
<b>AMBIENT STORAGE TEMPERATURE - MIN</b>	40 °C
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	0 W
<b>FORCE FOR POSITIVE OPENING - MIN</b>	0 N
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	0 W
<b>NUMBER OF COMMAND POSITIONS</b>	1
<b>OPENING DIAMETER</b>	22.5 mm
<b>RATED OPERATIONAL</b>	0 A

