



□□□□□

Eaton 216826

Eaton Moeller® series M22 Illuminated selector switch actuator, RMQ-Titan, With thumb-grip, maintained, 2 positions, red, Bezel: black

□□□□

PRODUCT NAME	Eaton Moeller® series M22 Illuminated selector switch actuator
CATALOG NUMBER	216826
PRODUCT LENGTH/DEPTH	46 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.013 kg
CERTIFICATIONS	CSA-C22.2 No. 14-05 IEC/EN 60947-5 UL UL 508 VDE 0660 CSA UL Category Control No.: NKCR UL File No.: E29184 CSA File No.: 012528 IEC/EN 60947 CSA Class No.: 3211-03 CSA-C22.2 No. 94-91 CE



Powering Business Worldwide

TYPE	Illuminated selector switch actuator
ACTUATOR COLOR	Black
BEZEL	Black
ACTUATOR FUNCTION	Maintained Switching function latching
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND	Meets the product

DECLARATIONS OF CONFORMITY

[eaton-key-operated-actuator-declaration-of-conformity-uk251348en.pdf](#)

[eaton-pushbutton-declaration-of-conformity-uk251341en.pdf](#)

□□□□□

[IL04716002Z](#)

□□/□□

[RMQ small E-Stop emergency-stop button](#)

CREEPAGE DISTANCES	standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Front ring
OPERATING FREQUENCY	2000 Operations/h
POLLUTION DEGREE	3
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
CONNECTION TO SMARTWIRE-DT	With SWD-RMQ connections Yes
ACTUATOR TYPE	Toggle
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
FORCE FOR POSITIVE OPENING - MIN	0 N
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
OPENING DIAMETER	22.5 mm
OPENING HEIGHT	0 mm
OPERATING TORQUE	0.3 Nm
RATED OPERATIONAL CURRENT FOR SPECIFIED	0 A

HEAT DISSIPATION (IN)	
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
SWITCHING ANGLE	60 °
WIDTH OPENING	0 mm
BEZEL COLOR	Black
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 30 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
COLOR	Red
BEZEL MATERIAL	Plastic
DESIGN	With thumb-grip
MOUNTING POSITION	As required
OVERVOLTAGE CATEGORY	III
DEGREE OF PROTECTION	NEMA 4X, 13
DEGREE OF PROTECTION (FRONT SIDE)	IP66
FUNCTIONS	Stay-put/spring-return function, can be changed with coding parts M22-XC-Y
INDICATOR COLOR	Red
LENS TYPE	Round
LIFESPAN, MECHANICAL	100,000 Operations
NUMBER OF SWITCH POSITIONS	2
SIZE	Front diameter: 29.7 mm
PRODUCT CATEGORY	RMQ-Titan
SUITABLE FOR	Illumination

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

