



□□□□□

Eaton 20D16R

Fuse-link, LV, 20 A, AC 500 V, D1, gR, IEC, ultra rapid

□□□□

PRODUCT NAME	Eaton Bussmann series low voltage D fuse
CATALOG NUMBER	20D16R
PRODUCT LENGTH/DEPTH	50 mm
PRODUCT HEIGHT	14 mm
PRODUCT WIDTH	14 mm
PRODUCT WEIGHT	14.2 g
COMPLIANCES	CE Marked RoHS Compliant
CERTIFICATIONS	IEC 60269 EAC DIN EN 60269-3 (VDE 0636 Part 30) DIN EN 60269-1 (VDE 0636 Part 10) DIN VDE 0636-301

Eaton	
AMPERAGE RATING	20 A
FUSE SIZE	DI
BREAKING CAPACITY	50 kA
CONSTRUCTION SIZE (FUSE INSERTS)	DI
RATED VOLTAGE AC	500 V
CLASS	Class gR
FUSE TYPE	D16R - Ultra rapid
UTILIZATION CATEGORY	gR (general purpose semiconductor protection)
ACCESSORY/SPARE PART TYPE	20GD16 Blue screw cap gauge piece
COLOR	Blue
INTERRUPT RATING	50 kAIC
FUSE INDICATOR	Non-indicating
CONNECTION	Other
CONSTRUCTION	D1
CONSTRUCTION SIZE	DI
FUSE SHAPE	Bottle
RESPONSE TIME	Ultra rapid
SUITABLE FOR	E16/DI Fuse base
MATERIAL	White ceramic body
RELEASE CHARACTERISTIC	Super fast (FF)
VOLTAGE RATING	500 V
TYPE	Fuse
APPLICATION	For domestic and general industrial applications

Eaton	
DECLARATIONS OF CONFORMITY	eaton-low-voltage-d-fuse-declaration-of-conformity-uk251016en.pdf