



□□□□□

Eaton 210073

Eaton Moeller® series Z5 Overload relay, Ir= 120 - 160 A, 1 N/O, 1 N/C, For use with: DILM250

□□□□

PRODUCT NAME	Eaton Moeller® series Z5 Thermal overload relay
CATALOG NUMBER	210073
PRODUCT LENGTH/DEPTH	146 mm
PRODUCT HEIGHT	167 mm
PRODUCT WIDTH	128 mm
PRODUCT WEIGHT	1.728 kg
CERTIFICATIONS	CSA File No.: 012528 IEC/EN 60947-4-1 CSA-C22.2 No. 60947-4-1-14 UL UL Category Control No.: NKCR VDE 0660 CSA CSA Class No.: 3211-03 IEC/EN 60947 UL 60947-4-1 UL File No.: E29184 CE

FEATURES	Trip-free release Test/off button Reset pushbutton manual/auto Phase-failure sensitivity (according to IEC/EN 60947, VDE 0660 Part 102)
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

CHARACTERISTIC CURVE	eaton-tripping-z5-overload-relay-characteristic-curve.eps eaton-tripping-z5-overload-relay-characteristic-curve-005.eps
DECLARATIONS OF CONFORMITY	eaton-thermal-overload-relay-declaration-of-conformity-uk251268en.pdf
□□□□□	eaton-overload-relays-z5-zb150-il03407006z.pdf
□□□	eaton-tripping-devices-overload-relay-zeb-overload-relay-wiring-diagram.eps
	eaton-tripping-devices-overload-relay-z5-overload-relay-dimensions-002.eps
□□	eaton-tripping-devices-overload-relay-z5-overload-relay-3d-drawing.eps

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
POLLUTION DEGREE	3
CLASS	CLASS 10 A
CLIMATIC PROOFING	Damp heat, cyclic, to IEC 60068-2-30 Damp heat, constant, to IEC 60068-2-78
RATED IMPULSE WITHSTAND VOLTAGE (UIMP)	4000 V (auxiliary and control circuits) 8000 V AC
RATED OPERATIONAL CURRENT (IE) AT AC-15, 220 V, 230 V, 240 V	1.5 A
RATED OPERATIONAL CURRENT (IE) AT AC-15, 380 V, 400 V, 415 V	0.9 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 110 V	0.4 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 220 V, 230 V	0.2 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 24 V	0.9 A
RATED OPERATIONAL CURRENT (IE) AT DC-13, 60 V	0.75 A
RATED OPERATIONAL	160 A

CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	0 W
STRIPPING LENGTH (CONTROL CIRCUIT CABLE)	8 mm
VOLTAGE RATING - MAX	600 VAC
PRODUCT CATEGORY	Overload relay Z5
PROTECTION	With terminal cover, Protection against direct contact when actuated from front (EN 50274)
ADJUSTABLE CURRENT RANGE - MAX	160 A
ADJUSTABLE CURRENT RANGE - MIN	120 A
AMBIENT OPERATING TEMPERATURE - MAX	60 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MAX	40 °C
AMBIENT OPERATING TEMPERATURE (ENCLOSED) - MIN	-25 °C
CONVENTIONAL THERMAL CURRENT ITH OF AUXILIARY CONTACTS (1-POLE, OPEN)	6 A
EQUIPMENT HEAT DISSIPATION, CURRENT- DEPENDENT PVID	24 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT- DEPENDENT PVID	8 W
NUMBER OF AUXILIARY CONTACTS (CHANGE- OVER CONTACTS)	0
NUMBER OF AUXILIARY CONTACTS (NORMALLY CLOSED CONTACTS)	1
NUMBER OF AUXILIARY CONTACTS (NORMALLY OPEN CONTACTS)	1
NUMBER OF CONTACTS (NORMALLY CLOSED)	1

CONTACTS)	
NUMBER OF CONTACTS (NORMALLY OPEN CONTACTS)	1
OVERLOAD RELEASE CURRENT SETTING - MAX	160 A
OVERLOAD RELEASE CURRENT SETTING - MIN	120 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	1000 V
RATED OPERATIONAL CURRENT (IE) AT AC-15, 120 V	1.5 A
ELECTRICAL CONNECTION TYPE OF MAIN CIRCUIT	Screw connection
RESET FUNCTION	Push-button Automatic
SCREWDRIVER SIZE	2, Terminal screw, Control circuit cables, Pozidriv screwdriver 1 x 6 mm, Terminal screw, Control circuit cables, Standard screwdriver
MOUNTING METHOD	Direct mounting Separate mounting Direct attachment
DEGREE OF PROTECTION	IP00
OVERVOLTAGE CATEGORY	III
SAFE ISOLATION	440 V, Between auxiliary contacts and main contacts, According to EN 61140 500 V AC, Between main circuits, According to EN 61140 240 V AC, Between auxiliary contacts, According to EN 61140
SCREW SIZE	M10 x 35, Terminal screw, Main connections M3.5, Terminal screw, Control circuit cables
SHOCK RESISTANCE	10 g, Mechanical, Sinusoidal, Shock duration 10 ms
SHORT-CIRCUIT CURRENT RATING (BASIC RATING)	10 kA, SCCR (UL/CSA) 600 A Class J, max. Fuse, SCCR (UL/CSA) 600 A, max. CB, SCCR (UL/CSA)
SWITCHING CAPACITY	B600 at opposite polarity,

(AUXILIARY CONTACTS, PILOT DUTY)	AC operated (UL/CSA) R300, DC operated (UL/CSA) B300 at opposite polarity, AC operated (UL/CSA)
SHORT-CIRCUIT PROTECTION RATING	Max. 6 A gG/gL, fuse, Without welding, Auxiliary and control circuits 400 A gG/gL, Fuse, Type "1" coordination 250 A gG/gL, Fuse, Type "2" coordination
SUITABLE FOR	Branch circuits, (UL/CSA)
TEMPERATURE COMPENSATION	$\leq 0.25\text{ \%}/\text{K}$, residual error for $T > 40^\circ$ Continuous
TERMINAL CAPACITY (BUSBAR)	25 mm width, Main connection
TERMINAL CAPACITY (FLEXIBLE WITH CABLE LUG)	185 mm ²
TERMINAL CAPACITY (FLEXIBLE WITH FERRULE)	2 x (0.75 - 2.5) mm ² , Control circuit cables 1 x (0.75 - 2.5) mm ² , Control circuit cables
TERMINAL CAPACITY (SOLID)	1 x (0.75 - 4) mm ² , Control circuit cables 2 x (0.75 - 4) mm ² , Control circuit cables
TERMINAL CAPACITY (SOLID/STRANDED AWG)	2 x (18 - 14), Control circuit cables 2/0 - 500 MCM, Main cables
TERMINAL CAPACITY (STRANDED WITH CABLE LUG)	185 mm ²
TIGHTENING TORQUE	1.2 Nm, Screw terminals, Control circuit cables 18 Nm, Main cable connection screw/bolt
WIDTH ACROSS FLATS	16 mm (Hexagon head spanner SW)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

