

Eaton 218153

Eaton Moeller® series M22 Button plate, flat red

PRODUCT NAME	Eaton Moeller® series M22 Accessory Button plate
CATALOG NUMBER	218153
PRODUCT LENGTH/DEPTH	24 mm
PRODUCT HEIGHT	3 mm
PRODUCT WIDTH	24 mm
PRODUCT WEIGHT	0.002 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	UL 508 CSA Std. C22.2 No. 14 IEC 60947 EN 60947 CSA IEC/EN 60947 CSA Class No.: 3211-03 CSA File No.: 012528 CSA-C22.2 No. 14 CE UL Category Control No.: NKCR UL File No.: E29184 UL

USED WITH	M22-DZ-X M22(S)-D-X M22(S)-DR-X M22-DG-X
TYPE	Flat
PRODUCT CATEGORY	Accessories
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS	Is the panel builder's responsibility.

	IL04716002Z
	eaton-operating-m22-accessory-3d-drawing-007.eps
/	RMO small E-Stop emergency-stop button

AND CONNECTIONS	
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
CONSTRUCTION TYPE	Flat
BUTTON COLOR	Red
CONNECTION TO SMARTWIRE-DT	No
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
OPENING DIAMETER	22.3 mm
OUTSIDE DIAMETER	22.5 mm
PROGRAM DIAMETER	22 mm
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
COLOR	Red
SHAPE	Round
DESIGN	Flush
LANGUAGE	Other
INSCRIPTION	Other
INSCRIPTION TYPE	Symbol
IMPRINT	Other
IMPRINT ISO SYMBOLS	Symbol "0"
SUITABLE FOR	Push button

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
: