



Eaton 215655

Eaton Moeller series xPole - Busbar. EV busbars 1Ph., 2.5HP, for auxiliary contact unit

□□□□

PRODUCT NAME	Eaton Moeller series busbar
CATALOG NUMBER	215655
PRODUCT LENGTH/DEPTH	45 mm
PRODUCT HEIGHT	30 mm
PRODUCT WIDTH	4 mm
PRODUCT WEIGHT	0.01 kg
COMPLIANCES	RoHS conform

□□□□

USED WITH	Busbar EVG
TYPE	• Busbar • EVG
FEATURES	Insulated
ACCESSORY/SPARE PART TYPE	Busbar for combined residual current/power circuit breaker Busbar for miniature circuit breaker Busbar for residual current circuit breakers
ELECTRIC CONNECTION TYPE	Fork
RATED SURGE VOLTAGE	4 kV
RATED UNINTERRUPTED CURRENT (IU)	63 A
SUITABLE FOR NUMBER OF DEVICES	3
NUMBER OF POLES	Single-pole
COLOR	Other
RATED SHORT-TIME WITHSTAND CURRENT (ICW)	0 kA
CROSS SECTION	10 mm ²
NUMBER OF MODULAR SPACINGS	2
NUMBER OF PHASES	1
PITCH DIMENSIONS	0 mm
RATED OPERATIONAL VOLTAGE (UE) - MAX	500 V
RATED CONDITIONAL SHORT-CIRCUIT CURRENT (IQ)	25 kA
FUNCTIONS	Busbar
SUITABLE FOR	Devices with N-busbar Devices with auxiliary switch 2 devices

□□

□□ [eaton-busbar-3d-drawing.jpg](#)

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

