



□□□□□

Eaton 216664

Eaton Moeller® series M22 Pushbutton,
RMQ-Titan, Extended, maintained, black,
Blank, Bezel: black

□□□□

PRODUCT NAME	Eaton Moeller® series M22 Pushbutton
CATALOG NUMBER	216664
PRODUCT LENGTH/DEPTH	30 mm
PRODUCT HEIGHT	35 mm
PRODUCT WIDTH	30 mm
PRODUCT WEIGHT	0.013 kg
CERTIFICATIONS	IEC/EN 60947-5 UL 508 CE CSA Class No.: 3211-03 CSA VDE 0660 CSA-C22.2 No. 94-91 IEC/EN 60947 UL UL Category Control No.: NKCR UL File No.: E29184 CSA File No.: 012528 CSA-C22.2 No. 14-05 DNV GL LR

□□□□

TYPE	Pushbutton actuator
ACTUATOR COLOR	Black
ACTUATOR FUNCTION	Switching function latching Maintained
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.

□□

DECLARATIONS OF CONFORMITY	eaton-pushbutton-declaration-of-conformity-uk251340en.pdf eaton-pushbutton-declaration-of-conformity-uk251341en.pdf
□□□□□	IL04716002Z
□□	eaton-operating-pushbutton-m22-dimensions.eps eaton-operating-pushbutton-m22-dimensions-005.eps eaton-operating-samrtwire-m22-3d-drawing-002.eps eaton-operating-button-symbol-005.eps
□□/□□	RMQ small E-Stop emergency-stop button

10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Front ring
OPERATING FREQUENCY	1800 Operations/h
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	Yes With SWD-RMQ connections
ACTUATING FORCE	5 N
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
AMBIENT STORAGE TEMPERATURE - MAX	80 °C
AMBIENT STORAGE TEMPERATURE - MIN	40 °C
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
FORCE FOR POSITIVE OPENING - MIN	0 N
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID	0 W
NUMBER OF COMMAND POSITIONS	1
OPENING DIAMETER	22.5 mm
OPENING HEIGHT	0 mm

RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
BEZEL COLOR	Black
SHOCK RESISTANCE	30 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms Mechanical, According to IEC/EN 60068-2-27
BEZEL MATERIAL	Plastic
DESIGN	Extended Classical
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP67 NEMA 3R NEMA 4X NEMA 13 IP69K NEMA 12 IP66
DEGREE OF PROTECTION (FRONT SIDE)	NEMA 4X IP67/IP69K
INSCRIPTION	Blank
FRONT ELEMENT TYPE	High
FUNCTIONS	Stay-put/spring-return function can be changed on device
LENS TYPE	Round
LIFESPAN, MECHANICAL	1,000,000 Operations (AC operated)
STATIC HEAT DISSIPATION, NON- CURRENT-DEPENDENT PVS	0 W
WIDTH OPENING	0 mm
PRODUCT CATEGORY	RMQ-Titan
SIZE	Front dimensions: 22 x 22 mm

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:



 Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

