



## Eaton 221511

Eaton Moeller® series STN Control transformer, 0.315 kVA, Rated input voltage 400± 5 % V, Rated output voltage 24 V

□□□□

<b>PRODUCT NAME</b>	Eaton Moeller® series STN Control transformer
<b>CATALOG NUMBER</b>	221511
<b>PRODUCT LENGTH/DEPTH</b>	91 mm
<b>PRODUCT HEIGHT</b>	112 mm
<b>PRODUCT WIDTH</b>	106 mm
<b>PRODUCT WEIGHT</b>	4.52 kg
<b>CERTIFICATIONS</b>	IEC/EN 60204-1, ÖVE-EN 13 UL report applies to both US and Canada IEC/EN 61558-2-2 UL 5085-2 CSA-C22.2 No. 66 CE Certified by UL for use in Canada UL File No.: E167225 CSA-C22.2 No. 66.2-06 UL5085-1 VDE 0113, VDE 0100 Part 410 UL Recognized CSA-C22.2 No. 66.1-06 UL Category Control No.: XPTQ2, XPTQ8 UL 506 VDE 0570 Part 2-2
<b>CATALOG NOTES</b>	Electrical characteristics: all details for no-load loss, short-circuit loss (copper losses), short-circuit voltage and efficiency values relate to a temperature of 20 °C



Powering Business Worldwide

<b>TYPE</b>	Single-phase STN control transformers
<b>FEATURES</b>	Separate windings Fully Vacuum-impregnated
<b>10.10 TEMPERATURE RISE</b>	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Meets the product standard's requirements.
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF</b>	Does not apply, since the entire switchgear needs to

DECLARATIONS OF CONFORMITY	<a href="#">eaton-control-transformer-declaration-of-conformity-uk251061en.pdf</a>
SYSTEM OVERVIEW	<a href="#">eaton-general-diagram-sti-control-transformer-explosion-drawing.eps</a>
□□	<a href="#">eaton-general-control-stn-control-transformer-dimensions-008.eps</a>

<b>ASSEMBLIES</b>	be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	40 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>APPARENT POWER</b>	315 VA
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	0 W
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	0 W
<b>NO-LOAD LOSSES</b>	11 W
<b>PRIMARY VOLTAGE 1 - MAX</b>	400 V
<b>PRIMARY VOLTAGE 1 - MIN</b>	400 V
<b>CONDUCTOR MATERIAL</b>	Copper
<b>DEGREE OF PROTECTION</b>	IP00
<b>CONNECTION LUG</b>	Yes for > 115 A
<b>CONNECTION TYPE</b>	Terminations, < 115 A
<b>DUTY FACTOR</b>	100 %
<b>INSULATION MATERIAL TYPE (IEC 85)</b>	B
<b>EFFICIENCY</b>	91 %
<b>RELATIVE SHORT-CIRCUIT</b>	5.3 %

