

Eaton 216876

Eaton Moeller® series M22 Emergency stop/emergency switching off pushbutton, RMQ-Titan, Mushroom-shaped, 38 mm, Non-illuminated, Pull-to-release function, Red, yellow, RAL 3000

PRODUCT NAME	Eaton Moeller® series M22 Emergency stop/emergency switching off pushbutton
CATALOG NUMBER	216876
PRODUCT LENGTH/DEPTH	38 mm
PRODUCT HEIGHT	70 mm
PRODUCT WIDTH	38 mm
PRODUCT WEIGHT	0.039 kg
COMPLIANCES	CE Marked
CERTIFICATIONS	EN 60947-5 CSA Std. C22.2 No. 94-91 IEC 60947-5 UL 508 CSA Std. C22.2 No. 14-05 VDE UL CE CSA File No.: 012528 IEC/EN 60947-5 CSA IEC/EN 60947 UL File No.: E29184 CSA Class No.: 3211-03 CSA-C22.2 No. 14-05 CSA-C22.2 No. 94-91 VDE 0660 UL Category Control No.: NKCR DNV GL LR
CATALOG NOTES	Max. number of contacts: four M22-(C)K01, ...10 or



Powering Business Worldwide

TYPE	Controlled stop pushbutton/emergency- stop button
ACTUATOR COLOR	Red
FEATURES	Tamper-proof (according to ISO 13850, EN 418)
ACTUATOR FUNCTION	Pull-to-release Switching function latching
10.10 TEMPERATURE RISE	Not applicable.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.
10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Please enquire
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.

DECLARATIONS OF CONFORMITY	eaton-emergency-stop- emergency-switching-off- pushbutton-declaration- of-conformity- uk251132en.pdf
	IL04716005Z.pdf IL04716002Z
	eaton-operating- emergency-m22- dimensions.eps eaton-operating- emergency-m22-3d- drawing-003.eps
/	RMQ small E-Stop emergency-stop button

10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
OPERATING FREQUENCY	600 Operations/h
BUTTON COLOR	Red
CLIMATIC PROOFING	Damp heat, constant, to IEC 60068-2-78 Damp heat, cyclic, to IEC 60068-2-30
CONNECTION TO SMARTWIRE-DT	No
BASE COLOR	Yellow
ACTUATING FORCE	50 N
ACTUATOR DIAMETER	38 mm
AMBIENT OPERATING TEMPERATURE - MAX	70 °C
AMBIENT OPERATING TEMPERATURE - MIN	-25 °C
DIAMETER CAP	38 mm
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID	0 W
FORCE FOR POSITIVE OPENING - MIN	0 N
HEAT DISSIPATION CAPACITY PDISS	0 W
HEAT DISSIPATION PER	0 W

POLE, CURRENT-DEPENDENT PVID	
OPENING DIAMETER	22.5 mm
OPENING HEIGHT	0 mm
RAL-NUMBER	3000
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	0 A
ILLUMINATION	Non-illuminated
BEZEL COLOR	Other
SHOCK RESISTANCE	Mechanical, According to IEC/EN 60068-2-27 50 g, Mechanical, According to IEC/EN 60068-2-27, Sinusoidal shock 11 ms
COLOR	Red
BEZEL MATERIAL	Other
DESIGN	Mushroom-shaped Classical
MOUNTING POSITION	As required
DEGREE OF PROTECTION	IP66 NEMA 4X, 13
FRONT ELEMENT TYPE	High
LENS TYPE	Round
LIFESPAN, MECHANICAL	100,000 Operations
STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS	0 W
WIDTH OPENING	0 mm
PRODUCT CATEGORY	RMQ-Titan
SIZE	Front dimensions: 35 mm
SUPPLY VOLTAGE LAMP	0 V
SUITABLE FOR	Emergency stop
UNLOCKING METHOD	Pull-release

PROJECT NAME:
PROJECT NUMBER:
PREPARED BY:
:



Eaton House
30 Pembroke Road
Dublin 4,
Eaton.com

© 2025

Follow us on social media to get the latest product and support information.

