



## Eaton 218192

Eaton Moeller® series M22 Button plate, flat black, raised

XXXX	
<b>PRODUCT NAME</b>	Eaton Moeller® series M22 button plate
<b>CATALOG NUMBER</b>	218192
<b>PRODUCT LENGTH/DEPTH</b>	24 mm
<b>PRODUCT HEIGHT</b>	3 mm
<b>PRODUCT WIDTH</b>	24 mm
<b>PRODUCT WEIGHT</b>	0.002 kg
<b>CERTIFICATIONS</b>	UL/CSA certification not required

□□□

<b>PRODUCT CATEGORY</b>	Accessories
<b>10.10 TEMPERATURE RISE</b>	Not applicable.
<b>10.11 SHORT-CIRCUIT RATING</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.12 ELECTROMAGNETIC COMPATIBILITY</b>	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
<b>10.13 MECHANICAL FUNCTION</b>	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
<b>10.2.2 CORROSION RESISTANCE</b>	Meets the product standard's requirements.
<b>10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES</b>	Meets the product standard's requirements.
<b>10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT</b>	Meets the product standard's requirements.
<b>10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS</b>	Meets the product standard's requirements.
<b>10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION</b>	Please enquire
<b>10.2.5 LIFTING</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.6 MECHANICAL IMPACT</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.2.7 INSCRIPTIONS</b>	Meets the product standard's requirements.
<b>10.3 DEGREE OF PROTECTION OF ASSEMBLIES</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.4 CLEARANCES AND CREEPAGE DISTANCES</b>	Meets the product standard's requirements.
<b>10.5 PROTECTION AGAINST ELECTRIC SHOCK</b>	Does not apply, since the entire switchgear needs to be evaluated.
<b>10.6 INCORPORATION OF</b>	Does not apply, since the

□□

□□□□	<a href="#">IL04716002Z</a>
□□	<a href="#">eaton-operating-button-symbol-005.eps</a>

<b>SWITCHING DEVICES AND COMPONENTS</b>	entire switchgear needs to be evaluated.
<b>10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS</b>	Is the panel builder's responsibility.
<b>10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS</b>	Is the panel builder's responsibility.
<b>10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH</b>	Is the panel builder's responsibility.
<b>10.9.3 IMPULSE WITHSTAND VOLTAGE</b>	Is the panel builder's responsibility.
<b>10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL</b>	Is the panel builder's responsibility.
<b>CONSTRUCTION TYPE</b>	Flat
<b>CONNECTION TO SMARTWIRE-DT</b>	No
<b>AMBIENT OPERATING TEMPERATURE - MAX</b>	70 °C
<b>AMBIENT OPERATING TEMPERATURE - MIN</b>	-25 °C
<b>EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT PVID</b>	0 W
<b>HEAT DISSIPATION CAPACITY PDISS</b>	0 W
<b>HEAT DISSIPATION PER POLE, CURRENT-DEPENDENT PVID</b>	0 W
<b>OUTSIDE DIAMETER</b>	22.5 mm
<b>PROGRAM DIAMETER</b>	22 mm
<b>RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)</b>	0 A
<b>STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT PVS</b>	0 W
<b>COLOR</b>	Black
<b>SHAPE</b>	Round
<b>DESIGN</b>	Flush
<b>LANGUAGE</b>	German
<b>INSCRIPTION</b>	" HEBEN "
<b>INSCRIPTION TYPE</b>	Text
<b>IMPRINT</b>	Other
<b>IMPRINT ISO SYMBOLS</b>	None
<b>SUITABLE FOR</b>	Push button

□□□□:

四

10

11

**EATON**  
Powering Business Worldwide

□□□□ Eaton House  
30 Pembroke Road  
Dublin 4, □□□  
Eaton.com

© 2026     

