



Eaton 235409

Eaton Moeller series xPole - PFIM Type AC, A, U, R RCCB. Residual current circuit breaker (RCCB), 25A, 4p, 500mA, type AC

|||||

PRODUCT NAME	Eaton Moeller series xPole - PFIM Type AC, A, U, R RCCB
CATALOG NUMBER	235409
PRODUCT LENGTH/DEPTH	76 mm
PRODUCT HEIGHT	80 mm
PRODUCT WIDTH	70 mm
PRODUCT WEIGHT	0.298 kg
COMPLIANCES	RoHS conform
CERTIFICATIONS	IEC/EN 61008

0000

USED WITH	Residual current circuit breakers Type AC PFIM KLV-TC-4 276241 (Compact enclosure) Z-FW/LP 248296 (Remote control and automatic switching device) Z-RC/AK-4MU 101062 (sealing cover set)
AMPERAGE RATING	25 A
VOLTAGE RATING	230 V AC / 400 V AC
FEATURES	Additional equipment possible Residual current circuit breaker
ACCESSORIES REQUIRED	Z-HK 248432
10.10 TEMPERATURE RISE	The panel builder is responsible for the temperature rise calculation. Eaton will provide heat dissipation data for the devices.
10.11 SHORT-CIRCUIT RATING	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.12 ELECTROMAGNETIC COMPATIBILITY	Is the panel builder's responsibility. The specifications for the switchgear must be observed.
10.13 MECHANICAL FUNCTION	The device meets the requirements, provided the information in the instruction leaflet (IL) is observed.
10.2.2 CORROSION RESISTANCE	Meets the product standard's requirements.
10.2.3.1 VERIFICATION OF THERMAL STABILITY OF ENCLOSURES	Meets the product standard's requirements.
10.2.3.2 VERIFICATION OF RESISTANCE OF INSULATING MATERIALS TO NORMAL HEAT	Meets the product standard's requirements.
10.2.3.3 RESIST. OF INSUL. MAT. TO ABNORMAL HEAT/FIRE BY INTERNAL ELECT. EFFECTS	Meets the product standard's requirements.

00

00000	eaton-rccb-rcbo-g9-il019140zu.pdf
00000	eaton-xpole-pfim-x-rccb-catalog-ca019029en-en-us.pdf
	eaton-xpole-pf67-rccb-3d-drawing.jpg
	eaton-circuit-breaker-xeffect-frcmm-rccb-dimensions.jpg

10.2.4 RESISTANCE TO ULTRA-VIOLET (UV) RADIATION	Meets the product standard's requirements.
10.2.5 LIFTING	Does not apply, since the entire switchgear needs to be evaluated.
10.2.6 MECHANICAL IMPACT	Does not apply, since the entire switchgear needs to be evaluated.
10.2.7 INSCRIPTIONS	Meets the product standard's requirements.
10.3 DEGREE OF PROTECTION OF ASSEMBLIES	Does not apply, since the entire switchgear needs to be evaluated.
10.4 CLEARANCES AND CREEPAGE DISTANCES	Meets the product standard's requirements.
10.5 PROTECTION AGAINST ELECTRIC SHOCK	Does not apply, since the entire switchgear needs to be evaluated.
10.6 INCORPORATION OF SWITCHING DEVICES AND COMPONENTS	Does not apply, since the entire switchgear needs to be evaluated.
10.7 INTERNAL ELECTRICAL CIRCUITS AND CONNECTIONS	Is the panel builder's responsibility.
10.8 CONNECTIONS FOR EXTERNAL CONDUCTORS	Is the panel builder's responsibility.
10.9.2 POWER-FREQUENCY ELECTRIC STRENGTH	Is the panel builder's responsibility.
10.9.3 IMPULSE WITHSTAND VOLTAGE	Is the panel builder's responsibility.
10.9.4 TESTING OF ENCLOSURES MADE OF INSULATING MATERIAL	Is the panel builder's responsibility.
FITTED WITH:	Interlocking device
FRAME	45 mm
FREQUENCY RATING	50 Hz
POLLUTION DEGREE	2
LIFESPAN, MECHANICAL	20000 operations
MOUNTING METHOD	DIN rail Quick attachment with 2 latch positions for DIN-rail IEC/EN 60715
CLIMATIC PROOFING	25-55 °C / 90-95% relative humidity according to IEC 60068-2
EQUIPMENT HEAT DISSIPATION, CURRENT-DEPENDENT	2.8 W
RATED IMPULSE	4 kV

WITHSTAND VOLTAGE

(UIMP)

RATED SHORT-TIME**WITHSTAND CURRENT**

(ICW)

10 kA

ADMISSIBLE BACK-UP**FUSE OVERLOAD - MAX**

16 A gG/gL

BUILT-IN WIDTH

(NUMBER OF UNITS)

70 mm (4 SU)

BUSBAR MATERIAL**THICKNESS**

0.8 mm - 2 mm

SHORT-CIRCUIT RATING

63 A (max. admissible back-up fuse)

TERMINAL PROTECTION

Finger and hand touch safe, DGUV VS3, EN 50274

TERMINALS (TOP AND BOTTOM)

Open mouthed/lift terminals

TEST CIRCUIT RANGE

196 V AC - 456 V AC

AMBIENT OPERATING**TEMPERATURE - MAX**

55 °C

AMBIENT OPERATING**TEMPERATURE - MIN**

-25 °C

BUILT-IN DEPTH

70.5 mm

CONNECTABLE**CONDUCTOR CROSS SECTION (MULTI-WIRED) - MAX**16 mm²**CONNECTABLE****CONDUCTOR CROSS SECTION (MULTI-WIRED) - MIN**1.5 mm²**CONNECTABLE****CONDUCTOR CROSS SECTION (SOLID-CORE) - MAX**35 mm²**CONNECTABLE****CONDUCTOR CROSS SECTION (SOLID-CORE) - MIN**1.5 mm²**FAULT CURRENT RATING**

500 mA

HEAT DISSIPATION**CAPACITY**

0 W

HEAT DISSIPATION PER**POLE, CURRENT-**

0 W

DEPENDENT**PERMITTED STORAGE****AND TRANSPORT**

60 °C

TEMPERATURE - MAX**PERMITTED STORAGE****AND TRANSPORT**

-35 °C

TEMPERATURE - MIN

DEGREE OF PROTECTION	IP20 IP20, IP40 with suitable enclosure
IMPULSE WITHSTAND CURRENT	Partly surge-proof 250 A
NUMBER OF POLES	Four-pole
LEAKAGE CURRENT TYPE	AC
LIFESPAN, ELECTRICAL	4000 operations
TYPE	<ul style="list-style-type: none"> • PFIM • Residual current circuit breakers • Type AC
SPECIAL FEATURES	<ul style="list-style-type: none"> • Maximum operating temperature is 55 °C: Starting at 40 °C, the max. permissible continuous current decreases by 3% for every 1 °C • Tripping signal contact for subsequent installation Z-NHK 248434
APPLICATION	<ul style="list-style-type: none"> • Residual current circuit breaker for residential and commercial applications • xPole - Switchgear for residential and commercial applications
SENSITIVITY TYPE	AC current sensitive
RATED FAULT CURRENT - MAX	0.5 A
RATED FAULT CURRENT - MIN	0.5 A
RATED INSULATION VOLTAGE (UI)	440 V
RATED OPERATIONAL CURRENT FOR SPECIFIED HEAT DISSIPATION (IN)	25 A
RATED OPERATIONAL VOLTAGE (UE) - MAX	400 V
RATED RESIDUAL MAKING AND BREAKING CAPACITY	500 A

STATIC HEAT DISSIPATION, NON-CURRENT-DEPENDENT	0 W
SURGE CURRENT CAPACITY	0.25 kA
WIDTH IN NUMBER OF MODULAR SPACINGS	4
VOLTAGE TYPE	AC
TERMINAL CAPACITY (SOLID WIRE)	1.5 mm ² - 35 mm ²
TRIPPING TIME	Non-delayed
RATED SHORT-CIRCUIT STRENGTH	10 kA
TERMINAL CAPACITY (STRANDED CABLE)	16 mm ² (2x)
RAL-NUMBER	7035
POWER LOSS	2.8 W
COLOR	Gray

□□□□:

□□□□:

□□□:

□□: